



Military Standard Connector Index

Military Standard Connector Index

The following is a listing of circular connectors defined by US Military Specifications, cross-referenced to the applicable active or inactive part number series. The symbols in the Connector Designator column are an essential element in Glenair's backshell part number developments.

| Part No. | Connector Designator | Specification | Series | Description |
|---|----------------------|---------------|--------|--|
| MS3100 | B | SAE AS50151 | MS3100 | Receptacle Wall Mount (Solder)*** |
| MS3101 | B | SAE AS50151 | MS3100 | Plug (Solder)*** |
| MS3102 | ** | SAE AS50151 | MS3100 | Receptacle Box Mount (Solder)*** |
| MS3103 | ** | SAE AS50151 | MS3100 | Receptacle Potting (Solder)*** |
| MS3105 | ** | SAE AS50151 | MS3100 | Dummy Receptacle*** |
| MS3106 | B | SAE AS50151 | MS3100 | Plug Straight (Solder)*** |
| MS3107 | B | SAE AS50151 | MS3100 | Plug Quick Disconnect (Solder)*** |
| MS3108 | B | SAE AS50151 | MS3100 | Plug 90° (Solder)*** |
| MS3110 | D-729 | MIL-DTL-26482 | 1 | Receptacle Wall Mount |
| MS3111 | D | MIL-DTL-26482 | 1 | Plug Cable Connecting |
| MS3112 | ** | MIL-DTL-26482 | 1 | Receptacle Box Mount |
| MS3113 | ** | MIL-DTL-26482 | 1 | Receptacle Solder Mount |
| MS3114 | D-717 | MIL-DTL-26482 | 1 | Receptacle Jam Nut |
| MS3115 | ** | MIL-DTL-26482 | 1-2 | Dummy Receptacle |
| MS3116 | D | MIL-DTL-26482 | 1 | Plug Straight |
| MS3119 | ** | MIL-DTL-26482 | 1 | Receptacle Thru-Bulkhead |
| MS3120 | D | MIL-DTL-26482 | 1 | Receptacle Wall Mount (Crimp) |
| MS3121 | D | MIL-DTL-26482 | 1 | Plug Straight (Crimp) |
| MS3122 | ** | MIL-DTL-26482 | 1 | Receptacle Box Mount (Crimp) |
| MS3124 | D-717 | MIL-DTL-26482 | 1 | Receptacle Rear Mount Jam Nut (Crimp) |
| MS3126 | D | MIL-DTL-26482 | 1 | Plug Straight (Crimp) |
| MS3127 | ** | MIL-DTL-26482 | 1 | Receptacle Box Mount (Crimp) |
| MS3128 | D | MIL-DTL-26482 | 1 | Receptacle Wall Mount (Crimp) |
| MS3130 | * | QPL-81703 | 1 | Receptacle Push Pull Wall Mount Flange |
| MS3132 | X-706 | QPL-81703 | 1 | Receptacle Push Pull Box Mount |
| MS3134 | X-706 | QPL-81703 | 1 | Receptacle Push Pull Jam Nut |
| MS3135 | ** | QPL-81703 | 1 | Dummy Receptacle |
| MS3137 | X-706 | QPL-81703 | 1 | Plug Straight Push Pull |
| MS3138 | X-706 | QPL-81703 | 1 | Plug Lanyard Push Pull |
| MS3139 | ** | QPL-81703 | 1 | Receptacle Thru-Bulkhead (Wall Mount) |
| * Consult Factory ** Connector Does Not Accommodate Rear Accessories ***Inactive For New Design | | | | |

Military Standard Connector Index



| Part No. | Connector Designator | Specification | Series | Description |
|--|----------------------|---------------|--------|--|
| MS3140 | X-706B | QPL-81703 | 2 | Receptacle Push Pull Wall Mount |
| MS3142 | ** | MIL-C-5015 | MS3100 | Receptacle Hermetic Box Mount (Solder) |
| MS3143 | ** | MIL-C-5015 | MS3100 | Receptacle Hermetic Solder Mount |
| MS3144 | X-706B | QPL-81703 | 2 | Receptacle Push Pull Jam Nut |
| MS3145 | ** | QPL-81703 | 3 | Receptacle Hermetic Push Pull Box Mount |
| MS3146 | ** | QPL-81703 | 3 | Receptacle Push Pull Hermetic Solder Mount |
| MS3147 | X-706B | QPL-81703 | 2 | Plug Push Pull (Crimp) |
| MS3148 | X-706B | QPL-81703 | 2 | Plug Push Pull Lanyard (Crimp) |
| MS3149 | ** | QPL-81703 | 3 | Receptacle Push Pull Hermetic (Single-Hole Mount) |
| MS3400 | A | MIL-C-5015 | MS3400 | Receptacle Wall Mount (Crimp) |
| MS3401 | A | SAE AS50151 | MS3400 | Receptacle Cable Connecting (Crimp) |
| MS3402 | ** | SAE AS50151 | MS3400 | Receptacle, Box Mount (Crimp) |
| MS3404 | A | SAE AS50151 | MS3400 | Receptacle Jam Nut (Crimp) |
| MS3406 | A | SAE AS50151 | MS3400 | Plug (Crimp) |
| MS3408 | A | SAE AS50151 | MS3400 | Plug 90° (Crimp) |
| MS3409 | A | SAE AS50151 | MS3400 | Plug 45° (Crimp) |
| MS3412 | A | SAE AS50151 | MS3400 | Receptacle Wall Mount (Crimp) |
| MS3424 | A | SAE AS81703 | 3 | Receptacle Push Pull Wall Mount |
| MS3440 | ** | MIL-DTL-26482 | 2 | Receptacle Narrow Flange Mount (Was M83723/9/10) |
| MS3442 | ** | MIL-DTL-26482 | 2 | Receptacle Wide Flange Mount |
| MS3443 | ** | MIL-DTL-26482 | 2 | Receptacle Solder Flange Mount |
| MS3445 | * | QPL-81703 | 2 | Plug Push Pull Rack & Panel Mount |
| MS3446 | A | QPL-81703 | 3 | Plug Push Pull Rack & Panel Mount |
| MS3449 | ** | MIL-DTL-26482 | 2 | Receptacle Push Pull Single Hole Mount |
| MS3450 | A | SAE AS50151 | MS3450 | Receptacle Wall Mount (Was M83723/19/20) (Crimp) |
| MS3451 | A | SAE AS50151 | MS3450 | Receptacle Cable Connecting (Was M83723/17/18) (Crimp) |
| MS3452 | ** | SAE AS50151 | MS3450 | Receptacle Box Mount (Was M83723/21/22) (Crimp) |
| MS3454 | A | SAE AS50151 | MS3450 | Receptacle Jam Nut (Crimp) |
| MS3456 | A | SAE AS50151 | MS3450 | Plug Straight (Was M83723/23/24) (Crimp) |
| MS3459 | A | SAE AS50151 | MS3450 | Plug Straight Self Locking (Was M83723/52/53) |
| MS3463 | ** | QPL-81703 | 3 | Receptacle Push Pull (Hermetic) |
| MS3464 | A | QPL-81703 | 3 | Receptacle Push Pull Jam Nut |
| MS3466 | ** | QPL-81703 | 3 | Receptacle Push Pull Hermetic (Box Mount) |
| MS3467 | A | QPL-81703 | 3 | Plug Push Pull |
| * Consult Factory ** Connector Does Not Accommodate Rear Accessories *** Inactive For New Design | | | | |



Military Standard Connector Index

A

| Part No. | Connector Designator | Specification | Series | Description |
|---|----------------------|---------------|---------|---|
| MS3468 | A | QPL-81703 | 3 | Plug Push Pull Lanyard |
| MS3469 | ** | QPL-81703 | 3 | Receptacle Push Pull Hermetic Jam Nut |
| MS3470 | A | MIL-DTL-26482 | 2 | Receptacle Narrow Flange Mount (Was M83723/1/2) |
| MS3471 | A | MIL-DTL-26482 | 2 | Receptacle Cable Connecting (Was M83723/7/8) |
| MS3472 | A | MIL-DTL-26482 | 2 | Receptacle Wide Flange Mount (Was M83723/3/4) |
| MS3473 | ** | MIL-DTL-26482 | 2 | Receptacle Solder Mount Hermetic |
| MS3474 | A | MIL-DTL-26482 | 2 | Receptacle Rear Mount Jam Nut (Was M83723/5/6) |
| MS3475 | A | MIL-DTL-26482 | 2 | Plug RFI Shielded (Was M83723/42/43) |
| MS3476 | A | MIL-DTL-26482 | 2 | Plug Straight (Was M83723/13/14) |
| MS3477 | ** | MIL-DTL-26482 | 2 | Receptacle Hermetic Box Mount |
| MS3479 | ** | MIL-DTL-26482 | 2 | Receptacle Hermetic Rear Mount Jam Nut |
| MS17343 | C | MIL-DTL-22992 | R | Receptacle Wall Mount |
| MS17344 | C | MIL-DTL-22992 | R | Plug Straight |
| MS17345 | C | MIL-DTL-22992 | R | Plug Cable Connecting (Female) |
| MS17346 | C | MIL-DTL-22992 | R | Receptacle Box Mount |
| MS17347 | C | MIL-DTL-22992 | R | Receptacle Jam Nut |
| MS17348 | ** | MIL-DTL-22992 | R | Receptacle Jam Nut Box Mount |
| MS18062 | ** | MIL-DTL-22992 | R | Dummy Receptacle |
| MS20026 | * | MIL-DTL-27599 | I | Receptacle Wall Mount Solder*** |
| MS20027 | * | MIL-DTL-27599 | I | Receptacle Line*** |
| MS20028 | * | MIL-DTL-27599 | I | Plug Straight*** |
| MS20029 | ** | MIL-DTL-27599 | I | Receptacle Jam Nut Mount*** |
| MS20030 | * | MIL-DTL-27599 | | Receptacle Box Mount Hermetic |
| MS20031 | ** | MIL-DTL-27599 | | Receptacle Jam Nut Hermetic*** |
| MS20032 | ** | MIL-DTL-27599 | | Receptacle Solder Mount Hermetic*** |
| MS20034 | * | MIL-DTL-27599 | | Receptacle Wall Mount*** |
| MS20035 | * | MIL-DTL-27599 | | Receptacle Box Mount*** |
| MS24264 | E | MIL-C-26500 | F G & R | Receptacle Flange Mount*** Use MIL-DTL-83723 |
| MS24265 | E | MIL-C-26500 | F G & R | Receptacle Single Hole Mount*** Use MIL-DTL-83723 |
| MS24266 | E | MIL-C-26500 | F G & R | Plug Straight*** Use MIL-DTL-83723 |
| MS25183 | ** | SAE AS50151 | MS3100 | Plug Potting Seal (Solder) |
| MS27034 | ** | MIL-C-26500 | | Receptacle Hermetic Solder Mount |
| MS27334 | * | MIL-DTL-27599 | | Receptacle Wall Mount *** |
| MS27335 | ** | MIL-DTL-27599 | | Receptacle Box Mount *** |
| * Consult Factory ** Connector Does Not Accommodate Rear Accessories ***Inactive For New Design | | | | |



Military Standard Connector Index

A

| Part No. | Connector Designator | Specification | Series | Description |
|---|----------------------|---------------|--------|--|
| MS27508 | ** | MIL-DTL-38999 | II | Receptacle Back Panel Box Mount |
| MS27513 | ** | MIL-DTL-38999 | II | Receptacle Box Mount |
| MS27515 | F | MIL-DTL-38999 | I | Inactive Use MS27656 |
| MS27613 | E-710 | MIL-DTL-26500 | | Receptacle Panel Mount ***Use MIL-DTL-83723 |
| MS27614 | E-710 | MIL-DTL-26500 | | Receptacle D-Hole Mount ***Use MIL-DTL-83723 |
| MS27615 | E-710 | MIL-DTL-26500 | | Plug Straight ***Use MIL-DTL-83723 |
| MS27652 | F | MIL-DTL-38999 | I | Inactive Use MS27466 |
| MS27653 | F | MIL-DTL-38999 | I | Inactive Use MS27467 |
| MS27654 | F | MIL-DTL-38999 | I | Inactive Use MS27656 |
| MS27656 | F | MIL-DTL-38999 | I | Receptacle Back Panel Wall Mount (MS27499) |
| MS27661 | F-752 | MIL-DTL-38999 | I | Plug Lanyard Release |
| MS27662 | ** | MIL-DTL-38999 | I | Receptacle Thru-Bulkhead |
| MS27664 | ** | MIL-DTL-38999 | II | Receptacle Back-Panel Wall Mount |
| MS27665 | F | MIL-DTL-38999 | I | Plug Rack & Panel Mount |
| MS27667 | ** | MIL-DTL-38999 | II | Receptacle Thru-Bulkhead |
| MS90555 | * | MIL-DTL-22992 | L | Receptacle Wall Mount |
| MS90556 | * | MIL-DTL-22992 | L | Plug Straight |
| MS90557 | * | MIL-DTL-22992 | L | Plug Cable Connecting |
| MS90558 | * | MIL-DTL-22992 | L | Receptacle W/Coupling Ring Wall Mount |
| M28840/10 | G | MIL-DTL-28840 | | Receptacle Wall Mount |
| M28840/11 | G | MIL-DTL-28840 | | Receptacle Cable Connecting |
| M28840/12 | ** | MIL-DTL-28840 | | Receptacle Box Mount |
| M28840/14 | G | MIL-DTL-28840 | | Receptacle Jam Nut |
| M28840/16 | G | MIL-DTL-28840 | | Plug Straight |
| D38999/20 | H | MIL-DTL-38999 | III | Receptacle Wall Mount |
| D38999/21 | ** | MIL-DTL-38999 | III | Receptacle Hermetic (Box Mount) |
| D38999/23 | ** | MIL-DTL-38999 | III | Receptacle Hermetic Jam Nut |
| D38999/24 | H | MIL-DTL-38999 | III | Receptacle Jam Nut |
| D38999/25 | ** | MIL-DTL-38999 | III | Receptacle Hermetic Solder Mount |
| D38999/26 | H | MIL-DTL-38999 | III | Plug Straight |
| D38999/27 | ** | MIL-DTL-38999 | III | Receptacle Hermetic Weld Mount |
| D38999/29 | H-701 | MIL-DTL-38999 | III | Plug Lanyard Release |
| D38999/30 | H-701 | MIL-DTL-38999 | III | Plug Lanyard Release |
| D38999/31 | H | MIL-DTL-38999 | III | Plug Lanyard Release |
| * Consult Factory ** Connector Does Not Accommodate Rear Accessories ***Inactive For New Design | | | | |

Military Standard Connector Index



| Part No. | Connector Designator | Specification | Series | Description |
|---|----------------------|---------------|--------|---|
| D38999/36 | H | MIL-DTL-38999 | III | Plug Lanyard Release |
| D38999/40 | H | MIL-DTL-38999 | IV | Receptacle Wall Mount |
| D38999/41 | ** | MIL-DTL-38999 | IV | Box Mount Receptacle Hermetic |
| D38999/42 | ** | MIL-DTL-38999 | IV | Receptacle Box Mount |
| D38999/43 | H | MIL-DTL-38999 | IV | Jam Nut Mount Hermetic Receptacle |
| D38999/44 | H-715 | MIL-DTL-38999 | IV | Receptacle Jam Nut |
| D38999/45 | ** | MIL-DTL-38999 | IV | Solder Mount Hermetic Receptacle |
| D38999/46 | H | MIL-DTL-38999 | IV | Plug Straight EMI |
| D38999/47 | H | MIL-DTL-38999 | IV | Plug Straight |
| D38999/49 | H | MIL-DTL-38999 | IV | In Line Cable Receptacle |
| D38999/60 | H | MIL-DTL-38999 | III | Tight Tolerance Fiber Optic Plug |
| D38999/61 | H | MIL-DTL-38999 | III | Tight Tolerance Wall Mount Fiber Optic Receptacle |
| M81511/1 | J | MIL-C-81511 | 2 | Receptacle Flange Mount |
| M81511/2 | ** | MIL-C-81511 | 2 | Receptacle Solder Flange |
| M81511/3 | J | MIL-C-81511 | 2 | Receptacle Jam Nut |
| M81511/4 | ** | MIL-C-81511 | 2 | Receptacle Jam Nut *** |
| M81511/5 | J | MIL-C-81511 | 2 | Plug Cable Connecting *** |
| M81511/6 | J | MIL-C-81511 | 2 | Plug *** |
| M81511/21 | J | MIL-C-81511 | 1 | Receptacle Flange Mount *** |
| M81511/22 | ** | MIL-C-81511 | 1 | Receptacle Solder Flange Mount *** |
| M81511/23 | J | MIL-C-81511 | 1 | Receptacle Jam Nut *** |
| M81511/24 | ** | MIL-C-81511 | 1 | Receptacle Jam Nut *** |
| M81511/25 | J | MIL-C-81511 | 1 | Receptacle Cable Connecting *** |
| M81511/26 | J | MIL-C-81511 | 1 | Plug *** |
| M81511/27 | ** | MIL-C-81511 | 1 | Receptacle Thru-Bulkhead Jam Nut *** |
| M81511/28 | ** | MIL-C-81511 | 2 | Receptacle Thru-Bulkhead Single Hole Mount *** |
| M81511/31 | J | MIL-C-81511 | 2 | Receptacle Flange Mount *** |
| M81511/32 | J | MIL-C-81511 | 2 | Receptacle Jam Nut Mount *** |
| M81511/33 | J | MIL-C-81511 | 2 | Receptacle, Cable Connecting *** |
| M81511/34 | J | MIL-C-81511 | 2 | Plug *** |
| M81511/35 | J | MIL-C-81511 | 1 | Receptacle Flange Mount *** |
| M81511/36 | J | MIL-C-81511 | 1 | Receptacle Jam Nut *** |
| M81511/37 | J | MIL-C-81511 | 1 | Receptacle Cable Connecting *** |
| M81511/38 | J | MIL-C-81511 | 1 | Plug *** |
| * Consult Factory ** Connector Does Not Accommodate Rear Accessories ***Inactive For New Design | | | | |



Military Standard Connector Index

A

| Part No. | Connector Designator | Specification | Series | Description |
|--|----------------------|---------------|--------|------------------------------------|
| M81511/41 | J | MIL-C-81511 | 3 | Receptacle Flange Mount *** |
| M81511/42 | ** | MIL-C-81511 | 3 | Receptacle Solder Flange Mount *** |
| M81511/44 | ** | MIL-C-81511 | 3 | Receptacle Jam Nut *** |
| M81511/45 | J | MIL-C-81511 | 3 | Receptacle Cable Connecting *** |
| M81511/46 | J | MIL-C-81511 | 3 | Plug *** |
| M81511/47 | ** | MIL-C-81511 | 3 | Receptacle Solder Flange Mount *** |
| M81511/48 | ** | MIL-C-81511 | 3 | Receptacle Jam Nut *** |
| M81511/49 | J | MIL-C-81511 | 3 | Receptacle Jam Nut *** |
| M81511/50 | ** | MIL-C-81511 | 4 | Receptacle Jam Nut *** |
| M81511/51 | J | MIL-C-81511 | 4 | Receptacle Flange Mount *** |
| M81511/52 | ** | MIL-C-81511 | 4 | Receptacle Solder Flange Mount *** |
| M81511/53 | J | MIL-C-81511 | 4 | Receptacle Jam Nut *** |
| M81511/54 | ** | MIL-C-81511 | 4 | Receptacle Jam Nut *** |
| M81511/55 | J | MIL-C-81511 | 4 | Receptacle Cable Connecting *** |
| M81511/56 | J | MIL-C-81511 | 4 | Plug *** |
| M81511/57 | ** | MIL-C-81511 | 4 | Receptacle Solder Flange Mount *** |
| M81582/1 | * | MIL-C-81582 | | Receptacle Jam Nut Mount *** |
| M81582/2 | * | MIL-C-81582 | | Plug Lanyard Release *** |
| M83723/1 | A | MIL-DTL-83723 | I | Superseded By MS3470 |
| M83723/2 | A | MIL-DTL-83723 | I | Superseded By MS3470 |
| M83723/3 | A | MIL-DTL-83723 | I | Superseded By MS3472 |
| M83723/4 | A | MIL-DTL-83723 | I | Superseded By MS3472 |
| M83723/5 | A | MIL-DTL-83723 | I | Superseded By MS3474 |
| M83723/6 | A | MIL-DTL-83723 | I | Superseded By MS3474 |
| M83723/7 | A | MIL-DTL-83723 | I | Superseded By MS3471 |
| M83723/8 | A | MIL-DTL-83723 | I | Superseded By MS3471 |
| M83723/9 | ** | MIL-DTL-83723 | I | Superseded By MS3440 |
| M83723/10 | ** | MIL-DTL-83723 | I | Superseded By MS3442 |
| M83723/11 | ** | MIL-DTL-83723 | I | Superseded By MS3443 |
| M83723/12 | ** | MIL-DTL-83723 | I | Superseded By MS3443 |
| M83723/13 | A | MIL-DTL-83723 | I | Superseded By MS3476 |
| M83723/14 | A | MIL-DTL-83723 | I | Superseded By MS3476 |
| M83723/17 | K | MIL-DTL-83723 | II | Superseded By MS3451 *** |
| M83723/18 | K | MIL-DTL-83723 | II | Superseded By MS3451 *** |
| * Consult Factory ** Connector Does Not Accomodate Rear Accessories ***Inactive For New Design | | | | |

Military Standard Connector Index



| Part No. | Connector Designator | Specification | Series | Description |
|---|----------------------|---------------|--------|---|
| M83723/19 | K | MIL-DTL-83723 | II | Superseded By MS3450 *** |
| M83723/20 | K | MIL-DTL-83723 | II | Superseded By MS3450 *** |
| M83723/21 | ** | MIL-DTL-83723 | II | Superseded By MS3452 *** |
| M83723/22 | ** | MIL-DTL-83723 | II | Superseded By MS3452 *** |
| M83723/23 | K | MIL-DTL-83723 | II | Superseded By MS3456 *** |
| M83723/24 | K | MIL-DTL-83723 | II | Superseded By MS3456 *** |
| M83723/25 | ** | MIL-DTL-83723 | II | Superseded By MS3142 *** |
| M83723/26 | ** | MIL-DTL-83723 | II | Superseded By MS3143 *** |
| M83723/36 | A | MIL-DTL-83723 | I | Inactive For New Design |
| M83723/37 | A | MIL-DTL-83723 | I | Inactive For New Design |
| M83723/38 | A | MIL-DTL-83723 | I | Inactive For New Design |
| M83723/39 | A | MIL-DTL-83723 | I | Inactive For New Design |
| M83723/40 | A | MIL-DTL-83723 | I | Inactive For New Design |
| M83723/41 | A | MIL-DTL-83723 | I | Inactive For New Design |
| M83723/42 | A | MIL-DTL-83723 | I | Superseded By MS3475 |
| M83723/43 | A | MIL-DTL-83723 | I | Superseded By MS3475 |
| M83723/45 | ** | MIL-DTL-83723 | I | Superseded By MS3115 |
| M83723/48 | A | MIL-DTL-83723 | I | Inactive For New Design |
| M83723/49 | A | MIL-DTL-83723 | I | Inactive For New Design |
| M83723/52 | K | MIL-DTL-83723 | II | Superseded By MS3459 |
| M83723/53 | K | MIL-DTL-83723 | II | Superseded By MS3459 |
| M83723/66 | A | MIL-DTL-83723 | III | Plug Push Pull (Pin Contacts) |
| M83723/67 | A | MIL-DTL-83723 | III | Plug Push Pull (Socket Contacts) |
| M83723/68 | A | MIL-DTL-83723 | III | Plug Push Pull Lanyard (Pin Contacts) |
| M83723/69 | A | MIL-DTL-83723 | III | Plug Push Pull Lanyard (Socket Contacts) |
| M83723/71 | A | MIL-DTL-83723 | III | Receptacle Bayonet Flange Mount (Socket Contact) |
| M83723/72 | A | MIL-DTL-83723 | III | Receptacle Bayonet Flange Mount (Pin Contact) |
| M83723/73 | A | MIL-DTL-83723 | III | Receptacle Bayonet Single Hole Mount (Socket Contact) |
| M83723/74 | A | MIL-DTL-83723 | III | Receptacle Bayonet Single Mount (Pin Contact) |
| M83723/75 | A | MIL-DTL-83723 | III | Plug Bayonet (Socket Contact) |
| M83723/76 | A | MIL-DTL-83723 | III | Plug Bayonet (Pin Contact) |
| M83723/77 | A | MIL-DTL-83723 | III | Plug Bayonet RFI (Socket Contact) |
| M83723/78 | A | MIL-DTL-83723 | III | Plug Bayonet RFI (Pin Contact) |
| M83723/79 | ** | MIL-DTL-83723 | III | Receptacle Bayonet Flange Mount Hermetic |
| * Consult Factory ** Connector Does Not Accommodate Rear Accessories ***Inactive For New Design | | | | |



Military Standard Connector Index

A

| Part No. | Connector Designator | Specification | Series | Description |
|---|----------------------|---------------|--------|--|
| M83723/80 | ** | MIL-DTL-83723 | III | Receptacle Bayonet Solder Flange Mount Hermetic |
| M83723/81 | ** | MIL-DTL-83723 | III | Receptacle Bayonet Single Hole Mount Hermetic |
| M83723/82 | A | MIL-DTL-83723 | III | Receptacle Threaded Flange Mount (Socket Contact) |
| M83723/83 | A | MIL-DTL-83723 | III | Receptacle Threaded Flange Mount (Pin Contact) |
| M83723/84 | A | MIL-DTL-83723 | III | Receptacle Threaded Single Hole Mount (Socket Contact) |
| M83723/85 | A | MIL-DTL-83723 | III | Receptacle Threaded Single Hole Mount (Pin Contact) |
| M83723/86 | A | MIL-DTL-83723 | III | Plug Threaded (Socket Contact) |
| M83723/87 | A | MIL-DTL-83723 | III | Plug Threaded (Pin Contact) |
| M83723/88 | ** | MIL-DTL-83723 | III | Receptacle Threaded Flange Mount (Pin Contact) |
| M83723/89 | ** | MIL-DTL-83723 | III | Receptacle Threaded Single Hole Mount Hermetic |
| M83723/90 | ** | MIL-DTL-83723 | III | Receptacle Threaded Solder Flange Mount Hermetic |
| M83723/91 | A | MIL-DTL-83723 | III | Plug Threaded RFI (Socket Contact) |
| M83723/92 | A | MIL-DTL-83723 | III | Plug Threaded RFI (Pin Contact) |
| M83723/93 | ** | MIL-DTL-83723 | III | Receptacle Bayonet Solder Flange Mount Hermetic |
| M83723/94 | ** | MIL-DTL-83723 | III | Receptacle Bayonet Single Hole Mount Hermetic |
| M83723/95 | A | MIL-DTL-83723 | III | Plug Threaded (Socket Contact) Self Locking |
| M83723/96 | A | MIL-DTL-83723 | III | Plug Threaded (Pin Contact) Self Locking |
| M83723/97 | A | MIL-DTL-83723 | III | Plug Threaded RFI (Socket Contact) Self Locking |
| M83723/98 | A | MIL-DTL-83723 | III | Plug Threaded RFI (Pin Contact) Self Locking |
| Natc00 | H* | SSQ21635 | | Receptacle Flange |
| Natc06 | H* | SSQ21635 | | Plug |
| Natc07 | H* | SSQ21635 | | Receptacle Jam Nut |
| Natc09 | *** | SSQ21635 | | Receptacle Weld Mount |
| Natc77 | *** | SSQ21635 | | Receptacle Jam Nut Bulkhead Feed-Thru |
| Natc99 | *** | SSQ21635 | | Receptacle Weld Mount |
| Nbo | A | 40M39569 | | Receptacle Flange Mount |
| Nboh | ** | 40M39569 | | Receptacle Hermetic |
| Nb3h | ** | 40M39569 | | Receptacle Hermetic |
| Nb4 | A | 40M39569 | | Receptacle Flange Mount |
| Nb5h | ** | 40M39569 | | Thru-Bulkhead Hermetic |
| NB6 | A | 40M39569 | | Plug Straight |
| NB6G | A | 40M39569 | | Plug Straight,EMI |
| NB7 | A | 40M39569 | | Receptacle Jam Nut |
| NB7H | ** | 40M39569 | | Receptacle Hermetic |
| * Consult Factory ** Connector Does Not Accommodate Rear Accessories ***Inactive For New Design | | | | |

Military Standard Connector Index



Conduit
Introduction

A

| Part No. | Connector Designator | Specification | Series | Description |
|--|----------------------|---------------|--------|-------------------------|
| NB8H | ** | 40M39569 | | Receptacle Hermetic |
| NLSO | F | 40M38277 | | Receptacle Flange Mount |
| NLS3H | ** | 40M38277 | | Receptacle Hermetic |
| NLS6 | F | 40M38277 | | Plug Straight |
| NLS6G | F | 40M38277 | | Plug Straight EMI |
| NLS7 | F | 40M38277 | | Receptacle Jam Nut |
| NLS7H | ** | 40M38277 | | Receptacle Jam Nut |
| NZGL00 | H** | SSQ21635 | | Receptacle Flange |
| NZGL03 | *** | SSQ21635 | | Receptacle Lever |
| NZGL06 | H** | SSQ21635 | | Plug |
| NZGL07 | H** | SSQ21635 | | Receptacle Weld Mount |
| NZGL09 | *** | SSQ21635 | | Receptacle Weld Mount |
| NZGL66 | H** | SSQ21635 | | Plug |
| NZGL77 | *** | SSQ21635 | | Receptacle Jam Nut |
| NZGL99 | *** | SSQ21635 | | Receptacle Weld Mount |
| * Consult Factory ** Connector Does Not Accomodate Rear Accessories ***Inactive For New Design | | | | |