

Guardian system quick selection guide



121-193
Conduit with 2 braids and jacket,
p. 15



712-839
Metal connector
adapter, p. 16



710-859
Double-Y
transition, p. 28



140-200 Octagonal junction box, p. 50



Factory terminated
guardian assemblies,
p. 54-59

Part No.	Description	Page No.
Annular Conduit Cores and Accessory Materials		
120-144	Conduit in 3 materials, Slit and Non Slit	10
600-180	Wire Loom Tool	11
121-190	Conduit with Braid	12
121-191	Conduit with Braid and Jacket	13
121-192	Conduit with 2 Braids	14
121-193	Conduit with 2 Braids and Jacket	15
Guardian Fittings		
712-839	Metal Connector Adapter	16
712M*838	Metal Mighty Mouse Connector Adapter	18
712-852	Metal Bulkhead Feed-Thru Fitting	20
713-356	Composite Connector Adapter	22
713-376	Composite Bulkhead and Junction Box Feed-Thru Fitting	24
Guardian Transitions		
Direct Attachment		
710-858	Y Transition	26
710-859	Double-Y Transition	28
710-860	T Transition	30
710-861	Double-T Transition	32
With H Code Teeth		
713-351	Y Transition	34
713-352	Double-Y Transition	35
713-353	T Transition	36
713-354	Double-T Transition	37
Tools, Bands, Boots and Boxes		
TG69	Soft Jaw Pliers	39
TG70	Connector Strap Wrench	40
600-164	Utility Shear	41
	BAND-IT® Shield Termination System	42
	Environmental Shrink Boots	43-46
	Shrink Boot General Installation Guide	47-49
	Composite Junction Boxes	50-51
712-877	Composite Junction Box Adapter	52
Factory Terminated Assemblies		
	Factory Terminated Guardian Assemblies	54-59
	Turnkey Factory Crimp Assemblies	60