



Series 79 Micro-Crimp Mateable, Hermetic Connectors General Information

The High-Density, High Performance Hermetic Rectangular

MICROCRIMP®

Meet the newest member of Glenair's ultraminiature connector family, the Series 79 Micro-Crimp. Environmental versions of the Micro-Crimp feature crimp, rear-release size #23 contacts on .075 inch (1.9 mm) spacing, as well as size #12 and #16 power contacts in a range of hybrid layouts. Hermetic versions of these high contact density connectors also feature rugged construction for demanding applications and, of course glass-to-metal hermetic sealing for severe environmental and pressure differential operating conditions. Designed for use in vacuum chambers and other pressurized systems, Glenair Micro-Crimp Hermetic Connectors offer outstanding performance in a lightweight microminiature package. The basic mounting configuration, an O-Ring equipped rear panel mount design may be customized for unique application environments. Specials, including weld mount versions are also available

- Pin Receptacles
- Glass to Metal Seals
- 31 insert arrangements, from 5 to 102 contacts
- O-Ring Mount;
Jackposts Options
- Solder Cup, PC Tail, and Pre-Wired Connectors

L

Hermetic Micro-Crimp mateable, solutions available in 31 insert arrangements, from 5 to 102 contacts.

