



Product Description	Page
Introduction	Intro
Introducing the Glenair Power Connectors Series	A2
IRT Series Connectors - Rectangular Multi Pole Power Connector	
Intoduction	A4
Technical Characteristics	A5
Mating and Unmating System	A9
Available Configurations	A10
How to Order - Part Number Breakdown	A15
IRT Connectors - SIZE 01 - n.3 Contact Screw Mating	
Receptacle Shell Size 01 for Metallic Gland - <i>IRT01R31-PM / IRT01R31-SM</i>	A16
Plug Shell Size 01 for Metallic Gland - <i>IRT01P-31PM / IRT01P-31SM</i>	A18
Receptacle Shell Size 01 for Clamp with Strain Relief - <i>IRT01R-31PE / IRT01R-31SE</i>	A20
Plug Shell Size 01 for Clamp with Strain Relief - <i>IRT01P-31EM / IRT01P-31SE</i>	A22
Receptacle Shell Size 01 for Screen EMC Gland - <i>IRT01R-31PS / IRT01R-31SS</i>	A24
Plug Shell Size 01 for Screen EMC Gland - <i>IRT01P-31PS / IRT01P-31SS</i>	A26
IRT Connectors - SIZE 02 - n.4 Contact Screw Mating	
Receptacle Shell Size 02 for Metallic Gland - <i>IRT02R-41PM / IRT02R-41SM</i>	A28
Plug Shell Size 02 for Metallic Gland - <i>IRT02P-41PM / IRT02P-41SM</i>	A30
Receptacle Shell Size 02 for Clamp with Strain Relief - <i>IRT02R-41PE / IRT02R-41SE</i>	A32
Plug Shell Size 02 for Clamp with Strain Relief - <i>IRT02P-41PE / IRT02P-41SE</i>	A34
Receptacle Shell Size 02 for Screen EMC Gland - <i>IRT02R-41PS / IRT02R-41SS</i>	A36
Plug Shell Size 02 for Screen EMC Gland - <i>IRT02P-41PS / RT02P-41SS</i>	A38

IRT Connectors - SIZE 03 - n.4 Contact Screw Mating

Receptacle Shell Size 03 for Metallic Gland - <i>IRT03R-41PM / IRT03R-41SM</i>	A40
--	-----

Plug Shell Size 03 for Metallic Gland - <i>IRT03P-41PM / IRT03P-41SM</i>	A42
--	-----

Receptacle Shell Size 03 for Clamp with Strain Relief - <i>IRT03R-41PE / IRT03R-41SE</i>	A44
--	-----

Plug Shell Size 03 for Clamp with Strain Relief - <i>IRT03P-41PE / IRT03P-41SS</i>	A46
--	-----

Receptacle Shell Size 03 for Screen EMC Gland - <i>IRT03R-41PS / IRT03R-41SS</i>	A48
--	-----

Plug Shell Size 03 for Screen EMC Gland - <i>IRT03P-41PS / IRT03P-41SS0</i>	A50
---	-----

IRT Connectors - SIZE 04 - n.3 Contact Screw Mating

Receptacle Shell Size 04 for Metallic Gland - <i>IRT04R-34PM / IRT04R-34SM</i>	A52
--	-----

Plug Shell Size 04 for Metallic Gland - <i>IRT04P-34PM / IRT04P-34SM</i>	A54
--	-----

Receptacle Shell Size 04 for Clamp with Strain Relief - <i>IRT04R-34PE / IRT04R-34SE</i>	A56
--	-----

Plug Shell Size 04 for Clamp with Strain Relief - <i>IRT04P-34PE / IRT04P-34SE</i>	A58
--	-----

Receptacle Shell Size 04 for Screen EMC Gland - <i>IRT04R-34PS / IRT04R-34SS</i>	A60
--	-----

Plug Shell Size 04 for Screen EMC Gland - <i>IRT04P-34PS / IRT04P-34SS</i>	A62
--	-----

IRT Connectors - SIZE 05 - n.4 Contact Screw Mating

Receptacle Shell Size 05 for Metallic Gland - <i>IRT05R-45PM / IRT05R-45SM</i>	A64
--	-----

Plug Shell Size 05 for Metallic Gland - <i>IRT05P-45PM / IRT05P-45SM</i>	A66
--	-----

Receptacle Shell Size 05 for Clamp with Strain Relief - <i>IRT05R-45PE / IRT05R-45SE</i>	A68
--	-----

Plug Shell Size 05 for Clamp with Strain Relief - <i>IRT05P-45PE / IRT05P-45SE</i>	A70
--	-----

Receptacle Shell Size 05 for Screen EMC Gland - <i>IRT05R-45PS / IRT05R-45SS</i>	A72
--	-----

Plug Shell Size 05 for Screen EMC Gland - <i>IRT05P-45PS / IRT05P-45SS</i>	A74
--	-----

Wiring Instructions - Receptacle and Plug Connectors	A76
--	-----

IRT 6 Poles Series Connectors for Metal and Screen EMC Gland	A80
--	-----

Crimping Table and Tools	A82
--------------------------	-----

ITS 901 Series Connectors - Reverse Bayonet Single Pole Power Connector **Page**

Intoduction	B1
Technical Characteristics	B2
Available Configurations	B5
How to Order / Part Number Breakdown	B6
ITS 901 02 Front and Rear Mount Receptacle	B7
<i>ITS901 02 50-2P / ITS901 02 50-3P / ITS901 02 50-31P / ITS901 02 50-N31P</i>	B7
<i>ITS901 02 50-2S / ITS901 02 50-3S / ITS901 02 50-31S / ITS901 02 50-N31S</i>	B7
ITS 901 00 - 1 Front and Rear Mount Receptacle Connector for Single Wires Cable Clamp	B9
<i>ITS90100 50-2P1 / ITS90100 50-3P1 / ITS90100 50-31P1 / ITS90100 50-N31P1</i>	B9
<i>ITS90100 50-2S1 / ITS90100 50-3S1 / ITS90100 50-31S1 / ITS90100 50-N31S1</i>	B9
ITS 901 06 - 1 Straight Cylindrical Plug for Single Wires Cable Clamp	B11
<i>ITS90106 50-2P1 / ITS90106 50-3P1 / ITS90106 50-31P1 / ITS90106 50-N31P1</i>	B11
<i>ITS90106 50-2S1 / ITS90106 50-3S1 / ITS90106 50-31S1 / ITS90106 50-N31S1</i>	B11
ITS 901 06G - 1 Straight Plug with Rubber Recovered Coupling for Single Wires Cable Clamp	B13
<i>ITS90106G 50-2P1 / ITS90106G 50-3P1 / ITS90106G 50-31P1 / ITS90106G 50-N31P1</i>	B13
<i>ITS90106G 50-2S1 / ITS90106G 50-3S1 / ITS90106G 50-31S1 / ITS90106G 50-N31S1</i>	B13
ITS 901 00 - 2 Front and Rear Mount Receptacle for Jacketed Cable	B15
<i>ITS90100 50-2P2 / ITS90100 50-3P2 / ITS90100 50-31P2 / ITS90100 50-N31P2</i>	B15
<i>ITS90100 50-2S2 / ITS90100 50-3S2 / ITS90100 50-31S2 / ITS90100 50-N31S2</i>	B15
ITS 901 06 - 2 Straight Cylindrical Plug for Jacketed Cable	B17
<i>ITS90106 50-2P2 / ITS90106 50-3P2 / ITS90106 50-31P2 / ITS90106 50-N31P2</i>	B17
<i>ITS90106 50-2S2 / ITS90106 50-3S2 / ITS90106 50-31S2 / ITS90106 50-N31S2</i>	B17



ITS 901 06G - 2 Straight Plug with Rubber Recovered Coupling for Jacketed Cable	B19
<i>ITS90106G 50-2P2 / ITS90106G 50-3P2 / ITS90106G 50-31P2 / ITS90106G 50-N31P2</i>	B19
<i>ITS90106G 50-2S2 / ITS90106G 50-3S2 / ITS90106G 50-31S2 / ITS90106G 50-N31S2</i>	B19
ITS 901 00 - 3 Front and Rear Mount Receptacle for Single Wires and Conduit	B21
<i>ITS90100 50-2P3 / ITS90100 50-3P3 / ITS90100 50-31P3 / ITS90100 50-N31P3</i>	B21
<i>ITS90100 50-2S3 / ITS90100 50-3S3 / ITS90100 50-31S3 / ITS90100 50-N31S3</i>	B21
ITS 901 06 - 3 Straight Plug for Single Wires and Conduit for Single Wires and Conduit	B23
<i>ITS90106 50-2P3 / ITS90106 50-3P3 / ITS90106 50-31P3 / ITS90106 50-N31P3</i>	B23
<i>ITS90106 50-2S3 / ITS90106 50-3S3 / ITS90106 50-31S3 / ITS90106 50-N31S3</i>	B23
ITS 901 06G - 3 Straight Cylindrical Plug with Rubber Recovered Coupling	B25
<i>ITS90106 G50-2P3 / ITS90106 G50-3P3 / ITS90106 G50-31P3 / ITS90106 G50-N31P3</i>	B25
<i>ITS90106 G50-2S3 / ITS90106 G50-3S3 / ITS90106 G50-31S3 / ITS90106 G50-N31S3</i>	B25
Accessories - 979-02T F6 / 979-TM-B	B27
Accessories - TP 2 110 / SP 979-46 (Non Conductive) / 979 05-F6	B28
Assembly Instructions - Receptacle and Plug Connectors	B29
Panel Cut Out and Mounting Data / Crimping Table and Tools	B33
ITS 500 Series Connectors - Reverse Bayonet Single Pole Power Connector	Page
Intoduction	C1
Technical Characteristics	C2
Available Configurations	C5
How to Order / Part Number Breakdown	C6
Front Mount Receptacle for Jacketed Cables <i>ITS500 00 GA40P - ITS500 00 GA40S</i>	C7
Rear Mount Receptacle for Jacketed Cables <i>ITS500 030 GA40P / ITS500 030 GA40S</i>	C9
Straight Plug for Jacketed Cables <i>ITS500 06 GA40P / ITS500 06 GA40S</i>	C11



Front Mount Receptacle for Jacketed Cables and Rubber Conduit <i>ITS500 00 GB40P / ITS500 00 GB40S</i>	C13
Rear Mount Receptacle for Jacketed Cables and Rubber Conduit <i>ITS500 030 GB40P / ITS500 030 GB40S</i>	C15
Straight Cylindrical Plug for Jacketed Cables and Rubber Conduit <i>ITS500 06 GB40P / ITS500 06 GB40S</i>	C17
Front Mount Receptacle for Jacketed Cables and Plastic or Metallic Conduit <i>ITS500 00 GC40P / ITS500 00 GC40S</i>	C19
Rear Mount Receptacle for Jacketed Cables and Plastic or Metallic Conduit <i>ITS500 030 GC40P / ITS500 030 GC40S</i>	C21
Straight Cylindrical Plug for Plastic or Metallic Conduit <i>ITS500 06 GC40P / ITS500 06 GC40S</i>	C23
Accessories <i>ITB 06T - 40 F6 / ITB 02T - 40 F6 / 10-030FMB-40</i>	C25
Accessories <i>ITS 05 - 40 F6 / ITS 05 - 40 F6 / IT - 40460 - 40 (Non Cond.) and IT - 40460 - 40S (Cond.)</i>	C26
Panel Cut Out and Mounting Data / Crimping Table and Tools	C27
Assembly Instructions	C28

UJ Series Connectors - Revolutionary Connection System

Introducing the Power Joint System	D1
Connectors and Cables Assembly Procedure	D3
UJ Connectors - 2 and 3 Ways Supports	D5
Assembly Drawings and Dimensions	D6
UJ1 - How to Order / Part Number Breakdown	D7
UJ2 - How to Order / Part Number Breakdown	D9
Crimping Instructions and Tools	D11