

Rev.03 - 2/28/2006

TABLE A

CONTACT SIZE	A		B DIA		C DIA		D DIA		CONDUCTOR SIZE		MANUAL CRIMP TOOL	TURRET	PNEUMATIC CRIMP TOOL	PNEUMATIC CRIMP TOOL	LOCATOR	HYDRAULIC CRIMP TOOL	CRIMPING DIE	INSERTION TOOL	EXTRACTION TOOL
	CONTACT SIZE	A	B	C	D	AWG	mm ²	mm ²	mm ²										
10-375-20	20	24.30	1.00	1.30	1.93	0.5	24+20	M.105001	M.105026	M.105003									M.118251
10-40579	18	26.60	1.40	1.30	1.93	0.15+0.6	26+20	M.105001	M.105025	M.105003									M.118249
10-40553	16S	26.60	1.58	1.70	2.60	1+1.5	18+16	M.105007	M.105009	M.105003									M.118250
10-40553-12	16S	26.60	1.58	1.20	2.60	0.6	20	M.105007	M.105009	M.105003									M.118250
10-40553-13	16S	26.60	1.58	1.30	1.93	0.15+0.6	26+20	M.105007	M.105009	M.105003									M.118250
10-40553-15	16S	26.60	1.58	1.50	2.60	1	18	M.105007	M.105009	M.105003									M.118250
10-40553-20	16S	26.60	1.58	2.00	2.90	2	14	M.105007	M.105009	M.105003									M.118250
10-40553-26	16S	26.60	1.58	2.50	3.80	3	12	M.105007	M.105009	M.105003									M.118250
10-40557	16	31.75	1.58	1.70	2.60	1+1.5	18+16	M.105007	M.105009	M.105003									M.118250
10-40557-08	16	31.75	1.58	0.85	1.55	0.15+0.2	26+24	M.105007	M.105009	M.105003									M.118250
10-40557-12	16	31.75	1.58	1.20	2.60	0.6	20	M.105007	M.105009	M.105003									M.118250
10-40557-13	16	31.75	1.58	1.30	1.93	0.15+0.6	26+20	M.105007	M.105009	M.105003									M.118250
10-40557-15	16	31.75	1.58	1.50	2.60	1	18	M.105007	M.105009	M.105003									M.118250
10-40557-20	16	31.75	1.58	2.00	2.90	2	14	M.105007	M.105009	M.105003									M.118250
10-40557-26	16	31.75	1.58	2.50	3.80	3	12	M.105007	M.105009	M.105003									M.118250
10-40557-32	16	31.75	1.58	0.45	1.95	32+28		M.105007	M.105009	M.105003									M.118250
10-40561	12	37.65	2.38	2.40	3.90	3	12	M.105007	M.105009	M.105003									M.118250
10-40561-12	12	37.65	2.38	1.20	2.60	0.6	20	M.105007	M.105009	M.105003									M.118250
10-40561-15	12	37.65	2.38	1.50	3.40	1	18	M.105007	M.105009	M.105003									M.118250
10-40561-20	12	37.65	2.38	2.00	3.90	1+2	18+14	M.105007	M.105009	M.105003									M.118250
10-40561-22	12	37.65	2.38	2.10	3.90	2.5		M.105007	M.105009	M.105003									M.118250
10-40561-30M	12	37.65	2.38	3.00	4.80	4		M.105007	M.105009	M.105003									M.118250
10-40561-38	12	37.65	2.38	3.60	4.80	6		M.105007	M.105009	M.105003									M.118250
10-40792	8	40.70	3.60	4.50	6.90	9	8	M.105007	M.105009	M.105003									M.118260
10-40792-15	8	40.70	3.60	1.50	3.40	1	18	M.105007	M.105009	M.105003									M.118260
10-40792-18	8	40.70	3.60	1.80	3.80	1+2	18+14	M.105000	M.105012	M.105012									M.118260
10-40792-30	8	40.70	3.60	3.00	4.80	4		M.105000	M.105012	M.105012									M.118260
10-40792-38	8	40.70	3.60	3.60	6.80	6													M.118260
10-40792-50	8	40.70	3.60	5.00	6.80	10													M.118260
10-40792-58	8	40.70	3.60	5.80	7.80	13.2	6												M.118260
10-113474-4P	4	42.00	5.70	7.10	9.53	22	4												M.118270
10-113474-4P-22	4	42.00	5.70	2.20	3.80	2.5		M.105007											M.118270
10-113474-4P-25	4	42.00	5.70	7.80	9.50	25													M.118270
10-113474-4P-26	4	42.00	5.70	2.50	3.80	3		M.105007											M.118270
10-113474-4P-30	4	42.00	5.70	3.00	4.80	4													M.118270
10-113474-4P-35	4	42.00	5.70	9.00	14.35	35													M.118270
10-113474-4P-50	4	42.00	5.70	6.00	7.00	10													M.118270
10-113474-4P-62	4	42.00	5.70	6.20	9.53	16													M.118270
10-113474-1P	0	45.00	9.05	11.50	14.30	53	0												M.118280
10-113474-1P-107	0	45.00	9.05	10.70	14.35	50													M.118280
10-113474-1P-25	0	45.00	9.05	7.80	9.50	25													M.118280
10-113474-1P-35	0	45.00	9.05	9.00	14.35	35													M.118280
10-113474-1P-45	0	45.00	9.05	4.55	6.80	9	8												M.118280
10-113474-1P-50	0	45.00	9.05	5.00	7.00	10													M.118280
10-113474-1P-62	0	45.00	9.05	6.20	9.50	16													M.118280
10-113474-0P	40	63.00	12.69	16.5	20	107	40												M.118280

All contacts are available with the following platings: G10 (Flash Cu + 3+6µ Au), G117 (2µ Ni + 0.4+0.6µ Au)