



# HIGH VOLTAGE SUBSEA SeaKing™ Power connectors for underwater primary power junctions



Size 48, 4-way #8 HV contacts, 3kV, 50 amps/contact

## 700-106-48 SEAKING POWER, FLANGE OR BULKHEAD CONNECTOR RECEPTACLE (FCR OR BCR), SIZE 48, 4-WAY #8 HV CONTACTS\*

How to Order	
Sample Part Number	700-106 -48HV4 Z1 S N B
Series	700-106 = bulkhead or flange connector receptacle (BCR OR FCR)
Shell Size / Insert Arrangement	-48HV4 = shell size 48 / layout HV4
Shell Material	Z1 = SS super duplex TC = titanium
Contact Style	P = pins S = sockets
Polarization	N = normal, A, B, C; see key positions table at right
Mounting Option*	B = BCR option includes bulkhead nut and washer F = FCR option and includes indexable mounting flange (fastener not included) N = None, receptacle is mountable to a threaded bulkhead
Shell Option*	API = test ports; omit for none

Key Positions		
Position	A	B
N	150°	210°
A	75°	210°
B	95°	230°
C	140°	275°

\*Mates only with 700-101 Cable Connector Plug

