


940-014 High-Pressure Environmental Sav-Con® Connector Saver (Non Scoop-Proof)


How To Order							
Sample Part Number	940	-014	M	24	-61	S	N
Series No.	940						
Basic No.	014						
Finish Symbol	B, J, M, N, NF, T, Z1 See Table II						
Shell Size	10, 12, 14, 16, 18, 20, 22, 24 See Table III						
Insert Arrangement	See Table I						
Contact Style	P = Pins, Plug Side S = Sockets, Plug Side						
Alternate Key Position	N, 1, 2, 3 or 4						

Notes

1. Assembly identified with manufacturer's name and P/N, space permitting.
2. Glenair 940-014 connector saver is designed to mate with Glenair 220-06 series Geo-Marine® connectors. (Non-scoop-proof)
3. Material/finish:
 Barrel, shell, coupling nuts - see Table II.
 Contacts - copper alloy/gold plate.
 Insulators - high grade rigid dielectric/N.A.
 O-ring & seals - silicone/N.A.



other end - any
geomarine non
scoop proof recpt



Shell Size	Insert Arrangement Dash No	Contact Size and Quantity			
		22	20	16	12
10	-2				2
	-4		6		4
	-6				
	-13	13			
12	-8		10		8
	-10				
	-22	22			
14	-12		19		12
	-19				
	--37	37			
16	-19		26		19
	-26				
	-55	55			
18	-11				11
	-22		32		22
	-32				
	-66	66			
20	30		41		30
	-41				
	-79	79			
22	-38				38
	-50	48	55		2
	-55				
	-85	85			
24	-24			16	16
	-48		61		48
	-61				
	-100	100			

Shell Size	A Thread	B Dia
10	.750-.1P-.1L	1.000 (25.40)
12	.875-.1P-.1L	1.125 (28.58)
14	1.000-.1P-.1L	1.250 (31.75)
16	1.125-.1P-.1L	1.375 (34.93)
18	1.250-.1P-.1L	1.594 (40.49)
20	1.375-.1P-.1L	1.719 (43.66)
22	1.500-.1P-.1L	1.894 (48.11)
24	1.625-.1P-.1L	1.969 (50.01)

Sym	Finish Description
B	Aluminum/Cadmium Plate/Olive Drab
J	Aluminum/Gold Iridite Over Cadmium Plate Over Nickel
M	Aluminum/Electroless Nickel
N	Aluminum/Cadmium Plate/Olive Drab Over Nickel
NF	Aluminum/Cad/O. D. Over Electroless Nickel (500 Hour Salt Spray)
T	Aluminum/Cadmium Plate/Bright Dip Over Nickel
Z1	Stainless Steel/Passivate Coupling Nut Nickel - Aluminum - Bronze/Degrease