




Series 22 Geo-Marine® Connectors Insert Arrangements

Geo-Marine® Contact Arrangements

Front Face of Pin Inserts Illustrated. Service Ratings Indicated in Parentheses.



10-2 (I)



10-4 (I)




10-6 (I)




10-13 (M)




12-8 (I)




12-10 (I)




12-22 (M)




14-4 (I)




14-12 (II)




14-19 (I)




14-37 (M)



16-6 (I)




16-19 (II)




16-26 (I)




16-55 (M)




18-8 (I)




18-22 (II)




18-32 (I)




18-66 (M)




20-11 (I)



20-30 (II)




20-38 (I)




20-41 (I)




20-79 (M)




22-19 (I)




22-38 (II)




22-55 (I)




22-85 (M)




24-48 (I)



24-61 (I)



24-100 (M)



24-128 (M)

H

Metric dimensions (mm) are indicated in parentheses