

IPT-SE CRIMP TOOLS - PIN AND SOCKET CONTACTS

	Type of contact	Conductor Size		MANUAL TOOL		*PNEUMATIC TOOL TYPE "A"		TURRET		INSERTION TOOL		EXTRACTION TOOL	
		mm ²	AWG										
10-314980-20P	20	0,2-0,5	20 22 24	M. 105001	M22520.1.01 AF8 DMC	M. 105003	WA27F DMC	M. 105011 (or M.105008)	M22520/1.02 DMC TH1A (or VH441 DMC)	M. 117349	GLENAIR IT TOOL	M. 118290	GLENAIR IT TOOL
10-314980-20S	20	0,2-0,5	20 22 24	M. 105001	M22520.1.01 AF8 DMC	M. 105003	WA27F DMC	M. 105011 (or M.105008)	M22520/1.02 DMC TH1A (or VH441 DMC)	M. 117349	GLENAIR IT TOOL	M. 118290	GLENAIR IT TOOL
10-314980-16S	16	0,5 ±1	16 18 20	M. 105001	M22520.1.01 AF8 DMC	M. 105003	WA27F DMC	M. 105011 (or M.105008)	M22520/1.02 DMC TH1A (or VH441 DMC)	M. 117350	GLENAIR IT TOOL	M. 118291	GLENAIR IT TOOL
10-314980-16P	16	0,5 ±1	16 18 20	M. 105001	M22520.1.01 AF8 DMC	M. 105003	WA27F DMC	M. 105011 (or M.105008)	M22520/1.02 DMC TH1A (or VH441 DMC)	M. 117350	GLENAIR IT TOOL	M. 118291	GLENAIR IT TOOL

* Use together as alternative.

