



SERIES 800 UN THREAD MATING
Mighty Mouse Connectors and Cables
Connector Weights



Connector Weights			
Maximum Weight In Grams			
Layout	Cable Plug	Jam-nut Receptacle	
		Crimp Contacts	PCB Contacts
5-3P	3.6	2.5	2.5
5-3S	3.7	2.6	2.6
6-1P	4.3	3.2	3.2
6-1S	4.4	3.3	3.3
6-4P	4.8	3.7	3.9
6-4S	5.2	4.0	3.7
6-6P	4.9	3.8	4.2
6-6S	5.3	4.1	4
6-7P	4.8	3.6	3.7
6-7S	4.7	4.0	3.9
6-23P	4.3	3.1	3.2
6-23S	4.6	3.4	3.3
7-1P	5.7	4.7	4.4
7-1S	5.9	5.0	4.5
7-10P	6.9	5.7	5.1
7-10S	7.4	6.2	5.4
7-25P	5.6	4.6	4.3
7-25S	5.9	5	4.3
8-2P	7.4	6.2	6.2
8-2S	8.1	6.9	6.9
8-28P	7.6	6.4	6.8
8-28S	8.6	7.4	7.5
8-13P	6.7	5.5	5.5
8-13S	7.2	5.9	5.9
8-200P	7.7	6.5	6.5
8-200S	8.4	7.2	7.2
9-4P	8.7	7.4	6.7
9-4S	8.8	7.6	6.8
9-210P	8.5	7.2	6.2
9-210S	8.8	7.6	6.5
9-19P	10.5	9.2	7.7
9-19S	11.2	9.6	7.9
9-200P	8.3	6.8	6.2
9-200S	9.4	7.9	7.3
9-201P	8.4	6.9	6.3

Connector Weights			
Maximum Weight In Grams			
Layout	Cable Plug	Jam-nut Receptacle	
		Crimp Contacts	PCB Contacts
9-201S	9.5	8.0	7.4
10-2P	9.5	9.7	11.3
10-2S	10.8	11	12.8
10-5P	9.7	9.9	12.2
10-5S	11.1	11.3	13.6
10-26P	7.9	8.1	10.5
10-26S	8.6	8.4	9.9
10-200P	8.8	9.0	11.3
10-200S	10.3	10.6	12.8
10-201P	9.1	9.4	11.7
10-201S	10.7	10.9	13.2
10-202P	8.8	9.0	11.2
10-202S	10.2	10.5	12.8
12-2P	10.5	10.1	11.6
12-2S	10.6	10.2	11.7
12-3P	10.7	10.3	11.8
12-3S	10.8	10.5	11.9
12-7P	14.3	13.8	15.3
12-7S	16.9	16.5	17.9
12-37P	12.5	12.1	13.5
12-37S	16.1	13.6	14.9
12-200P	13.2	12.8	14.2
12-200S	15.5	15.1	16.5
12-201P	13.3	12.9	14.3
12-201S	15.7	15.3	16.7
12-220P	11.3	10.6	13.9
12-220S	12.2	11.7	14.2
12-202P	10.6	10.2	13
12-202S	11.1	10.6	12.9
12-203P	10.2	10.5	13.5
12-203S	11.4	10.9	13.4
12-204P	11	10.6	13.3
12-204S	11.5	11	13.4
12-205P	12.1	11.7	17.6
12-205S	12.5	12	18

SERIES 800 UN THREAD MATING