



SERIES 803 BAYONET-LOCK
Mighty Mouse Connectors and Cables
Plug and Receptacle Weights



Series 803 maximum Connector Weight in grams					
Contact Arr.	Cable Plug	J/N Recep Crimp	J/N Recep PCB	Flange Recep Crimp	Flange Recep PCB
5-3P	3.6	3.6	3.9	2.9	3.3
5-3S	3.7	3.7	4.0	3.1	3.4
6-1P	4.4	4.4	4.6	3.1	3.5
6-1S	4.5	4.5	4.7	3.2	3.6
6-4P	4.7	3.7	4.1	3.1	3.6
6-4S	4.7	4.0	4.2	3.2	3.7
6-6P	4.3	3.8	4.6	3.4	3.6
6-6S	4.5	4.1	4.7	3.6	3.7
6-7P	5.1	4.8	5.3	3.3	4.4
6-7S	5.1	5.1	5.5	3.6	4.4
7-1P	5.7	5.9	5.8	4.4	4.7
7-1S	5.9	6.2	5.9	4.7	5.1
7-10P	6.9	7.4	8.1	5.0	6.5
7-10S	7.4	7.8	8.4	5.4	6.6
7-25P	5.6	5.8	5.7	4.2	4.6
7-25S	5.9	6.2	5.8	4.7	5
8-2P	8.6	8.9	9.9	6.6	8.6
8-2S	9.4	9.7	10.7	7.4	9.4
8-13P	7.9	8.3	9.2	5.9	7.9
8-13S	8.7	8.9	9.7	6.6	8.1
8-28P	8.8	9.1	10.5	6.8	9.2
8-28S	9.9	10.2	11.3	7.9	10
8-200P	8.9	9.2	10.2	6.9	8.9
8-200S	9.6	9.9	10.9	6.9	9.6
9-4P	9.2	9.6	10.6	6.6	9.2
9-4S	9.6	9.9	10.9	6.9	9.6
9-19P	9.2	9.1	10.6	7.0	9.9
9-19S	10.2	10.1	11.2	8.1	10.2
9-200P	9.1	9.5	10.5	7.2	9.1
9-200S	10.2	10.6	11.6	8.3	10.2
9-201P	9.2	9.6	10.6	7.3	10.3
9-201S	9.8	10.1	11.7	8.4	10.3
9-210P	9	9.4	10.1	6.4	8.7
9-210S	9.6	9.9	10.7	6.9	9.3
10-2P	13.1	13.8	14.1	10.4	13
10-2S	14.5	15.1	16.7	11.7	14.5
10-5P	13.4	14.1	15.0	10.6	13.9
10-5S	14.9	15.5	17.5	12.0	15.3
10-26P	11.7	12.3	14.3	8.8	12.8
10-26S	13.4	13.6	15.1	10.1	13.1
10-200	12.5	13.2	15.2	9.7	13.0

Series 803 maximum Connector Weight in grams					
Contact Arr.	Cable Plug	J/N Recep Crimp	J/N Recep PCB	Flange Recep Crimp	Flange Recep PCB
10-200	14.0	14.6	16.6	11.1	14.4
10-201P	12.9	13.5	15.5	10.0	13.3
10-201S	14.4	15.1	17.1	11.6	14.9
10-202P	12.4	13.1	15.1	9.6	11.8
10-202S	14.0	14.6	16.6	11.1	14.4
12-2P	15.5	16.4	19.1	11.4	16.9
12-2S	17.2	18.0	20.8	13.1	18.6
12-3P	16.5	17.4	20.1	12.4	17.9
12-3S	18.3	19.1	21.9	14.2	19.7
12-7P	16.7	17.6	20.4	12.7	18.2
12-7S	19.4	20.2	23.0	15.3	20.8
12-37P	15.0	15.8	18.6	10.9	16.4
12-37S	16.6	17.5	19.6	12.4	16.7
12-200P	15.6	16.5	19.3	11.6	17.1
12-200S	17.9	18.8	21.6	13.9	19.4
12-201P	15.7	16.6	19.4	11.7	17.2
12-201S	18.2	19.0	21.8	14.1	19.6
12-202P	15.6	16.4	20.5	12.2	18.3
12-202S	17.6	18.4	22.1	14.2	19.9
12-203P	15.9	16.8	21	12.5	18.8
12-203S	17.9	18.7	22.5	14.5	20.3
12-204P	16	16.2	21	12.6	18.6
12-204S	18	18.8	22.5	14.6	20.3
12-205P	17.1	18	22.6	13.7	20.4
12-205S	19	19.8	24.5	15.6	22.3
12-220P	16.3	17.2	21.4	12.9	19.2
12-220S	18.7	19.5	23.3	15.3	21.1
14-5P	22.2	23.5	27.7	17.3	25.5
14-5S	24.8	26.1	29.3	19.8	25.1
14-12P	22.7	24	29.7	17.6	27.5
14-12S	25.4	26.7	30.9	20.4	26.7
14-204P	21	22.3	27.6	15.9	25.4
14-204S	24.1	25.4	28.7	19.1	24.5
14-205P	21.3	22.6	28.1	16.2	25.9
14-205S	24.4	25.7	29.1	19.4	24.9
14-206P	21.5	22.8	28.2	16.4	26
14-206S	24.6	25.9	29.4	19.6	25.2
14-207P	22.3	23.6	29.1	17.2	26.9
14-207S	25.3	26.6	30.6	20.3	26.4
14-235P	22.6	23.9	29.6	17.5	27.4
14-235S	26.3	27.6	31.3	21.3	27.1
14-55P	19.6	20.9	25.1	14.6	22.9
14-55S	22.6	23.9	27.1	17.6	23.9

SERIES 803 BAYONET-LOCK