



# SERIES 805 TRIPLE-START ACME THREAD Mighty Mouse Connectors and Cables



## Panel Cutout Dimensions and Polarization

### PANEL CUTOUT DIMENSIONS

Panel Cutout For Jam-Nut and Wall Mount Receptacles						
<p>-02 FLANGE -12 &amp; -22 FLANGE</p>			<p>-07 JAM NUT</p>			
Shell Size	Square Flange			Jam-Nut		
	G Bsc	Ø H	Ø R	N Flat	Ø P	
8	.660 (16.76)	.096 (2.44) .091 (2.31)	.515 (13.08)	.545 (13.84) .541 (13.74)	.572 (14.53) .567 (14.40)	
9	.723 (18.36)		.578 (14.68)	.671 (17.04) .667 (16.94)	.698 (17.73) .693 (17.60)	
10	.785 (19.94)		.640 (16.26)	.671 (17.04) .667 (16.94)	.698 (17.73) .693 (17.60)	
11	.848 (21.54)		.703 (17.86)	.731 (18.57) .727 (18.47)	.760 (19.30) .755 (19.18)	
12	.909 (23.09)		.765 (19.43)	.794 (20.17) .790 (20.07)	.822 (20.88) .817 (20.75)	
13	.973 (24.71)		.828 (21.03)	.851 (21.62) .847 (21.51)	.885 (22.48) .881 (22.38)	
15	1.058 (26.87)		.130 (3.30) .126 (3.20)	.953 (24.21)	.980 (24.89) .976 (24.79)	1.010 (25.65) 1.005 (25.53)
18	1.255 (31.88)			1.140 (28.96)	1.157 (29.39) 1.153 (29.29)	1.198 (30.43) 1.193 (30.30)
19	1.327 (33.71)			1.203 (30.56)	1.231 (31.27) 1.227 (31.17)	1.260 (32.00) 1.255 (31.88)
21	1.452 (36.88)			1.328 (33.73)	1.358 (34.49) 1.354 (34.39)	1.383 (35.13) 1.381 (35.08)
23	1.570 (39.88)	1.453 (36.91)		1.480 (37.59) 1.476 (37.49)	1.510 (38.35) 1.505 (38.23)	

### POLARIZATION

Plug Key Positions		
Position	A°	B°
Normal (A)	150°	210°
B	75°	210°
C	95°	230°
D	140°	275°
E	75°	275°
F	95°	210°

  

Receptacle Keyway Positions		
Position	A°	B°
A	150°	210°
B	75°	210°
C	95°	230°
D	140°	275°
E	75°	275°
F	95°	210°

SERIES 805 TRIPLE-START ACME THREAD