

MIL-DTL-28840

TOOLS · CONTACTS · CONNECTORS AND ACCESSORIES

NAVY QPL COMPONENT SELECTION GUIDE

 <p>Crimping Tools</p>		 <p>Insertion & Removal Tools</p>		 <p>Pin Contact</p>		 <p>Socket Contact</p>	
<p>M22520/34-01 Basic Crimp Tool M22520/34-02 Positioner M22520/35 Gage</p>		<p>M81969/33-01 Straight Insertion Tool M81969/33-02 Offset Insertion Tool M81969/34-01 Removal Tool</p>		<p>M39029/83 Standard Duty Electrical Pin Contact</p>		<p>M39029/84 Standard Duty Electrical Socket Contact</p>	
 <p>Environmental Backshells</p>		 <p>EMI/RFI Environmental Backshells</p>		 <p>Connector Sockets</p>		 <p>"E" Nuts</p>	
				 <p>Strain Reliefs</p>			
				<p>Non-Self-Locking</p>		<p>Non-Self-Locking</p>	
<p>M28840/6 B Straight M28840/9 B 45° M28840/8 B 90°</p>		<p>M28840/6 A Straight M28840/8 A 90° M28840/9 A 45°</p>		<p>600G005*</p>		<p>M28840/23</p>	
						<p>M28840/1 Straight M28840/3 45° M28840/2 90°</p>	
 <p>Dummy Stowage Receptacles</p>		 <p>Protective Plug Covers</p>		 <p>Protective Receptacle Covers</p>		 <p>Jam Nuts</p>	
						 <p>Mounting Flanges and Gaskets</p>	
						 <p>MIL-PRF-24758A Conduit Fittings</p>	
<p>M28840/7</p>		<p>M28840/15</p>		<p>M28840/13</p>		<p>MS3186</p>	
						<p>M28840/24 Gasket</p>	
						<p>M24758-14 Straight (M24758/14 Straight.)* M28840/5 Straight • M28840/25 90° • M28840/27 45° • M28840/30 Coupling</p>	

