













Selection guide

	Straight strain relief AS85049/118	page 12
	90° strain relief AS85049/120	page 13
	Straight strain relief AS85049/52	page 14
	90° strain relief AS85049/51	page 15
	Straight shrink boot adapter AS85049/60-1	page 16
	Straight shrink boot adapter AS85049/60-2G	page 17
	Straight crimp ring backshell and crimp ring AS85049/26-1 and MS3419	page 18
	Backshell Crimp Ring AS85049/26-2	page 19
	E-Nut (Self-Locking and Non-Self-Locking) AS85049/31, MS3416 and MIL-DTL-85723/15N	page 20
	90° Environmental Backshell AS85049/9 and MS3188B	page 21
	Straight EMI/RFI Environmental Backshell AS85049/10 and MS3437A	page 22
	Straight Environmental Backshell AS85049/11 and MS3437B	page 23