



Glenair Series ITS and ITS-RG MIL-DTL-5015 Type Reverse Bayonet Connectors Contact Arrangement Tables

A

Arrangement	Rating	Contact Number	Contact Size								
			4/0	0	4	8	12	16	16S	18	20
10SL-3	A	3							3		
10SL-4	A	2							2		
14S-1	A	3							3		
14S-2	I	4							4		
14S-5	I	5							5		
14S-6	I	6							6		
14S-7	A	3							3		
14S-9	A	2							2		
14S-07	I	7							7		
16S-1	A	7							7		
16S-4	D	2							2		
16S-5	A	3							3		
16S-8	A	5							5		
16-2	E	1				1					
16-7	A	3				1		2			
16-9	A	4					2	2			
16-10	A	3					3				
16-11	A	2					2				
16-12	A	1			1						
16-A10	I	10							10		
18-1	I	10						10			
18-3	D	2					2				
18-4	D	4						4			
18-5	D	3					2	1			
18-6	D	1			1						
18-06	A	6					4	2			
18-7	B	1				1					
18-8	A	8					1	7			
18-9	I	7					2	5			
18-10	A	4					4				
18-10S MT	A	4					4				
18-11	A	5					5				
18-12	A	6						6			
18-13	A	4				1	3				
18-16	C	1					1				
18-19	A	10						10			
18-20	A	5						5			
18-22	D	3						3			
18-30 (18-20x110°)	A	5						5			
20-2	D	1		1							
20-3	D	3					3				
20-4	D	4					4				
20-6	D	3						3			
20-7	A	8						8			
20-8	I	6				2		4			
20-9	A	8					1	7			
20-11	I	13						13			
20-14	A	5				2	3				
20-15	A	7					7				
20-16	A	9					2	7			
20-17	A	6					5	1			
20-18	A	9					3	6			
20-19	A	3				3					
20-21	A	9					1	8			
20-22	A	6				3		3			
20-23	A	2				2					
20-24	A	4				2		2			
20-A24	A	4				2		2			
20-25 (20-11x100°)	I	13						13			
20-27	A	14						14			
20-29	A	17						17			
20-30 (20-11x250°)	I	13						13			

Arrangement	Rating	Contact Number	Contact Size								
			4/0	0	4	8	12	16	18	20	
20-33	A	11								11	
20-A8	I	8					2			6	
20-A9	A	9						9			
20-A48	I	19								19	
20-B8	A	8						4	4		
22-1	D	2					2				
22-2	D	3					3				
22-4	A	4					2	2			
22-5	D	6							2	4	
22-7	E	1		1							
22-9	E	3						3			
22-10	E	4								4	
22-11	B	2								2	
22-12	D	5					2			3	
22-14	A	19								19	
22-15	A	6						5	1		
22-17	A	9						1	8		
22-18	A	8								8	
22-19	A	14								14	
22-20	A	9								9	
22-21	A	3		1						2	
22-22	A	4					4				
22-23	A	8						8			
22-27	A	9					1		8		
22-28	A	7						7			
22-34	D	5						3	2		
22-82	A	10					2		8		
22-A10	A	10								10	
22-A37	A	37									37
22-22S MT	A	4					4				
24-2	D	7						7			
24-3	A	7						2	5		
24-4	D	4		1					3		
24-5	A	16								16	
24-06	D	6					4		2		
24-6	A	8						8			
24-07	D	7						7			
24-7	A	16						2	14		
24-9	A	2				2					
24-10	A	7					7				
24-11	A	9					3	6			
24-12	A	5				2		3			
24-013	A	13						6	7		
24-19	A	12							12		
24-20	D	11						2	9		
24-22	D	4					4				
24-27	E	7							7		
24-28	I	24								24	
24-67	A	19							19		
24-A1	B	1		1							
24-A8	A	8						5	3		
24-A11	A	11						2	9		
24-A12	A	12					2		10		
24-A14	A	14					2		12		
24-A25	A	25							25		
24-A28	I	28							28		
24-A55*	I	55									55
24-G5	A	5						5			
28-1	A	9						3	6		
28-2	D	14							2	12	
28-3	E	3						3			
28-6	D	3					3				

* Only Crimp Contact Version

© 2015 Glenair, Inc.

U.S. CAGE Code 06324

Printed in Italy

GLENAIR, INC. • 1211 AIR WAY • GLENDALE, CA 91201-2497 • 818-247-6000 • FAX 818-500-9912

www.glenair.com

A-28

E-Mail: sales@glenair.com

Glenair Series ITS and ITS-RG MIL-DTL-5015 Type Reverse Bayonet Connectors Contact Arrangement Tables



Arrangement	Rating	Contact Number	Contact Size							
			4/0	0	4	8	12	16	18	20
28-09	A	9			4			5		
28-9	D	12					6	6		
28-10	A	7			2	2	3			
28-11	A	22					4	18		
28-12	A	26						26		
28-13 (28-12x100*)	A	26						26		
28-15	A	35						35		
28-16	A	20						20		
28-17	A	15						15		
28-18	I	12						12		
28-19	A	10					4	6		
28-20	A	14					10	4		
28-21	A	37						37		
28-22	D	6			3			3		
28-51	D	12						12		
28-59	A	17					7	10		
28-70	A	7				7				
28-72*	I	72								72
28-79	A	16				7		9		
28-84	A	9				9				
28-124	A	16				4		12		
28-A29	A	29				2		27		
28-A31*	A	31				6				25
28-A35	A	35						35		
28-A63	I	28					9	19		
28-B1	B	1		1						
28-B2	E	2				2				
32-1	D	5		2			3			
32-2	E	5			3			2		
32-3	D	9		1	2		2	4		
32-5	D	2		2						
32-6	A	23			2	3	2	16		
32-7	I	35					7	28		
32-8	A	30					6	24		
32-9	D	14			2			12		
32-013	D	13					13			
32-13	D	23					5	18		
32-15	D	8		2			6			
32-17	D	4			4					
32-22	A	54						54		
32-31	A	31						31		
32-59	A	42				2		40		
32-68	A	16			4			12		
32-689	A	9			3			6		
32-A5GM	A	5			5					
32-76	A	19					19			
32-79	D	5			4	1				
32-88	A	54						54		
32-A1*	A	1	1							
32-A3	E	3			3					
32-A8	A	8				8				
32-A25	A	25						25		
32-A27	A	27						10	17	
32-A28	A	28						28		
32-A30	A	30						10	20	
32-A40	A	40						40		
32-A48	I	48						48		
32-A55	A	55						55		
32-B22	A	22			2			20		
36-01*	C	1	1							
36-3	D	6		3				3		
36-4	A	3		3						
36-5	A	4		4						

Arrangement	Rating	Contact Number	Contact Size							
			4/0	0	4	8	12	16	18	20
36-6	A	6		2	4					
36-7	A	47						7	40	
36-8	A	47						1	46	
36-9	A	31			1	2		14	14	
36-10	A	48							48	
36-14	D	16					5	5	6	
36-15	A	35							35	
36-18 (36-9x100*)	A	31			1	2		14	14	
36-22	D	22						22		
36-35	A	36					4		32	
36-54=36-B39	A	39					8		31	
36-66	A	56						4	52	
36-74	A	44					1		43	
36-77	D	7				7				
36-A7	A	7		3	2			2		
36-A10	A	10			2	8				
36-A35	A	8		4					4	
36-A51	D	6		3	2				1	
36-A72	I	72						4	16	52
36-A99*	A	65							15	50
36-B61	E	6			2			4		
36-B78	D	14					12		2	
36-B90	D	1							n.1 Special Contact	
36-D78	D	14						10	4	
40-1	D	30							6	24
40-9	A	47					1	22	24	
40-10	A	29			4	9			16	
40-26	A	26					7	19		
40-31	D	31							31	
40-35	D	35							35	
40-47	A	47					1	22	24	
40-53	A	60							60	
40-56	A	85							85	
40-62	A	60							60	
40-63	A	61							61	
40-67	A	11			10				1	
40-100	A	100								100
40-150	I	150								150
40-951	A	51						25	26	
40-A3	A	5			3				2	
40-A4	A	6			4				2	
40-A5	A	5			3	1			1	
40-A5GM	A	5			5					
40-A6	B	6							6	
40-A8	E	8			4				4	
40-A9	A	9			3			6		
40-A10	D	8				4			4	
40-A14	A	14				8			6	
40-A20	D	20						2	18	
40-A24	D	24						8	16	
40-A38	A	38							38	
40-A51	A	31						15	16	
40-A55	A	5			5					
40-A56	A	85							85	
40-A62	A	62						2	60	
40-A65	A	65							65	
40-A70	A	70							70	
40-B4	E	4			4					
40-B19	A	19						19		
40-B25	A	29			4				25	
40-B37	A	37							37	
40-D4	C	4						4		
40-G4	E	4						4		

* Only Crimp Contact Version

© 2015 Glenair, Inc.

U.S. CAGE Code 06324

Printed in Italy