

8572-0008 QDC Patch Cord, SuperFly-to-Standard-USB 3.0 Plug



Standard USB connectors. Commercial grade. Save assembly time and cost with pre-wired SuperFly Datalink “Blue” assemblies for SuperSpeed USB. Available with Type A, Type B or μ B interfaces, these cordsets have a SuperFly QDC Octaxial connector on one end and a standard USB 3.0 connector on the other end.

SuperFly Connector Construction

- **Shell, backshell:** aluminum alloy or SST
- **Insulators:** high-grade rigid dielectric
- **Contacts:** copper alloy, 50 microinches gold over nickel plating
- **Grommet:** fluorosilicone
- **O-rings:** fluorosilicone
- **Shield sleeve, ferrule:** copper alloy, nickel plated
- **Cable:** commercial-grade shielded USB 3.0 with black LSZH jacket

Specifications

- **Operating temp.:** -0° to +80°C
- **Impedance:** 90 ohms
- **DWV:** 100 Vrms
- **Current Rating:** 1.5 A
- **IR:** 100 M Ω min.

SuperFly Connector Mating Face



How To Order SuperFly to USB 3.0 Plug Patchcord				
Sample Part Number	8572-0008	- M	-01	-24
Product	8572-0008 = Pre-wired SuperFly QDC Plug to Standard USB 3.0 Connector			
Shell Finish	M = Electroless Nickel (aluminum shell) MT = Nickel-PTFE (aluminum shell) ZR = Black Zinc-Nickel (aluminum shell) Z2 = Gold (aluminum shell) ZMT = Nickel-PTFE (stainless steel shell)			
Order Code Connector Types	01 = Plug connector to USB 3.0 Type A plug 02 = Receptacle connector to USB 3.0 Type A receptacle 03 = Receptacle connector to USB 3.0 Type B plug 04 = Receptacle connector to USB 3.0 Type μ B plug			
Overall Length	Length in Inches (12 inch minimum)			

