



# Accessories and Tools



## 889-006 Plug & 889-007 Receptacle Dust Covers for Series 881 Threaded Connectors



889-006

889-007

- Fungus-resistant neoprene per ASTM D 2000 BC610Z1
- Fits SuperFly plugs with threaded coupling
- Attach with ring or field terminate with loose crimp ferrule (-CF)
- Flexible, high strength 1/32 inch stainless steel lanyard with black nylon coating
- Stainless steel attachment ring
- Copper alloy crimp ferrule with non-reflective black chromate over zinc finish



889-006 cover fits all threaded coupling plugs



889-007 cover fits all threaded coupling receptacles

889-006 Neoprene cover fits 880-001P, 886-021P AND 886-022P plugs with threaded coupling. 889-007 fits 881-002R, 886-023R and 886-024R receptacles with threaded coupling. Protects connector from debris ingress. Flexible stainless steel lanyard is coated with abrasion-resistant black nylon. Supplied with lanyard and ring, or with loose crimp ferrule for field termination of lanyard. Field terminate by looping lanyard around cable, compress ferrule with flat nose pliers and remove excess lanyard. -55° to +120°C. Meets fungus resistance requirement of MIL-STD-810.

How To Order	
<b>Sample Part Number</b>	<b>889-006</b> -F G 4 -02 C
<b>Series</b>	<b>889-006</b> Rubber Cover for Threaded Plug <b>889-007</b> Rubber Cover for Threaded Receptacles
<b>Cover Size</b>	A thru L, See Dimensions Table
<b>Attachment Type</b>	<b>Omit</b> = No attachment <b>G</b> = Ø1/16 black nylon cord <b>S</b> = Ø1/32 black nylon coated SST wire rope
<b>Attachment Length</b>	Length in inches, ±.25 inches
<b>Termination Type</b>	See Attachment Termination table for code
<b>Cover Material</b>	<b>Omit</b> = Standard <b>C</b> = Conductive Neoprene blend (conductance = 100k ohms/sq. minimum)

889-006 Dimensions				
Dash no.	I.D.		O.D.	
	in	mm	in	mm
-A	.31	7.87	.55	13.97
-B	.33	8.38	.55	13.97
-C	.35	8.89	.60	15.24
-D	.37	9.40	.60	15.24
-E	.38	9.65	.65	16.51
-F	.40	10.16	.65	16.51
-G	.42	10.67	.65	16.51
-H	.46	11.68	.70	17.78
-J	.50	12.70	.75	19.05
-K	.52	13.21	.75	19.05
-L	.56	14.22	.80	20.32

889-007 Dimensions						
Dash no.	I.D. 1		I.D. 2		O.D.	
	in	mm	in	mm	in	mm
-A	.22	5.59	.28	7.11	.50	12.70
-B	.24	6.10	.30	7.62	.55	13.97
-C	.26	6.60	.32	8.13	.55	13.97
-D	.28	7.11	.34	8.64	.55	13.97
-E	.30	7.62	.36	9.14	.60	15.24
-F	.32	8.13	.38	9.65	.60	15.24
-G	.34	8.64	.40	10.16	.65	16.51
-H	.38	9.65	.44	11.18	.65	16.51
-J	.42	10.67	.48	12.19	.70	17.78
-K	.44	11.18	.50	12.70	.75	19.05
-L	.68	17.27	.54	13.72	.75	19.05



# Accessories and Tools



## 889-006 Plug & 889-007 Receptacle Dust Covers for Series 881 Threaded Connectors

Attachment Termination		
Termination Code	Description	Style
<b>Ø 1/16 Nylon Cord Lanyard (Style "G") Attachment:</b>		
-00	No Terminal	
-01 thru -08 See Table I	Lug Termination	
-SCS	Slip Crimp Sleeve <sup>2</sup>	 Provides "slip knot" adjustment may be crimped for permanent attachment
-WS	With Strap	
-60 Thru -160 See Table III	Solid Ring	
-CF	Crimp Ferrule <sup>3</sup>	Supplied loose for field termination of lanyard
<b>Ø 1/32 Stainless Steel Wire (Style "S") Attachment:</b>		
-00	No Terminal Lug	
-11 thru -15 See Table II	Lug Termination	
-60 thru -160 See Table III	Solid Ring	
-CF	Crimp Ferrule <sup>3</sup>	Supplied loose for field termination of lanyard

Table III: Solid Ring Attachment for SST Wire or Nylon Rope				
Dash No	Ø R ±.005		Ø T ±.005	
	In	mm	In	mm
-60	0.244	6.20	0.352	8.94
-65	0.264	6.71	0.372	9.45
-70	0.284	7.21	0.392	9.96
-75	0.304	7.72	0.412	10.46
-80	0.323	8.20	0.431	10.95
-85	0.343	8.71	0.451	11.46
-90	0.363	9.22	0.471	11.96
-95	0.382	9.70	0.490	12.45
-100	0.402	10.21	0.510	12.95
-105	0.422	10.72	0.530	13.46
-110	0.441	11.20	0.549	13.94
-115	0.461	11.71	0.569	14.45
-120	0.480	12.19	0.588	14.94
-125	0.500	12.70	0.608	15.44
-130	0.520	13.21	0.628	15.95
-135	0.540	13.72	0.648	16.46
-140	0.559	14.20	0.667	16.94
-145	0.579	14.71	0.687	17.45
-150	0.599	15.21	0.707	17.96
-155	0.619	15.72	0.727	18.47
-160	0.639	16.23	0.747	18.97

Table I: Lug Termination Attachment for Nylon Rope				
Dash No	Ø R ±.005		Ø T ±.005	
	In	mm	In	mm
-01	.098	2.49	.30	7.62
-02	.126	3.20	.30	7.62
-03	.140	3.56	.30	7.62
-04	.145	3.68	.30	7.62
-05	.156	3.96	.30	7.62
-06	.167	4.24	.30	7.62
-07	.188	4.78	.30	7.62
-08	.197	5.00	.30	7.62

Table II: Lug Termination Attachment for SST Wire Rope				
Dash No	Ø V ±.005		Ø W ±.005	
	In	mm	In	mm
-11	0.093	2.36	0.14	3.56
-12	0.119	3.02	0.20	5.08
-13	0.145	3.68	0.20	5.08
-14	0.167	4.24	0.25	6.35
-15	0.197	5.00	0.25	6.35

### NOTES

- Attachment to withstand 25 lb pull test
- Slip/crimp sleeve (SCS) - for Type G nylon cord only provides "slip knot" adjustment, may be crimped for permanent attachment
- Crimp ferrule (CF) - for Type S wire rope and G nylon cord  
Supplied loose for user termination