

## Military Standard Connector Index



How  
to Order

The following is a listing of circular connectors defined by US Military Specifications, cross-referenced to the applicable active or inactive part number series. The

symbols in the Connector Designator column are an essential element in Glenair's backshell part number developments.

PART NO.	CONN. DESIG.	SPECIFICATION	SERIES	DESCRIPTION
MS3100	B	MIL-C-5015	MS3100	Receptacle, Wall Mtg (Solder)
MS3101	B	MIL-C-5015	MS3100	Receptacle
MS3102	**	MIL-C-5015	MS3100	Receptacle, Box Mtg (Solder)
MS3103	**	MIL-C-5015	MS3100	Receptacle, Potting (Solder)
MS3105	**	MIL-C-5015	MS3100	Dummy Receptacle
MS3106	B	MIL-C-5015	MS3100	Plug, Straight (Solder)
MS3107	B	MIL-C-5015	MS3100	Plug, Quick Disconnect (Solder)
MS3108	B	MIL-C-5015	MS3100	Plug, 90° (Solder)
MS3110	D-729	MIL-C-26482	1	Receptacle, Wall Mtg
MS3111	D	MIL-C-26482	1	Plug, Cable Connecting
MS3112	**	MIL-C-26482	1	Receptacle, Box Mtg
MS3113	**	MIL-C-26482	1	Receptacle, Solder Mtg
MS3114	D-717	MIL-C-26482	1	Receptacle, Jam Nut
MS3115	**	MIL-C-26482	1-2	Dummy Receptacle
MS3116	D	MIL-C-26482	1	Plug, Straight
MS3119	**	MIL-C-26482	1	Receptacle, Thru-Bulkhead
MS3120	D	MIL-C-26482	1	Receptacle, Wall Mtg, (Crimp)
MS3121	D	MIL-C-26482	1	Plug, Straight (Crimp)
MS3122	**	MIL-C-26482	1	Receptacle, Box Mtg, (Crimp)
MS3124	D-717	MIL-C-26482	1	Receptacle, Rear Mtg, Jam Nut (Crimp)
MS3126	D	MIL-C-26482	1	Plug, Straight (Crimp)
MS3127	**	MIL-C-26482	1	Receptacle, Box Mtg (Crimp)
MS3128	D	MIL-C-26482	1	Receptacle, Wall Mtg (Crimp)
MS3130	*	MIL-C-81703	1	Receptacle, Push Pull, Wide Flange
MS3132	X-706	MIL-C-81703	1	Receptacle, Push Pull, Box Mtg
MS3134	X-706	MIL-C-81703	1	Receptacle, Push Pull, Jam Nut
MS3135	**	MIL-C-81703	1	Dummy Receptacle
MS3137	X-706	MIL-C-81703	1	Plug, Straight, Push Pull
MS3138	X-706	MIL-C-81703	1	Plug, Lanyard, Push Pull
MS3139	**	MIL-C-81703	1	Receptacle, Thru-Bulkhead
MS3140	X-706B	MIL-C-81703	2	Receptacle, Push Pull, Wall Mtg
MS3142	**	MIL-C-5015	MS3100	Receptacle, Hermetic, Box Mtg
MS3143	**	MIL-C-5015	MS3100	Receptacle, Hermetic, Solder Mtg
MS3144	X-706B	MIL-C-81703	2	Receptacle, Push Pull, Jam Nut
MS3145	**	MIL-C-81703	3	Receptacle, Hermetic, Push Pull, Box Mtg
MS3146	**	MIL-C-81703	3	Receptacle, Push Pull, Hermetic, Solder Mtg
MS3147	X-706B	MIL-C-81703	2	Plug, Push Pull (Crimp)
MS3148	X-706B	MIL-C-81703	2	Plug, Push Pull, Lanyard (Crimp)
MS3149	**	MIL-C-81703	3	Receptacle, Push Pull, Hermetic
MS3400	A	MIL-C-5015	MS3400	Receptacle, Wall Mtg
* Consult factory				
** Connector does not accommodate rear accessories				



## Military Standard Connector Index

PART NO.	CONN. DESIG.	SPECIFICATION	SERIES	DESCRIPTION
MS3401	A	MIL-C-5015	MS3400	Receptacle, Cable Connecting
MS3402	**	MIL-C-5015	MS3400	Receptacle, Box Mtg
MS3404	A	MIL-C-5015	MS3400	Receptacle, Jam Nut
MS3406	A	MIL-C-5015	MS3400	Plug
MS3408	A	MIL-C-5015	MS3400	Plug, 90°
MS3409	A	MIL-C-5015	MS3400	Plug, 45°
MS3412	A	MIL-C-5015	MS3400	Receptacle, Wall Mtg
MS3424	A	MIL-C-81703	3	Receptacle, Push Pull, Wall Mtg
MS3440	**	MIL-C-26482	2	Receptacle, Narrow Flange Mtg (was M83723/9/10)
MS3442	**	MIL-C-26482	2	Receptacle, Wide Flange Mtg
MS3443	**	MIL-C-26482	2	Receptacle, Solder Flange Mtg
MS3445	*	MIL-C-81703	2	Plug, Push Pull, Rack & Panel Mtg
MS3446	A	MIL-C-81703	3	Plug, Rack & Panel
MS3449	**	MIL-C-26482	2	Receptacle, Single Hole Mtg
MS3450	A	MIL-C-5015	MS3450	Receptacle, Wall Mtg (was M83723/19/20)
MS3451	A	MIL-C-5015	MS3450	Receptacle, Cable Connecting (was M83723/17/18)
MS3452	**	MIL-C-5015	MS3450	Receptacle, Box Mtg (was M83723/21/22)
MS3454	A	MIL-C-5015	MS3450	Receptacle, Jam Nut
MS3456	A	MIL-C-5015	MS3450	Plug, Straight (was M83723/23/24)
MS3459	A	MIL-C-5015	MS3450	Plug, Straight, Self Locking (was M83723/52/53)
MS3463	**	MIL-C-81703	3	Receptacle, Push Pull
MS3464	A	MIL-C-81703	3	Receptacle, Push Pull, Jam Nut
MS3466	**	MIL-C-81703	3	Receptacle, Push Pull, Hermetic
MS3467	A	MIL-C-81703	3	Plug, Push Pull
MS3468	A	MIL-C-81703	3	Plug, Push Pull, Lanyard
MS3469	**	MIL-C-81703	3	Receptacle, Push Pull, Hermetic, Jam Nut
MS3470	A	MIL-C-26482	2	Receptacle, Narrow Flange Mtg (was M83723/1/2)
MS3471	A	MIL-C-26482	2	Receptacle, Cable Connecting (was M83723/7/8)
MS3472	A	MIL-C-26482	2	Receptacle, Wide Flange Mtg (was M83723/3/4)
MS3473	**	MIL-C-26482	2	Receptacle, Solder Mtg, Hermetic
MS3474	A	MIL-C-26482	2	Receptacle, Rear Mtg, Jam Nut (was M83723/5/6)
MS3475	A	MIL-C-26482	2	Plug, RFI Shielded (was M83723/42/43)
MS3476	A	MIL-C-26482	2	Plug, Straight (was M83723/13/14)
MS3477	**	MIL-C-26482	2	Receptacle Hermetic, Box Mtg
MS3479	**	MIL-C-26482	2	Receptacle, Hermetic, Rear Mtg, Jam Nut
MS17343	C	MIL-C-22992	R	Receptacle, Wall Mtg
MS17344	C	MIL-C-22992	R	Plug, Straight
MS17345	C	MIL-C-22992	R	Plug, Cable Connecting
MS17346	C	MIL-C-22992	R	Receptacle, Box Mtg
MS17347	C	MIL-C-22992	R	Receptacle, Jam Nut
MS17348	**	MIL-C-22992	R	Receptacle, Jam Nut, Box Mtg
MS18062	**	MIL-C-22992	R	Dummy Receptacle
MS20026	*	MIL-C-27599		Receptacle, Wall Mtg, Solder
MS20027	*	MIL-C-27599		Receptacle, Line
MS20028	*	MIL-C-27599		Plug, Straight
MS20029	**	MIL-C-27599		Receptacle, Jam Nut Mtg
MS20030	*	MIL-C-27599		Receptacle, Box Mtg, Hermetic

\* Consult factory  
\*\* Connector does not accommodate rear accessories

## Military Standard Connector Index



How  
to Order

PART NO.	CONN. DESIG.	SPECIFICATION	SERIES	DESCRIPTION
MS20031	**	MIL-C-27599		Receptacle, Jam Nut, Hermetic
MS20032	**	MIL-C-27599		Receptacle, Solder Mtg, Hermetic
MS20034	*	MIL-C-27599		Receptacle, Wall Mtg
MS20035	*	MIL-C-27599		Receptacle, Box Mtg
MS24264	E	MIL-C-26500	F, G & R	Receptacle, Flange Mtg
MS24265	E	MIL-C-26500	F, G & R	Receptacle, Single Hole Mtg
MS24266	E	MIL-C-26500	F, G & R	Plug, Straight
MS25183	**	MIL-C-5015	MS3100	Plug, Potting Seal
MS27034	**	MIL-C-26500		Receptacle, Hermetic, Solder Mtg
MS27334	*	MIL-C-27599		Receptacle, Wall Mtg
MS27335	**	MIL-C-27599		Receptacle, Box Mtg
MS27336	*	MIL-C-27599		Plug, Straight
MS27337	*	MIL-C-27599		Receptacle, Jam Nut
MS27338	*	MIL-C-27599		Receptacle, Wall Mtg, Hermetic
MS27339	**	MIL-C-27599		Receptacle, Box Mtg, Hermetic
MS27340	**	MIL-C-27599		Receptacle, Jam Nut Mtg, Hermetic
MS27341	**	MIL-C-27599		Receptacle, Solder Mtg, Hermetic
MS27466	F	MIL-C-38999	I	Receptacle, Wall Mtg
MS27467	F	MIL-C-38999	I	Plug, Straight
MS27468	F	MIL-C-38999	I	Receptacle, Jam Nut
MS27469	**	MIL-C-38999	I	Receptacle, Wall Mtg, Hermetic
MS27470	**	MIL-C-38999	I	Receptacle, Jam Nut, Hermetic
MS27471	**	MIL-C-38999	I	Receptacle, Solder Mtg, Hermetic
MS27472	F	MIL-C-38999	II	Receptacle, Wall Mtg
MS27473	F	MIL-C-38999	II	Plug, Straight
MS27474	F	MIL-C-38999	II	Receptacle, Jam Nut
MS27475	F	MIL-C-38999	II	Receptacle, Wall Mtg
MS27476	**	MIL-C-38999	II	Receptacle, Box Mtg, Hermetic
MS27477	**	MIL-C-38999	II	Receptacle, Jam Nut, Hermetic
MS27478	**	MIL-C-38999	II	Receptacle, Solder Mtg, Hermetic
MS27479	F	MIL-C-38999	II	Inactive Use MS27472
MS27480	F	MIL-C-38999	II	Inactive Use MS27473
MS27481	F	MIL-C-38999	II	Inactive Use MS27474
MS27482	F	MIL-C-38999	II	Inactive Use MS27475
MS27483	**	MIL-C-38999	II	Inactive Use MS27477
MS27484P	**	MIL-C-38999	II	Plug, Straight
MS27484T	F	MIL-C-38999	II	Plug, Straight
MS27496	**	MIL-C-38999	I	Receptacle, Box Mtg
MS27497	F	MIL-C-38999	II	Receptacle, Back Panel Wall Mtg
MS27498	F	MIL-C-38999	I	Plug, 90°
MS27499	**	MIL-C-38999	II	Receptacle, Box Mtg
MS27500	F	MIL-C-38999	II	Inactive See MS27473
MS27503	**	MIL-C-38999	II	Inactive See MS27478
MS27504	**	MIL-C-38999	II	Inactive See MS27499
MS27505	**	MIL-C-38999	I	Receptacle, Back Panel Box Mtg
MS27508	**	MIL-C-38999	II	Receptacle, Back Panel Box Mtg
MS27513	**	MIL-C-38999	II	Receptacle, Box Mtg

\* Consult factory  
 \*\* Connector does not accommodate rear accessories



## Military Standard Connector Index

PART NO.	CONN. DESIG.	SPECIFICATION	SERIES	DESCRIPTION
MS27515	F	MIL-C-38999	I	Inactive Use MS27656
MS27613	E-710	MIL-C-26500K		Receptacle, Panel Mtg
MS27614	E-710	MIL-C-26500K		Receptacle, D-Hole Mtg
MS27615	E-710	MIL-C-26500K		Plug, Straight
MS27652	F	MIL-C-38999	I	Inactive Use MS27466
MS27653	F	MIL-C-38999	I	Inactive Use MS27467
MS27654	F	MIL-C-38999	I	Inactive Use MS27656
MS27656	F	MIL-C-38999	I	Receptacle, Back Panel, Wall Mtg
MS27661	F-752	MIL-C-38999	I	Plug, Lanyard Release
MS27662	**	MIL-C-38999	I	Receptacle, Thru-Bulkhead
MS27664	**	MIL-C-38999	II	Receptacle, Back-Panel Wall Mtg
MS27665	F	MIL-C-38999	I	Plug, Rack & Panel Mtg
MS27667	**	MIL-C-38999	II	Receptacle, Thru-Bulkhead
MS90555	*	MIL-C-22992	L	Receptacle, Wall Mtg
MS90556	*	MIL-C-22992	L	Plug, Straight
MS90557	*	MIL-C-22992	L	Plug, Cable Connecting
MS90558	*	MIL-C-22992	L	Receptacle, W/Coupling Ring, Wall Mtg
M28840/10	G	MIL-C-28840		Receptacle, Wall Mtg
M28840/11	G	MIL-C-28840		Receptacle, Cable Connecting
M28840/12	**	MIL-C-28840		Receptacle, Box Mtg
M28840/14	G	MIL-C-28840		Receptacle, Jam Nut
M28840/16	G	MIL-C-28840		Plug, Straight
D38999/20	H	MIL-C-38999	III	Receptacle, Wall Mtg
D38999/21	**	MIL-C-38999	III	Receptacle, Hermetic
D38999/23	**	MIL-C-38999	III	Receptacle, Hermetic, Jam Nut
D38999/24	H	MIL-C-38999	III	Receptacle, Jam Nut
D38999/25	**	MIL-C-38999	III	Receptacle, Hermetic, Solder Mtg
D38999/26	H	MIL-C-38999	III	Plug, Straight
D38999/27	**	MIL-C-38999	III	Receptacle, Hermetic, Weld Mtg
D38999/29	H-701	MIL-C-38999	III	Plug, Lanyard Release
D38999/30	H-701	MIL-C-38999	III	Plug, Lanyard Release
D38999/40	H	MIL-C-38999	IV	Receptacle, Wall Mtg
D38999/42	H	MIL-C-38999	IV	Receptacle, Box Mtg
D38999/44	H-715	MIL-C-38999	IV	Receptacle, Jam Nut
D38999/46	H	MIL-C-38999	IV	Plug, Straight, EMI
D38999/47	H	MIL-C-38999	IV	Plug, Straight
M81511/1	J	MIL-C-81511	2	Receptacle, Flange Mtg
M81511/2	**	MIL-C-81511	2	Receptacle, Solder Flange
M81511/3	J	MIL-C-81511	2	Receptacle, Jam Nut
M81511/4	**	MIL-C-81511	2	Receptacle, Jam Nut
M81511/5	J	MIL-C-81511	2	Plug, Cable Connecting
M81511/6	J	MIL-C-81511	2	Plug
M81511/21	J	MIL-C-81511	1	Receptacle, Flange Mtg
M81511/22	**	MIL-C-81511	1	Receptacle, Solder Flange Mtg
M81511/23	J	MIL-C-81511	1	Receptacle, Jam Nut
M81511/24	**	MIL-C-81511	1	Receptacle, Jam Nut
M81511/25	J	MIL-C-81511	1	Receptacle, Cable Connecting
* Consult factory				
** Connector does not accommodate rear accessories				

# Military Standard Connector Index



How  
to Order

PART NO.	CONN. DESIG.	SPECIFICATION	SERIES	DESCRIPTION
M81511/26	J	MIL-C-81511	1	Plug
M81511/27	**	MIL-C-81511	1	Receptacle Thru-Bulkhead, Jam Nut
M81511/28	**	MIL-C-81511	2	Receptacle, Thru-Bulkhead, Single Hole Mtg
M81511/31	J	MIL-C-81511	2	Receptacle, Flange Mtg
M81511/32	J	MIL-C-81511	2	Receptacle, Jam Nut Mtg
M81511/33	J	MIL-C-81511	2	Receptacle, Cable Connecting
M81511/34	J	MIL-C-81511	2	Plug
M81511/35	J	MIL-C-81511	1	Receptacle, Flange Mtg
M81511/36	J	MIL-C-81511	1	Receptacle, Jam Nut
M81511/37	J	MIL-C-81511	1	Receptacle, Cable Connecting
M81511/38	J	MIL-C-81511	1	Plug
M81511/41	J	MIL-C-81511	3	Receptacle, Flange Mtg
M81511/42	**	MIL-C-81511	3	Receptacle, Solder Flange Mtg
M81511/44	**	MIL-C-81511	3	Receptacle, Jam Nut
M81511/45	J	MIL-C-81511	3	Receptacle, Cable Connecting
M81511/46	J	MIL-C-81511	3	Plug
M81511/47	**	MIL-C-81511	3	Receptacle, Solder Flange Mtg
M81511/48	**	MIL-C-81511	3	Receptacle, Jam Nut
M81511/49	J	MIL-C-81511	3	Receptacle, Jam Nut
M81511/50	**	MIL-C-81511	4	Receptacle, Jam Nut
M81511/51	J	MIL-C-81511	4	Receptacle, Flange Mtg
M81511/52	**	MIL-C-81511	4	Receptacle, Solder Flange Mtg
M81511/53	J	MIL-C-81511	4	Receptacle, Jam Nut
M81511/54	**	MIL-C-81511	4	Receptacle, Jam Nut
M81511/55	J	MIL-C-81511	4	Receptacle, Cable Connecting
M81511/56	J	MIL-C-81511	4	Plug
M81511/57	**	MIL-C-81511	4	Receptacle, Solder Flange Mtg
M81582/1	*	MIL-C-81582		Receptacle, Single Hole Mtg
M81582/2	*	MIL-C-81582		Plug, Lanyard Release
M83723/1	A	MIL-C-83723	I	Superseded by MS3470
M83723/2	A	MIL-C-83723	I	Superseded by MS3470
M83723/3	A	MIL-C-83723	I	Superseded by MS3472
M83723/4	A	MIL-C-83723	I	Superseded by MS3472
M83723/5	A	MIL-C-83723	I	Superseded by MS3474
M83723/6	A	MIL-C-83723	I	Superseded by MS3474
M83723/7	A	MIL-C-83723	I	Superseded by MS3471
M83723/8	A	MIL-C-83723	I	Superseded by MS3471
M83723/9	**	MIL-C-83723	I	Superseded by MS3440
M83723/10	**	MIL-C-83723	I	Superseded by MS3442
M83723/11	**	MIL-C-83723	I	Superseded by MS3443
M83723/12	**	MIL-C-83723	I	Superseded by MS3443
M83723/13	A	MIL-C-83723	I	Superseded by MS3476
M83723/14	A	MIL-C-83723	I	Superseded by MS3476
M83723/17	K	MIL-C-83723	II	Superseded by MS3451
M83723/18	K	MIL-C-83723	II	Superseded by MS3451
M83723/19	K	MIL-C-83723	II	Superseded by MS3450
M83723/20	K	MIL-C-83723	II	Superseded by MS3450

\* Consult factory  
 \*\* Connector does not accommodate rear accessories



## Military Standard Connector Index

PART NO.	CONN. DESIG.	SPECIFICATION	SERIES	DESCRIPTION
M83723/21	**	MIL-C-83723	II	Superseded by MS3452
M83723/22	**	MIL-C-83723	II	Superseded by MS3452
M83723/23	K	MIL-C-83723	II	Superseded by MS3456
M83723/24	K	MIL-C-83723	II	Superseded by MS3456
M83723/25	**	MIL-C-83723	II	Superseded by MS3142
M83723/26	**	MIL-C-83723	II	Superseded by MS3143
M83723/36	A	MIL-C-83723	I	Inactive For New Design
M83723/37	A	MIL-C-83723	I	Inactive For New Design
M83723/38	A	MIL-C-83723	I	Inactive For New Design
M83723/39	A	MIL-C-83723	I	Inactive For New Design
M83723/40	A	MIL-C-83723	I	Inactive For New Design
M83723/41	A	MIL-C-83723	I	Inactive For New Design
M83723/42	A	MIL-C-83723	I	Superseded by MS3475
M83723/43	A	MIL-C-83723	I	Superseded by MS3475
M83723/45	**	MIL-C-83723	I	Superseded by MS3115
M83723/48	A	MIL-C-83723	I	Inactive For New Design
M83723/49	A	MIL-C-83723	I	Inactive For New Design
M83723/52	K	MIL-C-83723	II	Superseded by MS3459
M83723/53	K	MIL-C-83723	II	Superseded by MS3459
M83723/66	A	MIL-C-83723	III	Plug, Push Pull (Pin Contacts)
M83723/67	A	MIL-C-83723	III	Plug, Push Pull (Socket Contacts)
M83723/68	A	MIL-C-83723	III	Plug, Push Pull Lanyard, (Pin Contacts)
M83723/69	A	MIL-C-83723	III	Plug, Push Pull, Lanyard, (Socket Contacts)
M83723/71	A	MIL-C-83723	III	Receptacle, Bayonet, Flange Mtg, (Socket Contact)
M83723/72	A	MIL-C-83723	III	Receptacle, Bayonet, Flange Mtg, (Pin Contact)
M83723/73	A	MIL-C-83723	III	Receptacle, Bayonet, Single Hole Mtg, (Socket Contact)
M83723/74	A	MIL-C-83723	III	Receptacle, Bayonet Single Mtg, (Pin Contact)
M83723/75	A	MIL-C-83723	III	Plug, Bayonet (Socket Contact)
M83723/76	A	MIL-C-83723	III	Plug, Bayonet (Pin Contact)
M83723/77	A	MIL-C-83723	III	Plug, Bayonet, RFI (Socket Contact)
M83723/78	A	MIL-C-83723	III	Plug, Bayonet, RFI (Pin Contact)
M83723/79	**	MIL-C-83723	III	Receptacle, Bayonet Flange Mtg, Hermetic
M83723/80	**	MIL-C-83723	III	Receptacle, Bayonet Solder Flange Mtg, Hermetic
M83723/81	**	MIL-C-83723	III	Receptacle, Bayonet Single Hole Mtg, Hermetic
M83723/82	A	MIL-C-83723	III	Receptacle, Threaded, Flange Mtg, (Socket Contact)
M83723/83	A	MIL-C-83723	III	Receptacle, Threaded, Flange Mtg, (Pin Contact)
M83723/84	A	MIL-C-83723	III	Receptacle, Threaded Single Hole Mtg, (Socket Contact)
M83723/85	A	MIL-C-83723	III	Receptacle, Threaded Single Hole Mtg, (Pin Contact)
M83723/86	A	MIL-C-83723	III	Plug, Threaded, (Socket Contact)
M83723/87	A	MIL-C-83723	III	Plug, Threaded, (Pin Contact)
M83723/88	**	MIL-C-83723	III	Receptacle, Threaded, Flange Mtg, (Pin Contact)
M83723/89	**	MIL-C-83723	III	Receptacle, Threaded, Single Hole Mtg, Hermetic
M83723/90	**	MIL-C-83723	III	Receptacle, Threaded, Solder Flange Mtg, Hermetic
M83723/91	A	MIL-C-83723	III	Plug, Threaded, RFI (Socket Contact)
M83723/92	A	MIL-C-83723	III	Plug, Threaded, RFI (Pin Contact)
M83723/93	**	MIL-C-83723	III	Receptacle, Bayonet, Solder Flange Mtg, Hermetic
M83723/94	**	MIL-C-83723	III	Receptacle, Bayonet, Single Hole Mtg, Hermetic

\* Consult factory  
\*\* Connector does not accommodate rear accessories

## Military Standard Connector Index



How  
to Order

PART NO.	CONN. DESIG.	SPECIFICATION	SERIES	DESCRIPTION
M83723/95	A	MIL-C-83723	III	Plug, Threaded, (Socket Contact), Self Locking
M83723/96	A	MIL-C-83723	III	Plug, Threaded, (Pin Contact), Self Locking
M83723/97	A	MIL-C-83723	III	Plug, Threaded, RFI (Socket Contact), Self Locking
M83723/98	A	MIL-C-83723	III	Plug, Threaded, RFI (Pin Contact), Self Locking
NATC00	H*	SSQ21635		Receptacle, Flange
NATC06	H*	SSQ21635		Plug
NATC07	H*	SSQ21635		Receptacle, Jam Nut
NATC09	***	SSQ21635		Receptacle, Weld Mtg
NATC77	***	SSQ21635		Receptacle, Jam Nut
NATC99	***	SSQ21635		Receptacle, Weld Mtg
NBO	A	40M39569		Receptacle, Flange Mtg
NBOH	**	40M39569		Receptacle, Hermetic
NB3H	**	40M39569		Receptacle, Hermetic
NB4	A	40M39569		Receptacle, Flange Mtg
NB5H	**	40M39569		Thru-Bulkhead, Hermetic
NB6	A	40M39569		Plug, Straight
NB6G	A	40M39569		Plug, Straight, EMI
NB7	A	40M39569		Receptacle, Jam Nut
NB7H	**	40M39569		Receptacle, Hermetic
NB8H	**	40M39569		Receptacle, Hermetic
NLSO	F	40M38277		Receptacle, Flange Mtg
NLS3H	**	40M38277		Receptacle, Hermetic
NLS6	F	40M38277		Plug, Straight
NLS6G	F	40M38277		Plug, Straight, EMI
NLS7	F	40M38277		Receptacle, Jam Nut
NLS7H	**	40M38277		Receptacle, Jam Nut
NZGL00	H**	SSQ21635		Receptacle, Flange
NZGL03	***	SSQ21635		Receptacle, Lever
NZGL06	H**	SSQ21635		Plug
NZGL07	H**	SSQ21635		Receptacle, Weld Mtg
NZGL09	***	SSQ21635		Receptacle, Weld Mtg
NZGL66	H**	SSQ21635		Plug
NZGL77	***	SSQ21635		Receptacle, Jam Nut
NZGL99	***	SSQ21635		Receptacle, Weld Mtg
* Consult factory				
** Connector does not accommodate rear accessories				
H* NATC Series size 09 through 25 mates to Glenair Connector Designator H, consult factory for sizes 33 & 37				
H** NZGL Series requires special accessories manufactured by Glenair, consult factory				
*** Connector noted does not have accessory thread. (NZGL and NATC hermetic/control leakage classes.)				