

Part Number Index

Part Number		Page
AS85049/93	687-749 Composite Banding Split-Ring	D-5
102-051	PEEK Tubular Braid (Black) for Series 74 Convolved Tubing	D-4
103-026	Composite Light Weight Metal-Clad EMI/RFI Braided Shielding (100%)	D-2
103-027	75%/25% Blended Composite/Metal EMI/RFI Braided Shielding	D-3
107-044	EMI/RFI Nickel Plated Copper Knit Braid Material	A-55
120-100	Type A - Convolved Tubing Only - Series 74 Convolved Tubing	C-7
120-103	Type B - External Black Dacron® Braid - Series 74 Convolved Tubing	C-8
121-100	Type C - External Shield and Jacket - Series 74 Convolved Tubing	C-9
121-101	Type D - External Shield - Series 74 Convolved Tubing	C-10
121-102	Type E - Two External Shields - Series 74 Convolved Tubing	C-11
121-103	Type F - Jacket and Two External Shields - Series 74 Convolved Tubing	C-12
123-100	Type G - External Jacket - Series 74 Convolved Tubing	C-13
140-074	Ultra-Miniature Junction Box	E-16
140-100	Mini Junction Box	E-18
140-101	Small Junction Box	E-20
140-102	Medium Junction Box	E-22
140-103	Large Junction Box	E-24
140-104	Small Low-Profile Box	E-26
140-105	Medium Low-Profile Junction Box	E-28
140-106	Small Three-Legged Junction Box	E-30
140-107	Jumbo Junction Box	E-32
140-200	8 Port Octagonal Junction Box	E-34
140-203	12 Port Rectangular Junction Box	E-35
233-105-05	MIL-DTL-38999 Series III Type In-Line Receptacle	F-14
233-105-07	MIL-DTL-38999 Series III Type Jam Nut Receptacle	F-12
233-105-G6	MIL-DTL-38999 Series III Type Plug	F-16
233-105-XX	MIL-DTL-38999 Series III Type Wall Mount Receptacle w/ Round (D0), Slotted (00) and Tapped (T0) Holes	F-10
310-017	Shrink Boot Adapter with Direct Coupling - Straight	A-4
310-045	Shrink Boot Adapter with Rotatable Coupling Nut; Straight	A-2
311-019	Lamp Base EMI/RFI Shield Termination Backshell with Shrink Boot Porch - Straight, 45° and 90°	A-6
311-034	Lamp Base EMI/RFI Shield Termination Backshell - Straight and 90°	A-5
311-063	Lamp Base EMI/RFI Environmental Adapter with Shrink Boot Porch and Direct Coupling - Straight	A-8
319-064	Swing Arm Backshell with Shield Sock and Self-Locking Rotatable Coupling - Adjustable to Straight, 45° and 90°	A-12
319-120	EMI/RFI Backshell with Shield Sock and Self-Locking Rotatable Coupling - Straight Only	A-14
319-134	EMI/RFI Micro Banding Backshell Shield Sock with Shrink Boot Porch and Self Locking Rotatable Coupling	A-16
319-136	EMI/RFI Standard Banding Backshell Shield Sock with Shrink Boot Porch and Self Locking Rotatable Coupling	A-18
319-137	Shield Sock Strain Relief with Self Locking Rotatable Coupling - Straight, 45° and 90°	A-22
319-138	Wide Mouth Swing Arm Strain Relief with Shield Sock and Self Locking Rotatable Coupling - Straight, 45° and 90°	A-24
327-060	Extender Backshell with Self-Locking Rotatable Coupling - Straight, 45° and 90°	A-26
347-129	Shorting Cap Backshell with Lanyard Attachment and Self Locking Rotatable Coupling	A-28
360-014	Non-Environmental Backshell with Self Locking Rotatable Coupling and Strain Relief - Straight and 90°	A-32
360-015	Non-Environmental Backshell with Self Locking Rotatable Coupling and Qwik-Clamp - Straight, 45° and 90°	A-34
370-016	Cable Sealing and Environmental Backshell with Self Locking Rotatable Coupling and Strain Relief Clamp or Nut	A-38
370-017	Cable Sealing and Environmental Backshell with Self Locking Rotatable Coupling and Qwik-Clamp or Nut	A-40
377-040	Fiber Optic Strain Relief Backshell with Fiber Alignment Grommet and Optional Banding adapter or Nut	A-42
377-041	Fiber Optic Conduit Backshell Adapter with Self Locking Rotatable Coupling and Fiber Alignment Grommet	C-14
380-099	Cone and Ring Style Shield Termination Backshell with Self Locking Coupling Nut and Strain Relief	A-46
380-100	Cone and Ring Style EMI/RFI Backshell with Self Locking Rotatable Coupling and Qwik-Clamp	A-48
380-130	Knit Braid Style EMI/RFI Shield Termination Backshell with Qwik-Ty and Rotatable Coupling	A-52
380-131	Knit Braid Style EMI/RFI Shield Termination Backshell with Clamp and Rotatable Coupling	A-53
380-132	Knit Braid Style EMI/RFI O-Ring Equipped Shield Termination Backshell with Shrink Boot Adapter	A-54
387-083	Multi Shield Cone and Ring Style EMI/RFI Shield Termination Backshell with Strain Relief	A-58
390-052	Environmental Cone and Ring Style EMI/RFI Shield Termination Backshell with Strain Relief	A-62
440-087	Ultra Lightweight Banding Strain Relief with Rotatable Coupling	A-64
440-143	EMI/RFI Micro-Banding Backshell with Qwik-Ty Strain Relief, Shrink Boot Groove	A-68
440-144	EMI/RFI Micro-Banding Backshell with Shrink Boot Groove and Self Locking Rotatable Coupling	A-70
447-325	EMI/RFI Banding Backshell with Shrink Boot Groove and Self Locking Rotatable Coupling	A-72
447-326	EMI/RFI Micro-Banding Backshell with Shrink Boot Groove and Self Locking Rotatable Coupling	A-74
447-327	EMI/RFI Banding Backshell with Qwik-Ty Strain Relief and Shrink Boot Groove	A-76

Part Number Index

Part Number		Page
447-328	EMI/RFI Band-in-a-Can Backshell with Strain Relief Clamp - Standard Profile Straight and 90°	A-78
447-329	EMI/RFI Environmental Band-in-a-Can Backshell with Strain Relief Clamp or Qwik-Clamp	A-80
447-330	EMI/RFI Non-Environmental Band-in-a-Can Backshell w/ Qwik-Clamp and Self-Locking Rotatable Coupling	A-82
447-331	EMI/RFI Dual Banding Backshell with Self Locking Rotatable Coupling - Straight and 90°	A-84
447-657	EMI/RFI Low Profile Micro Band-in-a-Can Backshell with Strain Relief Clamp	A-86
447-711	EMI/RFI Banding Backshell with Strain Relief - Standard Profile Straight and 90°	A-87
450-029	Qwik-Ty Strain Relief with Self Locking Rotatable Coupling - Straight, 45° and Low Profile 90°	A-88
450-030	Qwik-Ty Strain Relief with Ground Lug and Self Locking Rotatable Coupling	A-89
450-034	Ultra Lightweight Qwik-Ty Strain Relief with Free Rotating Coupling - Straight and Low Profile 90°	A-90
507-088	EMI/RFI Banding Backshell for MIL-DTL-83513 Micro-D Connectors - Top, 45° and Side Entry	A-92
557-186	EMI/RFI Banding Backshell for MIL-DTL-24308 D-Subminiature Connectors - Top, Side and End Entry	A-94
600-052	Standard Clamping Band	G-13
600-055	Calibration Key for Standard and Micro Hand Banding Tools	G-15
600-056	Cut-Off Blade for Standard Hand Banding Tools	G-14
600-057	Micro Clamping Band	G-13
600-058	Hand Banding Tool for Standard Bands	G-12
600-060	Cut-Off Blade for Micro Hand Banding Tools	G-14
600-061	Hand Banding Tool for Micro Bands	G-12
600-062	Cutter Knife for Standard Hand Banding Tools	G-14
600-072-1	Tension Gauge for Standard Hand Banding Tools	G-15
600-082	Cutter Knife for Micro Banding Tools	G-14
600-083	Micro Extended-Length Clamping Band	G-13
600-086-1	Tension Gauge for Micro Hand Banding Tools	G-15
600-090	Standard Extended-Length Clamping Band	G-13
600-091	Aluminum Hex-Coupling Wrench for Composite Backshells	G-6
600-157	Stainless Steel Hex-Coupling Wrench for Composite Backshells	G-7
600-161	Hand-Held Digital Torque Wrench with Dual 3/8" Drives	G-9
600-162	Bench Stand for 600-161 Digital Torque Wrench	G-9
600-164	Large Broad Blade Utility Shears	G-10
610-014	E Nut Backshell	A-96
620-042	Strain Relief Clamp with Self-Locking Rotatable Coupling - Straight, 45° and 90°	A-97
627-122	Swing Arm Strain Relief with Self Locking Rotatable Coupling Nut	A-98
627-142	Swing Arm Strain Relief with Keyed Banding Insert and Self Locking Rotatable Coupling Nut	A-100
630-030	EMI/RFI Environmental Thru-Box, Panel and Bulkhead Banding Adapter - Front or Rear Mount	E-36
630-031	Universal Environmental Thru-Box, Panel and Bulkhead Universal Adapter	E-38
637-094	EMI/RFI Environmental Bulkhead Feedthru Cable / Conduit Adapter	E-40
650-025	MIL-DTL-38999 Series III Dummy Stowage Receptacle	B-8
660-045 / 046	MIL-DTL-5015 Plug and Receptacle Covers	B-3
660-047 / 048	MIL-DTL-28840 Plug and Receptacle Covers	B-4
660-049 / 050	MIL-DTL-38999 Series III Plug and Receptacle Covers	B-5
660-051 / 052	MIL-DTL-83723 Series III Plug and Receptacle Covers	B-7
660-077 / 078	Glenair Series 190-015 / 016 Plug and Receptacle Covers	B-6
667-079	MIL-DTL-38999 Series III Receptacle Cover with Anti-Rotation Device	B-11
667-117	MIL-DTL-38999 Series III Receptacle Cover with Anti-Decoupling Device	B-9
667-118	MIL-DTL-5015 Receptacle Cover with Anti-Decoupling Device	B-10
687-305-22	Round Internal Mounting Plate for use with 140-106 Box	E-43
687-461	Hole Cap Assembly	E-45
687-466	Internal Mounting Plate for use with Rectangular Series Boxes	E-42
687-467	Slotted Terminal Block Mounting Rail	E-44
687-749	AS85049/93 Composite Banding Split-Ring	D-5
710-318	T Configuration Split Junction Fitting	C-16
710-319	Y Configuration Split Junction Fitting	C-17
710-320	Straight with 45° Branch Configuration Split Junction Fitting	C-18
710-321	Plus "+" Configuration Split Junction Fitting	C-19
712-419	Straight, 45° and 90° Conduit Connector Adapter for Glenair Series 74 Helical Convolved Tubing	C-24
712S269	Shrink Boot Conduit Fitting for Glenair Series 74 Helical Convolved Tubing	C-20
712S270	Single EMI/RFI Shield Termination Conduit Fitting for Glenair Series 74 Helical Convolved Tubing	C-21
712S271	Dual EMI/RFI Shield Termination Conduit Fitting for Glenair Series 74 Helical Convolved Tubing	C-22
770-001	Heat Moldable Shrink Boot - Straight and 90°	A-102