





Series 801 Mighty Mouse Double-Start ACME Threads Overmolded Cordset Dimensions



RIGHT ANGLE CORDSETS



How To Order Right Angle Cordsets

Insert the letter "R" after the End A or End B Connector letter designator.

Example

Straight cable 801-xxx-AC4Z16-4PA-72
Right Angle 801-xxx-ARC**R**4Z16-4PA-72

DIMENSIONS

Shell Size	A Max.		B Max.		C Max.		D Max.		E Max.	
	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.
5	2.2	55.88	0.6	15.24	1.5	38.1	0.6	15.24	1.9	48.26
6	2.2	55.88	0.6	15.24	1.5	38.1	0.6	15.24	1.9	48.26
7	2.2	55.88	0.7	17.78	1.5	38.1	0.7	17.78	2.1	53.34
8	2.3	58.42	0.75	19.05	1.6	40.64	0.75	19.05	2.2	55.88
9	2.6	66.04	0.85	21.59	1.9	48.26	0.85	21.59	2.4	60.96
10	2.6	66.04	0.85	21.59	1.9	48.26	0.85	21.59	2.4	60.96
13	2.9	73.66	1.1	27.94	2.2	55.88	1.1	27.94	2.9	73.66
16	3.2	81.28	1.3	33.02	2.5	63.5	1.3	33.02	3.3	83.82
17	3.7	93.98	1.4	35.56	3.0	76.2	1.4	35.56	3.5	88.90

Dimensions in Inches (millimeters) are subject to change without notice.