



### Mod Code Options

<p><b>Contacts</b></p> <p>Omitted for standard version ( . . . )</p> <p><b>B0</b> - Connector less contacts</p> <p><b>B1</b> - Connector with gold plated contacts</p> <p><b>Shells</b></p> <p>Omitted for standard version ( . . . )</p> <p><b>F2</b> - Connector with nickel plating (RoHS)</p> <p><b>F6</b> - Connector with black painting (RoHS)</p> <p><b>F7</b> - Connector with DEC conductive plating (RoHS)</p> <p><b>F8</b> - Connector with an olive drab passivation cadmium free</p> <p><b>MT</b> - Connector with Nickel-PTFE plating (RoHS)</p>	<p><b>Assembly with accessories</b></p> <p>Omitted for standard version ( . . . )</p> <p><b>N0</b> - Connector less backshell</p> <p><b>N1</b> - Connector with IT 3057 A cable clamp</p> <p><b>N2</b> - Connector with IT 393 backshell</p> <p><b>N4</b> - Connector with front O-Ring</p> <p><b>N5</b> - Connector with IT 3057 C cable clamp</p> <p><b>N12</b> - Connector with IT 3057 A cable clamp and neoprene sleeve IT 3420</p> <p><b>NXXX</b> - Special customer connector</p>
---	--