



Electrical Performance
Series ITH Rigid Insert Reverse Bayonet Connectors
Rated Current

Contact size	Rated current according to NFF61-030		Max. Contact resist.
	1 contact	A II contacts	
20	10 A	5 A	3.0 mΩ
16	15 A	8 A	2.5 mΩ
12	20 A	16 A	1.3 mΩ
8	25 A	25 A	0.9 mΩ

