




## Series 80 Mighty Mouse Contact Arrangements


### Mating Face View of Pin Connector (socket connector numbers are reversed)

**Contact Legend**  
#23◦ #20HD◦ #20● #16◐ #12⊕




Series 800, 801, 802, 803, 804	5-3	6-1	6-23	6-4	6-6	6-7	7-1	7-25
Series 805	Not Avail.	8-1	8-23	8-4	8-6	8-7	9-1	9-25
No. of Contacts	3	1	3	4	6	7	1	5
Contact Size	#23	#16	#20HD	#23	#23	#23	#12	#20HD
DWV Voltage (VAC)	500	1800	750	500	500	500	1800	750
Current Rating (Amps)	5	13	7.5	5	5	5	23	7.5

**Contact Legend**  
#23◦ #20HD◦ #20● #16◐ #12⊕




Series 800, 801, 802, 803, 804	7-10	8-2	8-200	8-28	8-13	9-4
Series 805	9-10	10-2	10-200	10-28	10-13	11-4
No. of Contacts	10	2	2 4	8	13	4
Contact Size	#23	#16	#20 #23	#20HD	#23	#16
DWV Voltage (VAC)	500	1800	1000 500	750	500	1800
Current Rating (Amps)	5	13	7 5	7.5	5	13

**Contact Legend**  
#23◦ #20HD◦ #20● #16◐ #12⊕



Series 800, 801, 802, 803, 804	9-200	9-201	9-210	9-19	10-2
Series 805	11-200	11-201	11-210	11-19	12-2
No. of Contacts	2 4	2 8	10	19	2
Contact Size	#16 #23	#20 #23	#20HD	#23	#12
DWV Voltage (VAC)	1800 500	1000 500	750	500	1800
Current Rating (Amps)	13 5	7.5 5	7.5	5	23

**Contact Legend**  
#23◦ #20HD◦ #20● #16◐ #12⊕



Series 800, 801, 802, 803, 804	10-5	10-201	10-202	10-200
Series 805	12-5	12-201	12-202	12-200
No. of Contacts	5	2 4	2 8	1 12
Contact Size	#16	#12 #23	#16 #23	#12 #23
DWV Voltage (VAC)	1800	1800 500	1800 500	1800 500
Current Rating (Amps)	13	23 5	13 5	23 5





# Series 80 Mighty Mouse Contact Arrangements



## Mating Face View of Pin Connector (socket connector numbers are reversed)

### Contact Legend





- #23 ○
- #20HD ●
- #20 ●
- #16 ●
- #12 ⊕



Series 800, 802, 803, 804	10-26	12-2	12-3	12-7
Series 801	10-26	13-2	13-3	13-7
Series 805	12-26	15-2	15-3	15-7
No. of Contacts	26	2	3	7
Contact Size	#23	#12	#12	#16
DWV Voltage (VAC)	500	1800	1800	1800
Current Rating (Amps)	5	23	23	13

### Contact Legend





- #23 ○
- #20HD ●
- #20 ●
- #16 ●
- #12 ⊕



Series 800, 802, 803, 804	12-200	12-201	12-220	12-37
Series 801	13-200	13-201	13-220	13-37
Series 805	15-200	15-201	15-220	15-37
No. of Contacts	2 6	2 10	20	37
Contact Size	#12 #23	#12 #23	#20HD	#23
DWV Voltage (VAC)	1800 500	1800 500	750	500
Current Rating (Amps)	23 5	23 5	7.5	5

### Contact Legend

- #23 ○
- #20HD ●
- #20 ●
- #16 ●
- #12 ⊕




Series 802, 803, 804	14-5	14-12	14-235	14-55
Series 801	16-5	16-12	16-235	16-55
Series 805	18-5	18-12	18-235	18-55
No. of Contacts	5	12	35	55
Contact Size	#12	#16	#20HD	#23
DWV Voltage (VAC)	1800	1800	750	500
Current Rating (Amps)	23	13	7.5	5



## Series 80 Mighty Mouse Contact Arrangements


**Mating Face View of Pin Connector (socket connector numbers are reversed)**

- Contact Legend**
- #23 ○
  - #20HD ●
  - #20 ●
  - #16 ●
  - #12 ⊕




Series 801	17-7	17-14	17-241
Series 802	15-7	15-14	15-241
Series 805	19-7	19-14	19-241
No. of Contacts	7	14	41
Contact Size	#12	#16	#20HD
DWV Voltage (VAC)	1800	1800	750
Current Rating (Amps)	23	13	7.5

- Contact Legend**
- #23 ○
  - #20HD ●
  - #20 ●
  - #16 ●
  - #12 ⊕



Series 801	17-85	21-12	21-22
Series 802	15-85	21-12	21-22
Series 805	19-85	23-12	23-22
No. of Contacts	85	12	22
Contact Size	#23	#12	#16
DWV Voltage (VAC)	500	1800	1800
Current Rating (Amps)	5	23	13

- Contact Legend**
- #23 ○
  - #20HD ●
  - #20 ●
  - #16 ●
  - #12 ⊕



Series 801, 802	21-269	21-130	
Series 805	23-269	23-130	
No. of Contacts	69	130	
Contact Size	#20HD	#23	
DWV Voltage (VAC)	750	500	
Current Rating (Amps)	7.5	5	