

Series 80 Mighty Mouse Contact Arrangement Table



Series 80 Mighty Mouse Contact Arrangement table

						Contact Arrangement					
Contact Size and Qty						Series 800	Series 801	Series 802	Series 803	Series 804	Series 805
#23	#20	#20HD	#16	#12							
Size #23 Contacts 5 Amp Max. Current 500 VAC #22-#28 AWG	3					5-3	5-3	5-3	5-3	5-3	Not Avail.
	4					6-4	6-4	6-4	6-4	6-4	8-4
	6					6-6	6-6	6-6	6-6	6-6	8-6
	7					6-7	6-7	6-7	6-7	6-7	8-7
	10					7-10	7-10	7-10	7-10	7-10	9-10
	13					8-13	8-13	8-13	8-13	8-13	10-13
	19					9-19	9-19	9-19	9-19	9-19	11-19
	26					10-26	10-26	10-26	10-26	10-26	12-26
	37					12-37	13-37	12-37	12-37	12-37	15-37
	55					Not Avail.	16-55	14-55	14-55	14-55	18-55
85					Not Avail.	17-85	15-85	Not Avail.	Not Avail.	19-85	
130					Not Avail.	21-130	21-130	Not Avail.	Not Avail.	23-130	
Size #20HD Contacts 7.5 Amp Max. Current 750 VAC #20-#24 AWG		3				6-23	6-23	6-23	6-23	6-23	8-23
		5				7-25	7-25	7-25	7-25	7-25	9-25
		8				8-28	8-28	8-28	8-28	8-28	10-28
		10				9-210	9-210	9-210	9-210	9-210	11-210
		20				12-220	13-220	12-220	12-220	12-220	15-220
		35				Not Avail.	16-235	14-235	14-235	14-235	18-235
		41				Not Avail.	17-241	15-241	Not Avail.	Not Avail.	19-241
	69				Not Avail.	21-269	21-269	Not Avail.	Not Avail.	23-269	
Size #16 Contacts 13 Amp Max. Current 1800 VAC #16-#20 AWG			1			6-1	6-1	6-1	6-1	6-1	8-1
			2			8-2	8-2	8-2	8-2	8-2	10-2
			4			9-4	9-4	9-4	9-4	9-4	11-4
			5			10-5	10-5	10-5	10-5	10-5	12-5
			7			12-7	13-7	12-7	12-7	12-7	15-7
			12			Not Avail.	16-12	14-12	14-12	14-12	18-12
			14			Not Avail.	17-14	15-14	Not Avail.	Not Avail.	19-14
			22			Not Avail.	21-22	21-22	Not Avail.	Not Avail.	23-22
Size #12 Contacts 23 Amp Max. Current 1800 VAC #12-#14 AWG				1		7-1	7-1	7-1	7-1	7-1	9-1
				2		10-2	10-2	10-2	10-2	10-2	12-2
				2		12-2	13-2	12-2	12-2	12-2	15-2
				3		12-3	13-3	12-3	12-3	12-3	15-3
				5		Not Avail.	16-5	14-5	14-5	14-5	18-5
				7		Not Avail.	17-7	15-7	Not Avail.	Not Avail.	19-7
				12		Not Avail.	21-12	21-12	Not Avail.	Not Avail.	23-12
Contact Arrangements with Mixed Size (Combo) Layouts	4	2				8-200	8-200	8-200	8-200	8-200	10-200
	8	2				9-201	9-201	9-201	9-201	9-201	11-201
	4			2		9-200	9-200	9-200	9-200	9-200	11-200
	8			2		10-202	10-202	10-202	10-202	10-202	12-202
	4				2	10-201	10-201	10-201	10-201	10-201	12-201
	6				2	12-200	13-200	12-200	12-200	12-200	15-200
	10				2	12-201	13-201	12-201	12-201	12-201	15-201
	12				1	10-200	10-200	10-200	10-200	10-200	12-200

