



## MIL-DTL-38999 Series I, II, III and IV Pin Contact Selection Guide

AS39029 Pin Contacts										
38999 Series I, II, III & IV	Contact Size	Type	Glenair Part Number	Military Part Number	Color Bands			BIN	Wire Size	Tool Code
					1st	2nd	3rd			
#10	S		850-002-10-528	M39029/58-528	GREEN	RED	GREY	528	#10 - #12	Consult Factory
	E		850-007-10-624	M39029/107-624	BLUE	RED	YELLOW	624		
#12	S		850-002-12-365	M39029/58-365	ORANGE	BLUE	GREEN	365	#12 - #14	A, B
	E		850-007-12-623	M39029/107-623	BLUE	RED	ORANGE	623		
	C		852-002-12-211	M39029/28-211	RED	BROWN	BROWN	211	RG174 RG179 RG316	C, I (inner)
	C		852-002-12-409	M39029/28-409	YELLOW	BLACK	WHITE	409	RG180	N, P (outer)
#16	S		850-002-16-364	M39029/58-364	ORANGE	BLUE	YELLOW	364	#16 - #20	A, B
	E		850-007-16-622	M39029/58-622	BLUE	RED	RED	622		
	C		852-008-16-424	M39029/76-424	YELLOW	RED	YELLOW	424	RG174 RG179 RG316	C, H (inner)
	C		852-008-16-425	M39029/76-425	YELLOW	RED	GREEN	425	RG178	Q, R (outer)
#20	S		850-002-20-363	M39029/58-363	ORANGE	BLUE	ORANGE	363	#20 - #24	C, D
	E		850-007-20-621	M39029/107-621	BLUE	RED	BROWN	621		
#22D	S		850-002-22-360	M39029/58-360	ORANGE	BLUE	BLACK	360	#22 - #28	C, E
	E		850-007-22-620	M39029/107-620	BLUE	RED	black	620		

Type	Crimp Style
S	Standard-Duty Crimp
E	Extended-Duty Crimp
C	Coaxial Crimp

BIN Color Coding									
0	1	2	3	4	5	6	7	8	9
BLACK	BROWN	RED	ORANGE	YELLOW	GREEN	BLUE	VIOLET	GREY	WHITE