



# Combo Micro-D for High Power Applications



## OVERVIEW AND PRODUCT SELECTION GUIDE



**Plug Connector**




**Receptacle Connector**

**Glenair's Combo Micro-D's** combine the size and weight advantages of a Micro -D connector with the added ability to handle higher power needs. These connectors feature combinations of .079 inch (2mm) power contacts and TwistPin signal contacts.

**13 Amp Current Rating** – Available in three styles: solder cup, pre-wired pigtails or printed circuit board, these Micro-D connectors handle up to #16 AWG wire.

### Combo Micro-D Solder Cup Connectors


Nonremovable solder cup #16 power contacts for termination to #16 AWG or smaller wire. Micro pins accept #26 AWG or smaller wire. Gold plated contacts are backfilled with rigid epoxy.



**Combo Solder Cup**  
Page E-3

### Combo Micro-D Pre-Wired Pigtails


Crimp contacts are terminated to insulated Teflon® wire. Connectors are backpotted with epoxy, providing strain relief and environmental protection.



**Combo Pre-Wired**  
Page E-6

### Combo Micro-D Printed Circuit Board

Ideal for flexible or rigid circuits, these vertical mount connectors feature high temperature materials to withstand soldering heat. A full range of hardware options is available.



**Combo Board Mount**  
Page E-9

