

Series 805 Mighty Mouse Triple-Start Threaded Coupling Introduction



SECTION C SERIES 805 TRIPLE-START PRODUCT SELECTION GUIDE

Plugs

Page H-6

805-001, 805-002



Series 805 Plugs

These connectors are supplied with a full complement of contacts for termination to insulated wire. The integral shield termination platform accepts **BAND-IT**[®] stainless steel bands (ordered separately), or select connectors with accessory threads for use with a variety of strain relief options. Contacts are crimp-type, and are packaged with the connector.

Crimp Receptacles

Page H-8

805-003, 805-004



Series 805 Receptacles for Insulated Wire

Jam nut for rear panel mounting, square flange and in-line versions make it easy to find a style for every application. The integral shield termination platform accepts **BAND-IT**[®] stainless steel bands (ordered separately), or select connectors with accessory threads for use with a variety of strain relief options. Contacts are crimp-type, and are packaged with the connector.

Solder Cup/PCB Receptacles

Page H-12

805-005, 805-017



Series 805 Receptacles With Solder Cup or PCB Termination

These panel mount connectors feature gold plated, factory-installed non-removable contacts. Choose printed circuit terminals for attachment to flex circuits or rigid boards, or choose solder cup contacts. Connectors are potted with epoxy for general purpose applications, or choose silicone-sealed, leak-tested versions for 1 meter water immersion.

Hermetic Receptacles

Page H-15

800-032



Series 805 Hermetic Receptacles

Need a hermetic for a sealed box or instrument? These stainless steel, glass-sealed connectors are available with solder cup or PC tail contacts. Choose jam nut, square flange or solder mount versions. Contacts are gold plated iron alloy. 100% tested to meet 1×10^{-6} cc/sec helium leakage. Open face pressure rating 1000 PSI.

Sav-Con[®]

Page H-19

805-010



Series 805 Sav-Con[®] Connector Savers

Protect expensive test equipment and cables with Glenair Sav-Con[®] connector savers. These plug/receptacle adapters feature non-removable contacts and a ratcheting coupling mechanism to prevent loosening under vibration.

Cordsets

Page H-21

800-034, 800-041,
800-038, 800-039



Series 805 Cordsets

Specify overmolded cordsets for optimum convenience and performance. Polyurethane jackets provide excellent all-weather cable protection. Fully shielded, with watertight overmolding.

Protective Covers

Page H-25

667-261, 667-262



Series 805 Protective Covers

Thread-on metal covers provide a watertight seal and prevent damage. Select nylon cord or wire rope lanyards with a range of ring terminal diameters to fit just about any need.

Dimensions in inches (millimeters) and are subject to change without notice.