

**M39029/122  
850-319  
Standard Duty Electrical Pin Contact**



AS39029


D38999  
Sr. III

QPL

**Standard Pin Crimp Contact Expanded Performance, for High Vibration,  
High Temperature in MIL-DTL-38999 Series III Connectors**

A

Mating End Size	Wire Accomodation	Military Part Number	Glenair Part Number
23	23-28 AWG	M39029/122-670	850-319-23-670



**Material and Finish**

Contact body - Copper alloy per AS39029 / gold plated per ASTM B488, Type II, Code C, .000050 inches minimum thick over nickel plated per AMS-QQ-N-290, class 2, .000030 to .000150 inches thick.  
Hood - Stainless steel 305, passivated.