

OPTIMIZED
FOR USE WITH



SeaKing
PRESSURE-RATED CABLES



**Super ITS-RG "RadGrip"
reverse-bayonet 5015-type
rubber-covered plug
connectors**



The reverse-bayonet power and signal connector with improved user ergonomics

Glenair Super ITS-RG Series connector plugs with RadGrip™ rubber coupling nut covers are ideal for harsh environmental field applications such as geophysical exploration in arctic conditions, where cryoadhesion (moist skin freezing to metal) is a risk. Super ITS-RG RadGrip™ connectors feature wide, easy-to-grip castellations as well as a raised thumb tab. Built for maximum durability and mechanical protection of plug coupling nuts, Super ITS-RG RadGrip™ is the perfect solution for protection against abusive handling and other forms of mechanical damage. In addition, RadGrip™ facilitates rapid mating and demating of connectors, even when surfaces are slick with oil, dust, water, and other fluids. The highly durable rubber compound may be specified in seven different colors for improved connector and cable identification and management.

Colors available: black, yellow, red, blue, light green, orange, and grey. RadGrip™ covers adhere easily to aluminum alloy, stainless steel, and marine bronze versions of Glenair ITS reverse-bayonet power and signal connectors.

- **Fast, easy, reverse-bayonet coupling: 1/4 Turn**
- **IP67 (mated condition)**
- **Compatible with all Series ITS 5015 Type connectors**
- **High shock and vibration resistance**
- **200 plus insert arrangements available with contact sizes from #20 to #4/0**
- **Audible and visual coupling indicators**
- **Colored materials facilitate connector and cable identification such as in multi-phase power applications**

