

NGCON MIL-PRF-64266/2 Type 180-118ASR Alignment Sleeve Retainer



HOW TO ORDER						
Sample Part Number	180-118	ASR	-15	-10	R	A
Basic Number	NGCON M64266 type connectors					
Alignment Sleeve Retainer	ASR = Alignment Sleeve Retainer					
Shell Size	See 180-118ASR Dimensions table					
Insert Arrangement	See Insert Arrangements table					
ASR Type	P = Plug R = Receptacle (Standard)					
Material/Finish	A = Al Alloy / Anodize (standard) (B = Composite or C = Stainless Steel / Passivate consult factory)					

MATERIAL AND FINISH

- Alignment Sleeve: Ceramic
- Alignment Pin and Screw: Stainless Steel / Passivate

180-118ASR DIMENSIONS		
Shell Size	Insert Arrangement	ØA
-11	-2	.412 / .408
	-4	10.46 / 10.36
-13	-6	.488 / .484
		12.40 / 12.29
-15	-8	.666 / .662
	-10	16.92 / 16.81
-23	-18	1.070 / 1.066
	-36	27.18 / 27.08

INSERT ARRANGEMENTS						
Shell Size -11 Arrangement -2	Shell Size -11 Arrangement -4	Shell Size -13 Arrangement -6	Shell Size -15 Arrangement -8	Shell Size -15 Arrangement -10	Shell Size -23 Arrangement -18	Shell Size -23 Arrangement -36

Receptacle front face shown. ○ = large guide pin ○ = small guide pin