

# IN-LINE SPLICE M81824/1 Type Splice



070-003 • In-Line, Insulated, Environmental. Tin-Plated Copper



HOW TO ORDER			
Sample Part Number	070	-003	-1
Product Series	In-Line Splice		
Basic No.	-003 AS81824/1 Type, Tin-Plated Copper splice		
Size	-1, -2, -3 (See Table)		

## MATERIAL AND PERFORMANCE NOTES

- Splice: Copper, tin-plate over nickel
- Sealing material: thermoplastic, thermally stabilized
- Shrink Sleeve: transparent, heat-shrinkable, crosslinked PVDF, per AMS-DTL-23053/8
- Temperature rating: -55°C to +150°C
- Wire rating: 150°C min
- Color coded seal ring per size dash no. Splice to have matching color stripe.

