

IN-LINE SPLICE GS81824/1 Splice



GS81824/1 • In-Line, Insulated, Environmental. Tin-Plated Copper



MATERIAL AND PERFORMANCE NOTES

- Splice: Copper, tin-plate
- Sealing material: thermoplastic, thermally stabilized
- Shrink Sleeve: transparent, heat-shrinkable, crosslinked PVDF, per AMS-DTL-23053/8
- Temperature rating: -55°C to +150°C
- Cable jacket rating: 150°C min
- Color coded seal ring per size dash no. Splice to have matching color stripe.

HOW TO ORDER			
Sample Part Number	GS81824	/1	-3
Product Series	In-Line Splice		
Basic No.	/1 AS81824/1 Type, Tin-Plated Copper splice		
Size	-1, -2, -3 (See Table)		

