


| Part number | Contact Size | A | | ØB | | ØC | | ØD | | Wire Size | |
|---|---|---|---|---|---|---|---|---|---|---|---|
| | | mm | Inches | mm | Inches | mm | Inches | mm | Inches | mm² | AWG |
| 10-375-20 | 20 | 24,30 | 0,957 | 1,00 | 0,039 | 1,30 | 0,051 | 1,93 | 0,076 | 0,15-0,6 | 26÷20 |
| 10-40579 | 18 | 29,60 | 1,165 | 1,40 | 0,055 | 1,30 | 0,051 | 1,93 | 0,076 | 0,15÷0,6 | 26÷20 |
| 10-40553 | 16S | 26,60 | 1,047 | 1,58 | 0,062 | 1,70 | 0,067 | 2,60 | 0,102 | 1÷1,5 | 18÷16 |
| 10-40553-12 | 16S | 26,60 | 1,047 | 1,58 | 0,062 | 1,19 | 0,047 | 2,59 | 0,102 | 0.6 | 20 |
| 10-40553-13* | 16S | 26,60 | 1,047 | 1,58 | 0,062 | 1,30 | 0,051 | 1,93 | 0,076 | 0,15÷0,6 | 26÷20 |
| 10-40553-15* | 16S | 26,60 | 1,047 | 1,58 | 0,062 | 1,50 | 0,059 | 2,60 | 0,102 | 0,75-1,0 | 18 |
| 10-40553-20 | 16S | 26,60 | 1,047 | 1,58 | 0,062 | 2,00 | 0,079 | 2,90 | 0,114 | 2 | 14 |
| 10-40553-26 | 16S | 26,60 | 1,047 | 1,58 | 0,062 | 2,5 | 0,098 | 3,8 | 0,150 | 2,5-3,0 | 12 |
| 10-40557 | 16 | 31,75 | 1,250 | 1,58 | 0,062 | 1,70 | 0,067 | 2,60 | 0,102 | 1÷1,5 | 18÷16 |
| 10-40557L | 16 | 33,25 | 1,309 | 1,58 | 0,062 | 1,70 | 0,067 | 2,60 | 0,102 | 1÷1,5 | 18÷16 |
| 10-40557-08* | 16 | 31,75 | 1,250 | 1,58 | 0,062 | 0,85 | 0,033 | 1,55 | 0,061 | 0,15÷0,2 | 26÷24 |
| 10-40557-12* | 16 | 31,75 | 1,250 | 1,58 | 0,062 | 1,20 | 0,047 | 2,60 | 0,102 | 0,6 | 20 |
| 10-40557-13* | 16 | 31,75 | 1,250 | 1,58 | 0,062 | 1,30 | 0,051 | 1,93 | 0,076 | 0,15÷0,6 | 26÷20 |
| 10-40557-15* | 16 | 31,75 | 1,250 | 1,58 | 0,062 | 1,50 | 0,059 | 2,60 | 0,102 | 0,75-1,0 | 18 |
| 10-40557-20** | 16 | 31,75 | 1,250 | 1,58 | 0,062 | 2,00 | 0,079 | 2,90 | 0,114 | 2 | 14 |
| 10-40557-22** | 16 | 31,75 | 1,250 | 1,57 | 0,062 | 2,2 | 0,087 | 3,8 | 0,150 | 2,5 | / |
| 10-40557-22L** | 16 | 33,25 | 1,309 | 1,57 | 0,062 | 2,2 | 0,087 | 3,8 | 0,150 | 2,5 | / |
| 10-40557-26** | 16 | 31,75 | 1,250 | 1,58 | 0,062 | 2,5 | 0,098 | 3,8 | 0,150 | 2,5-3,0 | 12 |
| 10-40557-32* | 16 | 31,75 | 1,250 | 1,58 | 0,062 | 0,45 | 0,018 | 1,95 | 0,077 | / | 32÷28 |
| 10-40561 | 12 | 37,65 | 1,482 | 2,38 | 0,094 | 2,50 | 0,098 | 3,90 | 0,154 | 2,5-3,0 | 12 |
| 10-40561-12* | 12 | 37,65 | 1,482 | 2,38 | 0,094 | 1,20 | 0,047 | 2,60 | 0,102 | 0,6 | 20 |
| 10-40561-15* | 12 | 37,65 | 1,482 | 2,38 | 0,094 | 1,50 | 0,059 | 2,60 | 0,102 | 0,75-1,0 | 18 |
| 10-40561-177* | 12 | 37,65 | 1,482 | 2,38 | 0,094 | 1,77 | 0,070 | 2,75 | 0,108 | 1,5 | 18-16 |
| 10-40561-20* | 12 | 37,65 | 1,482 | 2,38 | 0,094 | 2,00 | 0,079 | 3,90 | 0,154 | 2 | 14 |
| 10-40561-22* | 12 | 37,65 | 1,482 | 2,38 | 0,094 | 2,10 | 0,083 | 3,90 | 0,154 | 2,5 | / |
| 10-40561-30** | 12 | 37,65 | 1,482 | 2,38 | 0,094 | 3,00 | 0,118 | 4,80 | 0,189 | 4-5 | / |
| 10-40561-30M** | 12 | 37,65 | 1,482 | 2,38 | 0,094 | 3,30 | 0,130 | 4,20 | 0,165 | 4 | / |
| 10-40561-38** | 12 | 37,65 | 1,482 | 2,38 | 0,094 | 3,60 | 0,142 | 6,8 | 0,268 | 6 | 10 |

Please consult our sales department for other contacts or crimp tooling details.

**PLATING OPTIONS**
**G10 : Silver**
**(Standard)**
**G117 : Gold**

*These contacts accept smaller wire than standard ones. There may be a sealing problem with grommets. The max current rating is limited by the wire max current rating.

** These contacts accept larger wires than standard ones. The reduced air/creepage distance may worsen the service rating and there may be difficulties with grommets. The max current rating is limited by the contact max current rating. See page 4.

Please contact factory for solutions.

© 2013 Glenair, Inc. U.S. CAGE Code 06324 Printed in U.S.A

# Contatti maschio a pinzare
## *Pin crimp contacts*




| Part number | Contact Size | A | | ØB | | ØC | | ØD | | Wire Size | |
|---|---|---|---|---|---|---|---|---|---|---|---|
| | | mm | Inches | mm | Inches | mm | Inches | mm | Inches | $mm^2$ | AWG |
| 10-40792 | 8 | 42,00 | 1,654 | 3,60 | 0,142 | 4,50 | 0,177 | 6,90 | 0,272 | 9 | 8 |
| 10-40792-15* | 8 | 42,00 | 1,654 | 3,60 | 0,142 | 1,50 | 0,059 | 3,40 | 0,134 | 0,75-1,0 | 18 |
| 10-40792-18* | 8 | 42,00 | 1,654 | 3,60 | 0,142 | 1,80 | 0,071 | 3,80 | 0,150 | 1÷2 | 18÷14 |
| 10-40792-20* | 8 | 42,00 | 1,654 | 3,60 | 0,142 | 2,00 | 0,079 | 3,80 | 0,150 | 2 | 14 |
| 10-40792-26* | 8 | 42,00 | 1,654 | 3,60 | 0,142 | 2,5 | 0,098 | 3,8 | 0,150 | 2,5-3,0 | 12 |
| 10-40792-30* | 8 | 42,00 | 1,654 | 3,60 | 0,142 | 3,00 | 0,118 | 4,80 | 0,189 | 4-5 | / |
| 10-40792-38* | 8 | 42,00 | 1,654 | 3,60 | 0,142 | 3,60 | 0,142 | 6,80 | 0,268 | 6 | 10 |
| 10-40792-50** | 8 | 42,00 | 1,654 | 3,60 | 0,142 | 5,00 | 0,197 | 6,90 | 0,272 | 10 | / |
| 10-40792-58** | 8 | 42,00 | 1,654 | 9,05 | 0,356 | 5,80 | 0,228 | 7,80 | 0,307 | 13,2 | 6 |
| 10-113474-4P | 4 | 42,00 | 1,654 | 5,70 | 0,224 | 7,10 | 0,280 | 9,53 | 0,375 | 22-25 | 4 |
| 10-113474-4P-22* | 4 | 42,00 | 1,654 | 5,70 | 0,224 | 2,20 | 0,087 | 3,80 | 0,150 | 2,5 | / |
| 10-113474-4P-25 | Replaced by 10-113474-4P | | | | | | | | | | |
| 10-113474-4P-26* | 4 | 42,00 | 1,654 | 5,70 | 0,224 | 2,50 | 0,098 | 3,80 | 0,150 | 2,5-3,0 | 12 |
| 10-113474-4P-30* | 4 | 42,00 | 1,654 | 5,70 | 0,224 | 3,00 | 0,118 | 4,80 | 0,189 | 4-5 | / |
| 10-113474-4P-38* | 4 | 42,00 | 1,654 | 5,70 | 0,224 | 3,60 | 0,142 | 6,80 | 0,268 | 6 | 10 |
| 10-113474-4P-50* | 4 | 42,00 | 1,654 | 5,70 | 0,224 | 5,00 | 0,197 | 7,00 | 0,276 | 10 | / |
| 10-113474-4P-58* | 4 | 42,00 | 1,654 | 9,05 | 0,356 | 5,80 | 0,228 | 7,80 | 0,307 | 13,2 | 6 |
| 10-113474-4P-62* | 4 | 42,00 | 1,654 | 5,70 | 0,224 | 6,20 | 0,244 | 9,53 | 0,375 | 16 | / |
| 10-113474-1P | 0 | 45,00 | 1,772 | 9,05 | 0,356 | 11,50 | 0,453 | 14,30 | 0,563 | 50-60 | 0 |
| 10-113474-1P-107* | 0 | 45,00 | 1,772 | 9,05 | 0,356 | 10,70 | 0,421 | 14,35 | 0,565 | 50 | / |
| 10-113474-1P-72* | 0 | 45,00 | 1,772 | 9,05 | 0,356 | 7,15 | 0,281 | 9,50 | 0,374 | 22-25 | 4 |
| 10-113474-1P-35* | 0 | 45,00 | 1,772 | 9,05 | 0,356 | 9,00 | 0,354 | 14,35 | 0,565 | 35 | / |
| 10-113474-1P-45* | 0 | 45,00 | 1,772 | 9,05 | 0,356 | 4,55 | 0,179 | 6,80 | 0,268 | 9 | 8 |
| 10-113474-1P-50* | 0 | 45,00 | 1,772 | 9,05 | 0,356 | 5,00 | 0,197 | 7,00 | 0,276 | 10 | / |
| 10-113474-1P-58* | 0 | 45,00 | 1,772 | 9,05 | 0,356 | 5,80 | 0,228 | 7,80 | 0,307 | 13,2 | 6 |
| 10-113474-1P-62* | 0 | 45,00 | 1,772 | 9,05 | 0,356 | 6,20 | 0,244 | 9,50 | 0,374 | 16 | / |
| 10-113474-0P* | 4/0 | 63,00 | 2,480 | 12,69 | 0,500 | 16,5 | 0,650 | 20 | 0,787 | 107 | 4/0 |
| 10-113474-0P-78* | 4/0 | 63,00 | 2,480 | 12,69 | 0,500 | 7,10 | 0,280 | 9,53 | 0,375 | 22-25 | 4 |
| 10-113474-0P-107* | 4/0 | 63,00 | 2,480 | 12,69 | 0,500 | 10,7 | 0,421 | 14,35 | 0,565 | 50 | / |
| 10-113474-0P-144* | 4/0 | 63,00 | 2,480 | 12,69 | 0,500 | 14,5 | 0,571 | 20 | 0,787 | 70 | / |

Please consult our sales department for other contacts or crimp tooling details.

**PLATING OPTIONS**
**G10 : Silver**
**(Standard)**
**G117 : Gold**

*These contacts accept smaller wire than standard ones. There may be a sealing problem with grommets. The max current rating is limited by the wire max current rating.

** These contacts accept larger wires than standard ones. The reduced air/creepage distance may worsen the service rating and there may be difficulties with grommets. The max current rating is limited by the contact max current rating. See page 4.

Please contact factory for solutions.

© 2013 Glenair, Inc.