



SUBSEA/SHALLOW WATER: AQUAMOUSE™

SERIES 802

AquaMouse

Ultraminiature High-pressure

Originally developed for petroleum pipeline inspection equipment, Series 802 connectors are available in ten sizes from 1 to 130 contacts and equipped with Viton® O-rings to withstand exposure to corrosive chemicals and high temperature environments. These connectors feature high density crimp Mighty Mouse inserts, 316 stainless steel or marine bronze shells and a piston O-ring for hydrostatic sealing. Series 802 insulated wire, panel mount receptacles can be ordered as square flange, in-line or jam-nut versions. Choose integral shield termination platform or accessory thread for use with a variety of strain relief options. Crimp style gold-plated crimp contacts accept #12-30 wire. Connectors are backfilled with epoxy potting compound. Hermetic glass-sealed connectors come with solder cup contacts (non-removable) or PC tails. 100% tested to meet 1 x 10⁻⁷ cc/sec helium leakage. Mated pressure rating 3500 PSI.



- 1000 PSI open face pressure rated
- High-temperature and corrosive chemical-resistant Viton® or Nitrile O-rings
- Ultraminiature #23 contacts
- Size #20, #20HD, #16, #12, #8 signal, power, fiber optic and shielded contacts
- Discrete connectors and turnkey cable assemblies


AQUAMOUSE CONNECTOR CONFIGURATIONS AND CLASSES




Series 802 Plugs




Series 802 Jam Nut Mount



Series 802 Square Flange Receptacle



Series 802 Hermetic



Series 802 Hermetic Bulkhead Feed-Thru