

	GLMC MICRO WET-CON	
---	-----------------------------------	--

GLMC Cross Reference List

Introduction

Glenair's Marine Molded Connectors (GLMC) follow industry standard part numbering with a Glenair (**GL**) prefix.

*As standard GLMC Bulkheads (BH) are supplied with 2ft of Glenair **GS22759** colour coded wires and In-Lines (IL) with 3ft of cable.

*As standard GLMC Bulkhead material is Stainless Steel 316L. Other materials (PEEK, Brass, etc.) available upon request.

Glenair	MacArtney/SubConn	TE/Seacon	BIRNS
Glenair Micro Wet-Con	Micro-Circular	Micro Wet-Con	Aqua-Mate
Bulkheads (BH)			
GLMC-BH-2-F-0002	MCBH2F	MC-BH-2-F	MCBH2F
GLMC-BH-2-M-0002	MCBH2M	MC-BH-2-M	MCBH2M
GLMC-BH-3-F-0002	MCBH3F	MC-BH-3-F	MCBH3F
GLMC-BH-3-M-0002	MCBH3M	MC-BH-3-M	MCBH3M
GLMC-BH-4-F-0002	MCBH4F	MC-BH-4-F	MCBH4F
GLMC-BH-4-M-0002	MCBH4M	MC-BH-4-M	MCBH4M
GLMC-BH-5-F-0002	MCBH5F	MC-BH-5-F	MCBH5F
GLMC-BH-5-M-0002	MCBH5M	MC-BH-5-M	MCBH5M
GLMC-BH-6-F-0002	MCBH6F	MC-BH-6-F	MCBH6F
GLMC-BH-6-M-0002	MCBH6M	MC-BH-6-M	MCBH6M
GLMC-BH-8-F-0002	MCBH8F	MC-BH-8-F	MCBH8F
GLMC-BH-8-M-0002	MCBH8M	MC-BH-8-M	MCBH8M
GLMC-BH-10-F-0002	MCBH10F	MC-BH-10-F	MCBH10F
GLMC-BH-10-M-0002	MCBH10M	MC-BH-10-M	MCBH10M
GLMC-BH-12-F-0002	MCBH12F	MC-BH-12-F	MCBH12F
GLMC-BH-12-M-0002	MCBH12M	MC-BH-12-M	MCBH12M
GLMC-BH-16-F-0002	MCBH16F	MC-BH-16-F	MCBH16F
GLMC-BH-16-M-0002	MCBH16M	MC-BH-16-M	MCBH16M
In-Lines (IL)			
GLMC-IL-2-F-0003	MCIL2F	MC-IL-2-F	MCIL2F
GLMC-IL-2-M-0003	MCIL2M	MC-IL-2-M	MCIL2M
GLMC-IL-3-F-0003	MCIL3F	MC-IL-3-F	MCIL3F
GLMC-IL-3-M-0003	MCIL3M	MC-IL-3-M	MCIL3M
GLMC-IL-4-F-0003	MCIL4F	MC-IL-4-F	MCIL4F
GLMC-IL-4-M-0003	MCIL4M	MC-IL-4-M	MCIL4M
GLMC-IL-5-F-0003	MCIL5F	MC-IL-5-F	MCIL5F
GLMC-IL-5-M-0003	MCIL5M	MC-IL-5-M	MCIL5M
GLMC-IL-6-F-0003	MCIL6F	MC-IL-6-F	MCIL6F

Glenair	MacArtney/SubConn	TE/Seacon	BIRNS
Glenair Micro Wet-Con	Micro-Circular	Micro Wet-Con	Aqua-Mate
GLMC-IL-6-M-0003	MCIL6M	MC-IL-6-M	MCIL6M
GLMC-IL-8-F-0003	MCIL8F	MC-IL-8-F	MCIL8F
GLMC-IL-8-M-0003	MCIL8M	MC-IL-8-M	MCIL8M
GLMC-IL-10-F-0003	MCIL10F	MC-IL-10-F	MCIL10F
GLMC-IL-10-M-0003	MCIL10M	MC-IL-10-M	MCIL10M
GLMC-IL-12-F-0003	MCIL12F	MC-IL-12-F	MCIL12F
GLMC-IL-12-M-0003	MCIL12M	MC-IL-12-M	MCIL12M
GLMC-IL-16-F-0003	MCIL16F	MC-IL-16-F	MCIL16F
GLMC-IL-16-M-0003	MCIL16M	MC-IL-16-M	MCIL16M
Dummy Connectors (DC)			
GLMC-DC-2-F	MCDC2F	MC-DC-2-F	MCDC2F
GLMC-DC-2-M	MCDC2M	MC-DC-2-M	MCDC2M
GLMC-DC-3-F	MCDC3F	MC-DC-3-F	MCDC3F
GLMC-DC-3-M	MCDC3M	MC-DC-3-M	MCDC3M
GLMC-DC-4-F	MCDC4F	MC-DC-4-F	MCDC4F
GLMC-DC-4-M	MCDC4M	MC-DC-4-M	MCDC4M
GLMC-DC-5-F	MCDC5F	MC-DC-5-F	MCDC5F
GLMC-DC-5-M	MCDC5M	MC-DC-5-M	MCDC5M
GLMC-DC-6-F	MCDC6F	MC-DC-6-F	MCDC6F
GLMC-DC-6-M	MCDC6M	MC-DC-6-M	MCDC6M
GLMC-DC-8-F	MCDC8F	MC-DC-8-F	MCDC8F
GLMC-DC-8-M	MCDC8M	MC-DC-8-M	MCDC8M
GLMC-DC-10-F	MCDC10F	MC-DC-10-F	MCDC10F
GLMC-DC-10-M	MCDC10M	MC-DC-10-M	MCDC10M
GLMC-DC-12-F	MCDC12F	MC-DC-12-F	MCDC12F
GLMC-DC-12-M	MCDC12M	MC-DC-12-M	MCDC12M
GLMC-DC-16-F	MCDC16F	MC-DC-16-F	MCDC16F
GLMC-DC-16-M	MCDC16M	MC-DC-16-M	MCDC16M
Locking Sleeves (LS)			
GLMC-LS-FA	MCDLS-F	MC-DLS-F	FLS-MC
GLMC-LS-MA	MCDLS-M	MC-DLS-M	MLS-MC
GLMC-LS-FB	DLSA-F	DLSA-F	FLS-MCA
GLMC-LS-MB	DLSA-M	DLSA-M	MLS-MCA