MWEB Pre-Wired and Solder Cup Connectors
MWEB2L

MWEB EdgeBoard Connectors For Input/Output Wire-To-Board Applications

With 128 or 184 contacts, these narrow profile factory-terminated MWEB connectors provide a space-saving I/O wire to board solution. Connector width of .25 inch (6.4 mm.) allows for high-density card slots.

High Performance TwistPin Contacts

Suitable for airborne avionics processors and mission-critical computers, these pre-wired connectors feature interfacial seals and backpotting for improved environmental protection. Or, choose solder cup connectors for integration into wire harnesses.

How To Order MWEB Pigtail Conncectors

Sample Part Number	MWEB2L	-128	P	-6	K	7	-18	N
Series	**MWEB2L**							
Connector Layout	**128**, **184N**							
Contact Type	**P** - Pin **S** - Socket							
Wire Gage (AWG)	**4** - #24 **6** - #26 **8** - #28 **0** - #30							
Wire Type	**K** - M22759/11 600 VRMS Fluoropolymer (TFE) **J** - M22759/33 600 VRMS Modified Cross-Linked Tefzel® (ETFE)							
Wire Color	**1** - White **2** - Yellow **7** - Ten Color Repeating							
Wire Length Inches	**18** - Total Length In Inches. "18" Specifies 18 Inches.							
Hardware Option	**N** - No hardware							

How To Order MWEB Solder Cup Connectors

Sample Part Number	MWEB2L	-128	P	S	N
Series	**MWEB2L**				
Connector Layout	**128**, **184N**				
Contact Type	**P** - Pin **S** - Socket				
Termination Type	**S** - Solder Cup				
Hardware Option	**N** - No Hardware				

© 2013 Glenair, Inc.