



Glenair MIL-DTL-26482 Type Bayonet-Lock Connectors



MIL-DTL-26482 Series II Type Rugged bayonet-coupling crimp-contact connectors

- For rugged military and industrial applications that require quick mate/demate three-point bayonet-lock coupling
- Glenair 26482-style connectors offer high-performance plating options unavailable in standard mil-spec parts including TZ Tin-Zinc, our recommended RoHS-material AMS2434 Type 2 qualified cadmium-compatible replacement, ZR black zinc-nickel, and Z1 passivated stainless steel.
- Complete range of tooled MIL-STD-1669 insert arrangements for size #20, #16, and #12 signal and power crimp, rear-release contacts. The Glenair solution offers three shell size 8 arrangements not available in the mil-spec version

