


103-026 and -027
100% AmberStrand® Composite Braid
and 75% / 25% AmberStrand®/Nickel Copper Braid
for EMI Shielding Applications



Specify number of feet on purchase order.

103-026 (100% AmberStrand®)			
Dash Number	Nominal I.D.	Wire Bundle Range	Approximate Grams Per Foot
004	.125 (3.2)	.093 (2.4) .140 (3.5)	1.0
008	.250 (6.4)	.125 (3.2) .312 (7.9)	1.8
012	.375 (9.5)	.250 (6.4) .437 (11.1)	2.3
016	.500 (12.7)	.250 (6.4) .590 (15.0)	3.0
020	.625 (15.9)	.375 (9.5) .700 (17.8)	4.4
024	.750 (19.1)	.500 (12.7) .830 (21.1)	5.2
032	1.000 (25.4)	.780 (19.8) 1.100 (27.94)	8.0
040	1.250 (31.8)	.938 (23.8) 1.312 (33.3)	10.0
048	1.500 (38.1)	1.187 (30.1) 1.590 (40.37)	15.2
064	2.000 (50.8)	1.312 (33.3) 2.090 (50.8)	22.0

103-027 (75% AmberStrand® and 25% Nickel Copper)			
Dash Number	Nominal I.D.	Wire Bundle Range	Approximate Grams Per Foot
004	.125 (3.2)	.093 (2.4) .140 (3.5)	1.5
008	.250 (6.4)	.125 (3.2) .312 (7.9)	2.4
012	.375 (9.5)	.250 (6.4) .437 (11.1)	3.9
016	.500 (12.7)	.250 (6.4) .590 (15.0)	5.4
020	.625 (15.9)	.375 (9.5) .700 (17.8)	6.4
024	.750 (19.1)	.500 (12.7) .830 (21.1)	7.2
032	1.000 (25.4)	.780 (19.8) 1.100 (27.94)	11.0
040	1.250 (31.8)	.938 (23.8) 1.312 (33.3)	15.0
048	1.500 (38.1)	1.187 (30.1) 1.590 (40.37)	25.2
064	2.000 (50.8)	1.312 (33.3) 2.090 (50.8)	32.0

Metric dimensions (mm) are indicated in parentheses.