

D38999/50
Dummy Stowage Receptacle
Bayonet Coupling



MIL-DTL-38999

MATING CONNECTOR

MIL-DTL-38999 Series IV

**Basic
Part No.**

D38999/50


Class Per Spec.

*(Finish is Cadmium Olive Drab
over Electroless Nickel)*

B

W

**Shell
Size Code**



**TABLE I: Dash Number, Cable Entry
and Backshell Dimensions**

Shell Size Code	Shell Size Ref.	A		B BSC		C		D		Ø E	
		±.043	(±1.10)			+ 0 -.015	(0.00) (-0.39)	±.010	(±0.25)	±.008	(±0.2)
B	11	1.030	(26.15)	.812	(20.62)	.793	(20.15)	.093	(2.35)	.130	(3.3)
C	13	1.124	(28.55)	.906	(23.02)	.919	(23.35)	.093	(2.35)	.130	(3.3)
D	15	1.219	(30.95)	.969	(24.62)	1.044	(26.52)	.093	(2.35)	.130	(3.3)
E	17	1.313	(33.35)	1.062	(26.98)	1.170	(29.72)	.093	(2.35)	.130	(3.3)
F	19	1.439	(36.55)	1.156	(29.36)	1.294	(32.87)	.093	(2.35)	.130	(3.3)
G	21	1.561	(39.65)	1.250	(31.76)	1.419	(36.05)	.124	(3.15)	.130	(3.3)
H	23	1.687	(42.85)	1.375	(34.92)	1.544	(39.22)	.124	(3.15)	.150	(3.8)
J	25	1.813	(46.05)	1.500	(38.10)	1.669	(42.40)	.124	(3.15)	.150	(3.8)

APPLICATION NOTES

1. Assembly to be identified with manufacturer's name and part number, space permitting.
2. For complete dimensions, see the applicable Military Specification.
3. Metric dimensions (mm) are in parentheses.

Dimensions in inches (millimeters) and are subject to change without notice.

© 2013 Glenair, Inc.

U.S. CAGE Code 06324

Printed in U.S.A.