

AS85049 QUALIFIED PRODUCTS Military Standard Backshells and Accessories



Part Number Index

Military Standard Backshells and Accessories Part Number Index				
AS85049 QUALIFIED PRODUCTS				
Industry Specification Number	Part Identification Number	Glenair Commercial Part Number	Description	Glenair Connector Designator/ Interface
AS85049/1	M85049/1	620-053 Style B	Straight Strain Relief	MS V Thread
AS85049/2	M85049/2	620-053 Style C	Straight Environmental Strain Relief	MS V Thread
AS85049/3	M85049/3 Style 1 M85049/3 Style 2 M85049/3 Style 3	GS85049/3 377	Straight Environmental Backshell	C MIL-DTL-22992, C, J & R
AS85049/4	M85049/4 Style 1 M85049/4 Style 2 M85049/4 Style 3	GS85049/4 377	Straight Step-Up Environmental Backshell	C MIL-DTL-22992, C, J & R
AS85049/5	M85049/5 Style 1 M85049/5 Style 2 M85049/5 Style 3	377-034	Straight Step-Down Environmental Backshell	C MIL-DTL-22992, C, J & R
AS85049/6	M85049/6	390AB001	45° RFI/EMI Environmental Backshell	A AS50151; MIL-DTL-26482, Series 2; AS81703 Series 3; MIL-DTL-83723, Series III
AS85049/7	M85049/7	370AB001	45° Environmental Backshell	A AS50151; MIL-DTL-26482, Series 2; AS81703 Series 3; MIL-DTL-83723, Series III
AS85049/8	M85049/8	390AA001	90° RFI/EMI Environmental Backshell	A AS50151; MIL-DTL-26482, Series 2; AS81703 Series 3; MIL-DTL-83723, Series III
AS85049/9	M85049/9	360-061 Consult sales@glenair.com for more information	90° Environmental Backshell	A AS50151; MIL-DTL-26482, Series 2; AS81703 Series 3; MIL-DTL-83723, Series III
AS85049/10	M85049/10	390AS001	Straight RFI/EMI Environmental Backshell	A AS50151; MIL-DTL-26482, Series 2; AS81703 Series 3; MIL-DTL-83723, Series III
AS85049/11	M85049/11	370AS001	Straight Environmental Backshell	A AS50151; MIL-DTL-26482, Series 2; AS81703 Series 3; MIL-DTL-83723, Series III
AS85049/14	M85049/14-M85049/14 N M85049/14 S	610HS011	E Nut E Nut, Non-Detented, Self Locking E Nut, Detented, Self-Locking	H MIL-DTL-38999, Ser. III & IV EN3645
AS85049/15	M85049/15-M85049/15 N M85049/15 S M85049/15 G M85049/15 H	450HB001 450HB041 450HB043 450HB043 G 450HB041 G	45° Qwik-Ty® Strain Relief Non-Detented, Self-Locking Detented Self-Locking Detented, Self-Locking, Ground Lug Non-Detented Self-Locking, Ground Lug	H MIL-DTL-38999, Ser. III & IV; EN3645
AS85049/16	M85049/16-M85049/16 N M85049/16 S M85049/16 G M85049/16 H	450HA001 450HA041 450HA043 450HA043 G 450HA041 G	90° Qwik-Ty® Strain Relief Non-Detented, Self-Locking Detented Self-Locking Detented, Self-Locking, Ground Lug Non-Detented Self-Locking, Ground Lug	H MIL-DTL-38999, Ser. III & IV; EN3645

AS85049 QUALIFIED PRODUCTS

Military Standard Backshells and Accessories



Part Number Index

Military Standard Backshells and Accessories Part and Page Number Index				
AS85049 QUALIFIED PRODUCTS				
Industry Specification Number	Part Identification Number	Glenair Commercial Part Number	Description	Glenair Connector Designator/ Interface
AS85049/17	M85049/17	390FS012	Straight RFI/EMI Environmental Backshell	F MIL-DTL-38999 Series I & II
AS85049/18	M85049/18	390HS011	Straight RFI/EMI Environmental Backshell	H MIL-DTL-38999, Ser. III & IV; EN3645
AS85049/19	M85049/19	380HS007	Straight Environmental Backshell	H MIL-DTL-38999, Ser. III & IV; EN3645
AS85049/20	M85049/20	440HS063	Straight Crimp Ring Backshell and Crimp Ring	H MIL-DTL-38999, Ser. III & IV; EN3645
AS85049/21	M85049/21	360HS002	Straight Non-Environmental Strain Relief Backshell	H MIL-DTL-38999, Ser. III & IV; EN3645
AS85049/23	M85049/23	380AB001	45° RFI-EMI Non-Environmental Backshell	A AS50151; MIL-DTL-26482, Series 2; AS81703 Series 3; MIL-DTL-83723, Series III
AS85049/24	M85049/24	390AA001	90° RFI-EMI Non-Environmental Backshell	A AS50151; MIL-DTL-26482, Series 2; AS81703 Series 3; MIL-DTL-83723, Series III
AS85049/25	M85049/25	380AS001	Straight RFI-EMI Non-Environmental Backshell	A AS50151; MIL-DTL-26482, Series 2; AS81703 Series 3; MIL-DTL-83723, Series III
AS85049/26	M85049/26-1 M85049/26-2 M85049/26-3	440AS063 687-150	Adapter Only Crimp Ring Only Adapter with Crimp Ring	A AS50151; MIL-DTL-26482, Series 2; AS81703 Series 3; MIL-DTL-83723, Series III
AS85049/27	M85049/27-M85049/27 N M85049/27 S	610FS011	E Nut E Nut, Non-Detented, Self-Locking E Nut, Detented, Self-Locking	F MIL-DTL-38999 Series I & II
AS85049/28	M85049/28	G61570	Strt. Rectangular Non-Environmental Backshell	---
AS85049/29	M85049/29	360FS002	Straight Non-Environmental Strain Relief Backshell	F MIL-DTL-38999 Series I & II
AS85049/30	M85049/30	400FS001	Straight RFI-EMI Individual Shield Termination Backshell	F MIL-DTL-38999 Series I & II
AS85049/31	M85049/31-M85049/31 N M85049/31 S	610AS011	E Nut E Nut, Non-Detented, Self-Locking E Nut, Detented, Self Locking	A AS50151; MIL-DTL-26482, Series 2; AS81703 Series 3; MIL-DTL-83723, Series III
AS85049/33	M85049/33-2	440FS063	Straight Crimp Ring Non-Environmental Backshell	F MIL-DTL-38999 Series I & II
AS85049/34	M85049/34	320	Straight Adapter and Extender For use with MS3114 & MS3124 Connectors	D MIL-DTL-26482 Series I
AS85049/36	M85049/36	380FS008	Straight RFI-EMI Non-Environmental Backshell	F MIL-DTL-38999 Series I & II
AS85049/37	M85049/37	380FD007	90° RFI-EMI Non-Environmental Backshell	F MIL-DTL-38999 Series I & II
AS85049/38	M85049/38 N M85049/38 S	620HS011 620HS048	Str. Strain Relief, Non-Detented Self-Locking Straight Strain Relief, Detented Self-Locking	H MIL-DTL-38999 Series III & IV EN3645

AS85049 QUALIFIED PRODUCTS

Military Standard Backshells and Accessories



Part Number Index

Military Standard Backshells and Accessories Part and Page Number Index				
AS85049 QUALIFIED PRODUCTS				
Industry Specification Number	Part Identification Number	Glenair Commercial Part Number	Description	Glenair Connector Designator/ Interface
AS85049/39	M85049/39	620HA011 620HA048	90° Strain Relief, Non-Detented Self-Locking 90° Strain Relief, Detented Self-Locking	H MIL-DTL-38999 Series III & IV; EN3645
AS85049/41	M85049/41	620-053 Style A	Straight Strain Relief	MS V Thread
AS85049/42	M85049/42	620-053 Style H	Straight Strain Relief	MS V Thread
AS85049/43	M85049/43	620AB047	45° Strain Relief	---
AS85049/44	M85049/44	G61257	Straight Rectangular Strain Relief Backshell	---
AS85049/45	M85049/45	440FS037	Straight Strain Relief	F MIL-DTL-38999 Series I & II
AS85049/46	M85049/46	440FA037	90° Non-Self-Locking Composite Strain Relief	F MIL-DTL-38999 Series I & II
AS85049/81	M85049/81	GS85049/81 687	Sealing Plug	MIL-DTL-38999
AS85049/82 AS85049/83 AS85049/84	M85049/82 M85049/83 M85049/84	440AS069 440AH069 440AJ069	Straight Banding Backshell 45° Banding Backshell 90° Banding Backshell	A AS50151; MIL-DTL-26482, Series 2; AS81703 Series 3; MIL-DTL-83723, Series III
AS85049/85 AS85049/86 AS85049/87	M85049/85 M85049/86 M85049/87	440FS069 440FH069 440FJ069	Straight Banding Backshell 45° Banding Backshell 90° Banding Backshell	F MIL-DTL-38999 Series I & I
AS85049/88 AS85049/89 AS85049/90	M85049/88 M85049/89 M85049/90	440HS069 440HH069 440-HJ069	Straight Banding Backshell 45° Banding Backshell 90° Banding Backshell	H MIL-DTL-38999 Ser. III & IV EN3645
AS85049/91 AS85049/92	M85049/91 M85049/92	620HS042 620HA042	Straight Strain Relief 90° Strain Relief	H MIL-DTL-38999 Ser. III & IV EN3645
AS85049/93	M85049/93	687-207	Banding Split Ring	---
AS85049/94	M85049/94	GS85049/94 687	Full Perimeter Mounting Flange	---
AS85049/95	M85049/95	GS85049/95 687	3/4 Perimeter Mounting Flange	---
AS85049/96	M85049/96	GS85049/96 687	1/4 Perimeter Mounting Flange	---
AS85049/103	M85049/103	319-137	Straight Shield Sock Composite Adapter with Detented or Non-Detented Self-Locking Coupling Nut	H MIL-DTL-38999 Ser. III & IV EN3645
AS85049/104	M85049/104	319-137	45° Shield Sock Composite Adapter with Detented or Non-Detented Self-Locking Coupling Nut	H MIL-DTL-38999 Ser. III & IV EN3645
AS85049/105	M85049/105	319-137	90° Shield Sock Composite Adapter with Detented or Non-Detented Self-Locking Coupling Nut	H MIL-DTL-38999 Ser. III & IV EN3645
AS85049/109	M85049/109	319AS001	Straight Shield Sock Shrink Boot Adapter with Detented or Non-Detented Self-Locking or Non-Self Locking Coupling Nut	A AS50151; MIL-DTL-26482, Series 2; AS81703 Series 3; MIL-DTL-83723, Series III
AS85049/111	M85049/111	319AJ001	90° Shield Sock Sock Shrink Boot Adapter with Optional Self-Locking Coupling Nut	A AS50151; MIL-DTL-26482, Series 2; AS81703 Series 3; MIL-DTL-83723, Series III

AS85049 QUALIFIED PRODUCTS

Military Standard Backshells and Accessories



Part Number Index

Military Standard Backshells and Accessories Part and Page Number Index				
AS85049 QUALIFIED PRODUCTS				
Industry Specification Number	Part Identification Number	Glenair Commercial Part Number	Description	Glenair Connector Designator/ Interface
AS85049/112	M85049/112	319FS001	Straight Shield Sock Shrink Boot Adapter with Optional Self-Locking Coupling Nut	F MIL-DTL-38999 Series I & II
AS85049/114	M85049/114	319FJ001	90° Shield Sock Shrink Boot Adapter with Detented or Non-Detented Self-Locking Coupling Nut	F MIL-DTL-38999 Series I & II
AS85049/115	M85049/115	319HS001	Straight Shield Sock Shrink Boot Adapter with Optional Self-Locking Coupling Nut	H MIL-DTL-38999 Ser. III & IV EN3645
AS85049/118	M85049/118	620AS038	Straight Strain Relief, Self-Locking or Non-Self-Locking	A AS50151; MIL-DTL-26482, Series 2; AS81703 Series 3; MIL-DTL-83723, Series III
AS85049/120	M85049/120	620AA038	90° Strain Relief, Self-Locking or Non-Self-Locking	A AS50151; MIL-DTL-26482, Series 2; AS81703 Series 3; MIL-DTL-83723, Series III
AS85049/121	M85049/121	620FS038	Straight Strain Relief, Self-Locking or Non-Self-Locking	F MIL-DTL-38999 Series I & II; MIL-DTL-27599
AS85049/123	M85049/123	620FA038	90° Strain Relief, Self-Locking or Non-Self-Locking	F MIL-DTL-38999 Series I & II; MIL-DTL-27599
AS85049/124	M85049/124	620HS038	Straight Strain Relief, Self-Locking or Non-Self-Locking	H MIL-DTL-38999 Ser. III & IV EN3645
AS85049/126	M85049/126	620HA038	90° Strain Relief, Self-Locking or Non-Self-Locking	H MIL-DTL-38999 Ser. III & IV EN3645
AS85049/127	M85049/127	687-581	Bushing Strip	--
AS85049/128-3 AS85049/128-4	M85049/128-3 M85049/128-4	600-052 600-052-1	Standard Clamping Band Precoiled Standard Clamping Band	AS85049/128
AS85049/130	M85049/130	Consult sales@glenair.com for more information	Gasket	--
AS85049/139	M85049/139	GS85049/139 687	Telescoping Bushing, C or L	--
AS85049/140	M85049/140-05 M85049/140-09 M85049/140-20 M85049/140-25	770-003S107 770-006S102W1 770-007S104 770-018S102	Straight Lipped Heat Shrink Boot Str. Lipped Long Tail Low Profile H.S. Boot Str. Lipped Mini. Long Tail Low Profile H.S. Boot Straight Lipped Sealing Heat Shrink Boot	--
AS85049/141	M85049/141-03 M85049/141-10 M85049/141-19	770-003A105 770-006A103 770-007A103	90° Lipped Heat Shrink Boot 90° Lipped Low Profile Heat Shrink Boot 90° Lipped Mini. Low Profile Heat Shrink Boot	--
AS85049/142	M85049/142-02 M85049/142-05 M85049/142-10	770-011T102 770-010Y105 770-013110W1	Tee Transition Wide Body Heat Shrink Boot Wye Transition Wide Body Heat Shrink Boot 1:3 Transition Wide Body Heat Shrink Boot	--