





# M28840/22 Metal Conduit Bushing



| Size | MIL-<br>DTL-28840/04<br>Size Ref. | A<br>+.020 (.50)<br>-.000 (.000) | B<br>+.005 (.12)<br>-.000 (.000) | C<br>+.000 (.000)<br>-.005 (.12) | D<br>+.000 (.000)<br>-.005 (.12) |
|------|-----------------------------------|----------------------------------|----------------------------------|----------------------------------|----------------------------------|
| 03   | 03                                | .375 (9.53)                      | .540 (13.71)                     | .625 (15.87)                     | .525 (13.34)                     |
| 04   | 04                                | .500 (12.70)                     | .665 (16.89)                     | .750 (19.05)                     | .650 (16.51)                     |
| 05   | 05                                | .625 (15.87)                     | .780 (19.81)                     | .875 (22.23)                     | .775 (19.69)                     |
| 06   | 06                                | .750 (19.05)                     | .940 (23.88)                     | 1.000 (25.40)                    | .900 (22.86)                     |
| 08   | 08                                | 1.000 (25.40)                    | 1.225 (31.12)                    | 1.375 (34.93)                    | 1.275 (32.39)                    |
| 10   | 10                                | 1.250 (31.75)                    | 1.470 (37.34)                    | 1.625 (41.28)                    | 1.525 (38.74)                    |
| 12   | 12                                | 1.500 (38.10)                    | 1.740 (44.20)                    | 1.875 (47.65)                    | 1.775 (45.09)                    |
| 16   | 16                                | 2.000 (50.80)                    | 2.215 (56.26)                    | 2.375 (60.33)                    | 2.275 (57.79)                    |

Dimensions in Inches (millimeters) are subject to change without notice.