

BATTLE-TESTED

STAR-PAN™

Commercial protocol cables, adapters, and accessories
808-079 USB Type A Cable



USB Type A Cable

SPECIFICATIONS

- USB Type A host adapter cable, without USB VBUS
- Santoprene jacketed cable, black
- TPE overmolded, ergonomic connector strain relief, black.
- Mighty Mouse 807 (NATO standard) connector and USB-A connector
- Weight, 18" cable: 26g
- Export classification: 3A611.x

HOW TO ORDER

Sample Part Number:	808-079	-24
Cable Series	USB-A Host Adapter Cable	
Length Designator	In inches. Maximum 180" Omit for default length of 18.00"	



QUALIFIED FOR USE WITH ALL STAR-PAN POWER / DATA HUBS

LIGHT, II, IV, AND VI

HUB PORT DESIGNATOR:

EUD

COMMERCIAL PROTOCOL CABLES AND ADAPTERS

