

BATTLE-TESTED

STAR-PAN™

Radio cables and adapters

808-035 AN/PRC-117G Radio Cable



RADIO CABLES AND ADAPTERS



AN/PRC-117G, AN/PRC-160
RF-7800M-MP,
RF7800H-MP
Radio Cable

SPECIFICATIONS

- For interconnection of referenced man-pack radio type to STAR-PAN power / data hubs
- Nomex® braided wire protection, olive drab. Consult factory for other cable finish options
- Overmolded, ergonomic connector strain reliefs, desert tan
- Mighty Mouse 807 (NATO standard) connector and J4 Radio connector
- Weight, 32" cable: 90g
- Export classification: ECCN 3A611.x

HOW TO ORDER

Sample Part Number:		808-035	-24
Cable Series	AN/PRC-117G Radio Adapter Cable		
P2 Angle Option	-R = Right Angle -U = 180° Omit for straight (default)		
Length Designator	In inches (6.00" min.) Omit for default length of 32.00"		



QUALIFIED FOR USE WITH ALL STAR-PAN POWER / DATA HUBS

LIGHT, II, IV, AND VI

HUB PORT DESIGNATOR:
RADIO

