

BATTLE-TESTED

STAR-PAN™

Radio cables and adapters

808-088 AN/PRC-117G PAN Port Radio Cable



RADIO CABLES AND ADAPTERS



AN/PRC-117G, AN/PRC-160
RF-7800M-MP,
RF7800H-MP
Radio Cable

SPECIFICATIONS

- For interconnection of referenced man-pack radio type to STAR-PAN power / data hubs
- Nomex® braided wire protection, olive drab. Consult factory for other cable finish options
- Overmolded, ergonomic connector strain reliefs, desert tan
- Mighty Mouse 807 (NATO standard) connector and J4 Radio connector.
- Weight, 32" cable: 90g
- Export classification: ECCN 3A611.x
- PAN Port connection

HOW TO ORDER

Sample Part Number:	808-088	-36
Cable Series	AN/PRC-117G / RF7800 Radio Adapter Cable	
P2 Angle Option	-R = Right Angle -U = 180° Omit for straight (default)	
Length Designator	In inches (6.00" min.) Omit for default length of 32.00"	



QUALIFIED FOR USE WITH ALL STAR-PAN POWER / DATA HUBS
LIGHT, II, IV, AND VI
HUB PORT DESIGNATOR:
PAN

