METAL PROTECTIVE COVERS

Metal covers protect unmated series 921 connectors. Available with no attachment or choose sash chain or nylon-coated wire rope attachments from the ordering table. For shell materials and finishes see HOW TO ORDER table.

Plug Cover with Sash Chain

Plug Cover with Nylon Coated SST Wire Rope

Receptacle Cover with Sash Chain

Receptacle Cover with Nylon Coated SST Wire Rope

How To Order					
Sample Part Number		**921-02T**	**-24**	**F6**	**N**
Series	**921-02T** = receptacle cover **921-06T** = plug cover				
Shell Size	**24, 28, 32, 40**				
Material and Finish	**F6** = aluminum, black electrostatic paint **G3** = aluminum, cadmium, olive drab **MT** = aluminum nickel-PTFE **M** = aluminum, electroless nickel **G2** = aluminum, anodize, hardcoat **Z1** = stainless steel, passivate **AB** = marine bronze, unplated				
Attachment Type	**N** = no attachment **S** = sash chain with clevis fitting **H** = nylon coated SST wire rope with ring terminal **SR** = sash chain with clevis fitting for jam-nut **HR** = nylon coated SST wire rope with ring for jam-nut				

© 2020 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324 • Super ITS™ catalog
Dimensions in millimeter (inches) are subject to change without notice.

Super ITS-921 Reverse-Bayonet Rigid Insert, High-Ampacity Connectors

Protective Covers and Sealing Plugs

PLASTIC PROTECTIVE COVERS

Plastic cap for receptacle and plug connectors for protection against dust and mechanical damage for use during shipping and storage.



Receptacle Plastic Dust Cap Dimensions				
Part Number	Shell Size	ØA ±0.25 (.010)	ØB ±0.25 (.010)	ØC ± 0.78 (.031)
IT P02-24	24	40.65 (1.600)	43.20 (1.701)	47.00 (1.850)
IT P02-28	28	46.45 (1.829)	49.05 (1.931)	52.00 (2.047)
IT P02-32	32	53.15 (2.093)	55.75 (2.195)	60.00 (2.362)
IT P02-40	40	65.25 (2.569)	67.85 (2.671)	72.00 (2.835)

PlugPlasticDustCapDimensions				
PartNumber	ShellSize	ØA ±0.25(.010	ØB ±0.25(.010	ØC ±0.78(.031
IT90376-24R	24	37.16 (1.463)	39.94 (1.572)	43.18 (1.700)
IT90376-28R	28	43.56 (1.715)	45.46 (1.790)	49.53 (1.950)
IT90376-32R	32	49.91 (1.965)	51.82 (2.040)	56.39 (2.220)
IT90376-40R	40	61.98 (2.440)	64.26 (2.530)	67.56 (2.660)

SEALING PLUG

Sealing plugs and wire seals are used to seal unwired contact cavities.

Sealing Plug	
Contact Size	Part Number
16	921-16-HP
12	921-12-HP
8	921-8-HP
4	921-4-HP
1/0	921-0-HP
2/0	921-2-0-HP

© 2020 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324 • Super ITS™ catalog
Dimensions in millimeter (inches) are subject to change without notice.