PLUG (06) COVER

Stainless Steel Chain (T)



Stainless Steel Wire Rope (TF)



Sample Part Number

NGITB	06	T	-18	FK1
Series	Plug Cover	Lanyard Type	Shell Size Desig.	Material and Finish

Lanyard Type	
Code	Description
T	Stainless Steel Chain
TF	Stainless Steel Wire Rope

Lanyard and Standard Ring Eyelet Diameter dimensions				
Shell Size Desig.	SST Chain (Lanyard Type T		SST Wire Rope (Laynard Type TF	
	Std Length (C	Ring Eyelet Dia (F	Std Length (D	Ring Eyelet Dia (G
-14S	123 (4.84)	4.3 (0.17)	193 (7.60)	4.3 (0.17)
-16S	123 (4.84)	4.3 (0.17)	193 (7.60)	4.3 (0.17)
-18	123 (4.84)	4.3 (0.17)	193 (7.60)	4.3 (0.17)
-20	138 (5.43)	4.8 (0.19)	193 (7.60)	4.3 (0.17)
-22	138 (5.43)	4.8 (0.19)	193 (7.60)	4.3 (0.17)
-24	138 (5.43)	4.8 (0.19)	193 (7.60)	4.3 (0.17)
-28	206 (8.11)	4.8 (0.19)	193 (7.60)	5.3 (0.21)
-32	206 (8.11)	5.6 (0.22)	193 (7.60)	5.3 (0.21)
-36	206 (8.11)	5.6 (0.22)	193 (7.60)	5.3 (0.21)
-40	206 (8.11)	5.6 (0.22)	193 (7.60)	5.3 (0.21)

Material and Finish	
Code	Material/Finish
FK1	Stainless Steel

© 2020 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324 • Super ITS™ catalog
Dimensions in millimeter (inches) are subject to change without notice.

JAM-NUT (07) RECEPTACLE COVER

Stainless Steel
Chain (T)



Stainless Steel
Wire Rope (TF)



Sample Part Number				
NGITB	07	T	-18	FK1
Series	Basic P/N	Lanyard Type	Shell Size	Material and Finish

Lanyard Type	
Code	Description
T	Stainless Steel Chain
TF	Stainless Steel Wire Rope

Lanyard and Ring Attachment Dimensions				
	SST Chain (Lanyard Type T)		SST Wire Rope (Laynard Type TF)	
Shell Size	Std Length (C)	Ring Eyelet Dia (F)	Std Length (E)	Ring Eyelet Dia (G)
14S	4.764 (121)	1.142 (29.00)	8.189 (208)	1.142 (29.00)
16S	4.764 (121)	1.266 (32.15)	8.189 (208)	1.266 (32.15)
18	5.394 (137)	1.392 (35.35)	8.189 (208)	1.392 (35.35)
20	5.433 (138)	1.516 (38.50)	8.189 (208)	1.516 (38.50)
22	5.433 (138)	1.614 (41.00)	8.189 (208)	1.614 (41.00)
24	5.433 (138)	1.760 (44.70)*	8.189 (208)	1.772 (45.00)*
28	8.701 (221)	2.016 (51.20)*	8.189 (208)	2.016 (51.20)*
32	8.701 (221)	2.264 (57.50)*	8.189 (208)	2.264 (57.50)*
36	8.701 (221)	2.512 (63.80)*	8.189 (208)	2.512 (63.80)*
40	8.701 (221)	2.764 (70.20)*	8.189 (208)	2.764 (70.20)*

Material and Finish	
Code	Material / Finish
FK1	Stainless Steel

© 2020 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324 • Super ITS™ catalog
Dimensions in millimeter (inches) are subject to change without notice.

WALL MOUNT (02) RECEPTACLE COVER





Sample Part Number				
NGITB	02	T	-18	FK1
Series	Shell Style Cover Type	Lanyard Type	Shell Size	Material and Finish

Lanyard Type	
Code	Description
T	Stainless Steel Chain
TF	Stainless Steel Wire Rope

Lanyard and Ring Attachment Dimensions				
Shell Size Desig.	SST Chain (Lanyard Type T)		SST Wire Rope (Laynard Type TF)	
	Std Length (C)	Ring Eyelet Dia (F)	Std Length (D)	Ring Eyelet Dia (G)
-14S	108	.169 (4.3)	7.598 (193)	.169 (4.3)
-16S	108	.169 (4.3)	7.598 (193)	.169 (4.3)
-18	123	.169 (4.3)	7.598 (193)	.169 (4.3)
-20	123	.169 (4.3)	7.598 (193)	.169 (4.3)
-22	123	.169 (4.3)	7.598 (193)	.169 (4.3)
-24	123	.169 (4.3)	7.598 (193)	.169 (4.3)
-28	206	.220 (5.6)	7.598 (193)	.209 (5.3)
-32	206	.220 (5.6)	7.598 (193)	.209 (5.3)
-36	206	.220 (5.6)	7.598 (193)	.209 (5.3)
-40	206	.220 (5.6)	7.598 (193)	.209 (5.3)

Material and Finish	
Code	Material / Finish
FK1	Stainless Steel

© 2020 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324 • Super ITS™ catalog
Dimensions in millimeter (inches) are subject to change without notice.