Seacrow™

SUPER ITS

REVERSE-BAYONET

Super ITS-MB Seacrow™ Connectors

For amphibious vehicle, geo-marine, and other harsh-environment applications

Super ITS - MB Seacrow reverse bayonet marine bronze series connectors are compliant with MIL-DTL-5015, using the same power and signal insert arrangements but with reverse-bayonet coupling and precision-machined marine bronze construction. Typically used for power and signal transmission, with wires from 26 AWG to 4/0, these ultra-harsh environment connectors are ideally suited for above-deck navy shipboard applications where repeated exposure to seawater and salt spray can quickly degrade effectiveness of connector finishes leading to corrosion and possible failure.

Super-ITS MB Seacrow connectors exceed VG95234 standards for both sealing and durability. Over 200 plus MIL-STD-1651A, standard and combo insert arrangements are available, in 9 shell sizes fully tooled and ready for immediate shipment. A wide selection of backshell options including cable shield termination for EMI/RFI applications and cable sealing backshells for conduit termination ensure reliable shielding and sealing performance. IP67 protection standard with IP68 available on request.

- **Precision-machined marine bronze alloy for superior corrosion resistance and reliable mating in seawater and other harsh environments—no plating or passivization required**
- **Ideal for shipboard and other harsh geo-marine applications (VG95234 versions available for military / defense)**
- **IP67 environmental sealing in mated condition; IP68 versions available**
- **Super ITS - MB Seacrow connectors accomodate wires from 26 AWG square to 4/0 AWG**
- **Over 200 power and signal arrangements IAW MIL-DTL-5015 / VG95234**
- **Precision-machined for outstanding mating performance and durability**

© 2020 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324 • Super ITS™ catalog

Dimensions in millimeter (inches) are subject to change without notice.