




# SERIES 701 SeaKing™ Junior High-Density Dry-Mate Connectors Insert arrangements




## SEAKING™ JUNIOR TOOLED INSERT ARRANGEMENTS (STANDARD LAYOUTS)

Contact Legend  
#22D • #16 ⊕  
#20 ⊖ #12 ⊖




Insert Arrangement	9-35	9-98	11-2	11-4	11-5	11-35	11-98
No. of Contacts	6	3	2	4	5	13	6
Contact Size	#22D	#20	#16	#20	#20	#22D	#20
Service Rating	M	I	I	I	I	M	I

Contact Legend  
#22D • #16 ⊕  
#20 ⊖ #12 ⊖




Insert Arrangement	11-99	13-4	13-8	13-98	13-35	15-5
No. of Contacts	7	4	8	10	22	5
Contact Size	#20	#16	#20	#20	#22D	#16
Service Rating	I	I	I	I	M	II

Contact Legend  
#22D • #16 ⊕  
#20 ⊖ #12 ⊖




Insert Arrangement	15-18	15-19	15-35	17-6	17-8
No. of Contacts	18	19	37	6	8
Contact Size	#20	#20	#22D	#12	#16
Service Rating	I	I	M	I	II

Contact Legend  
#22D • #16 ⊕  
#20 ⊖ #12 ⊖



Insert Arrangement	17-26	17-35	19-11	19-32
No. of Contacts	26	55	11	32
Contact Size	#20	#22D	#16	#20
Service Rating	I	M	II	I

Contact Legend  
#22D • #16 ⊕  
#20 ⊖ #12 ⊖



Insert Arrangement	19-35	19-45	21-11	21-16
No. of Contacts	66	67	11	16
Contact Size	#22D	#22D	#12	#16
Service Rating	M	M	I	II







# SERIES 701 SeaKing™ Junior High-Density Dry-Mate Connectors Insert arrangements



## SEAKING™ JUNIOR TOOLED INSERT ARRANGEMENTS (STANDARD LAYOUTS)

Contact Legend





#22D • #16 ⊕  
#20 ⊖ #12 ◐



Insert Arrangement	21-24	21-25	21-27	21-35
No. of Contacts	24	25	27	79
Contact Size	#20	#20	#20	#22D
Service Rating	I	I	I	M

Contact Legend





#22D • #16 ⊕  
#20 ⊖ #12 ◐



Insert Arrangement	21-41	23-21	23-32	23-34
No. of Contacts	41	21	32	34
Contact Size	#20	#16	#20	#20
Service Rating	I	II	I	I

Contact Legend




#22D • #16 ⊕  
#20 ⊖ #12 ◐



Insert Arrangement	23-35	23-36	23-53	23-55
No. of Contacts	100	36	53	55
Contact Size	#22D	#20	#20	#20
Service Rating	M	I	I	I

Contact Legend

#22D • #16 ⊕  
#20 ⊖ #12 ◐



Insert Arrangement	23-97	23-99	25-19
No. of Contacts	16	11	19
Contact Size	#16	#16	#12
Service Rating	I	II	I






# SERIES 701 SeaKing™ Junior High-Density Dry-Mate Connectors Insert arrangements




## SEAKING™ JUNIOR TOOLED INSERT ARRANGEMENTS (STANDARD LAYOUTS)

Contact Legend  
 #22D • #16 ⊕  
 #20 ⊖ #12 ◐






Insert Arrangement	25-29	25-35	25-37
No. of Contacts	29	128	37
Contact Size	#16	#22D	#16
Service Rating	I	M	II

Contact Legend  
 #22D • #16 ⊕  
 #20 ⊖ #12 ◐






Insert Arrangement	25-61
No. of Contacts	61
Contact Size	#20
Service Rating	I

## SEAKING™ JUNIOR TOOLED INSERT ARRANGEMENTS (HIGH-DENSITY LAYOUTS)



Insert Arrangement	9-23	11-23	13-23	15-23
No. of Contacts	9	19	32	55
Contact Size	#23	#23	#23	#23
Service Rating	N	N	N	N





Insert Arrangement	17-23	19-23	21-23
No. of Contacts	73	88	121
Contact Size	#23	#23	#23
Service Rating	N	N	N



# SERIES 701 SeaKing™ Junior High-Density Dry-Mate Connectors Insert arrangements







## SEAKING™ JUNIOR TOOLED INSERT ARRANGEMENTS (HIGH-DENSITY LAYOUTS)



Insert Arrangement	23-23	25-23
No. of Contacts	151	187
Contact Size	#23	#23
Service Rating	N	N




## SEAKING™ JUNIOR TOOLED INSERT ARRANGEMENTS (COMBO LAYOUTS)

Contact Legend  
 #22D • #20 ⊖ #16 ⊕  
 #12 ◐ #10 ⊙






Insert Arrangement	15-15		15-97		17-99		19-28	
No. of Contacts and Size	1X #16	14X #20	4X #16	8X #20	2X #16	21X #20	2X #16	26X #20
Service Rating								

Contact Legend  
 #22D • #20 ⊖ #16 ⊕  
 #12 ◐ #10 ⊙



Insert Arrangement	19-30		21-39		25-4	
No. of Contacts and Size	1X #16	29X #20	2X #16	37X #20	8X #16	48X #20
Service Rating						

Contact Legend  
 #22D • #20 ⊖ #16 ⊕  
 #12 ◐ #10 ⊙



Insert Arrangement	25-11		25-24		25-43	
No. of Contacts and Size	9X #10	2X #20	12X #12	12X #16	20X #16	23X #20
Service Rating	N					






# SERIES 701 SeaKing™ Junior High-Density Dry-Mate Connectors Insert arrangements






## SEAKING™ JUNIOR TOOLED INSERT ARRANGEMENTS (SPECIAL SHIELDED LAYOUTS)

Contact Legend






Shell Size - Insert Arrangement	9-1	11-1*	17-2
No. of Contacts	1x #8	1x #8	1x #8      38x #22D

Contact Legend






Shell Size - Insert Arrangement	17-22	17-60	17-75
No. of Contacts	2x #8      2x #12	2x #8      8x #22	2x #8

Contact Legend



Shell Size - Insert Arrangement	19-4	19-17	19-18
No. of Contacts	4x #8	2x #8      4x #16      1x #20      10x #22D	4x #8      14x #22D

Contact Legend



Shell Size - Insert Arrangement	21-75	23-5	23-6
No. of Contacts and Size	4x #8	5x #8	6x #8






# SERIES 701 SeaKing™ Junior High-Density Dry-Mate Connectors Insert arrangements



## SEAKING™ JUNIOR TOOLED INSERT ARRANGEMENTS (SPECIAL SHIELDED LAYOUTS)

Contact Legend



- #22D #16
- #20 #12
- #8



Shell Size - Insert Arrangement	25-7		25-8		25-17	
No. of Contacts and Size	2x #8	97x #22	8x #8		6x #8	36x #22

Contact Legend



- #22D #16
- #20 #12
- #8



Shell Size - Insert Arrangement	25-20				25-26		
No. of Contacts and Size	3x #8	4x #12	13x #16	10x #20	4x #8	5x #12	16x #20

Contact Legend

- #22D #16
- #20 #12
- #8



Shell Size - Insert Arrangement	25-41					25-46		
No. of Contacts and Size	3x #8	2x #12	11x #16	3x #20	22x #22D	2x #8	4x #16	40x #20