VersaLink™ Circular Backshell Selection Guide

Backshells listed here are specially designed to fit over shielded contacts and their grommet followers to accommodate the appropriate bend radius of the cables they are used with.

HIGH SPEED CONTACT BACKSHELL OPTIONS

Series	EMI	Environmental	Strain Relief	Straight	45°	90°	Description
Straight 620V**S**090	None	No	Saddle Bar		N/A	N/A	**Lightweight Strain Relief** (to be used at a minimum)
Straight 4470V**S**1130 **45 Degree** 4470V**M**1130 **90 Degree** 4470V**N**1130	Banding Porch	No	Saddle Bar				**EMI/RFI Banding Strain Relief** Advised for overbraid with or without individual shield terminations requiring medium duty strain relief
Straight 443V**S**042 **45 Degree** 443V**M**042 **90 Degree** 443V**N**042	Banding Porch	O-Ring Gland (Splash Proof)	Saddle Bar				**EMI/RFI Banding Strain Relief, Environmental** Advised for environmental overbraid with or without individual shield terminations requiring medium duty strain relief

© 2024 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324 • VersaLink Connectors
Dimensions in Inch (millimeter) are subject to change without notice.