




SERIES 70 10K PSI / 700 BAR / 7000 M



SeaKing™ High-Pressure Subsea Connectors, Cables, and PBOF Assemblies

709-016 Splash Proof Cap Assembly for Recaptacle

SeaKing - How To Order				
Sample Part Number	709-016	-K	L	4
Product Series	709-016 = Splash proof cap assembly for SeaKing receptacle (FCR or BCR)			
Shell Size	See Dimensions Table			
Lanyard Option	(Omit If None)			
Lanyard Length	Standard Lanyard Length: 4 Inches (Omit If None)			



MATERIAL COMPOSITION:

- Cap: black delrin (acetal)
- Rope: stainless steel w/nylon coating
- Loop sleeve: stainless steel, passivated
- Eyelet: stainless steel, passivated

Shell Size	A		B	Eyelet Screw Size	FCR Screw Size
	In.	mm			
E	1.02	25.91	13/16-12 UN-2B	4 or 6	4
G	1.15	29.21	15/16-12 UN-2B	4 or 6	4
K	1.27	32.26	1 1/16-12 UN-2B	4 or 6	6
L	1.38	35.05	1 3/16-12 UN-2B	4 or 6	6
M	1.51	38.35	1 5/16-12 UN-2B	8	8
O	1.74	44.20	1 9/16-12 UN-2B	8	8
P	1.89	48.01	1 11/16-12 UN-2B	8	8
Q	2.01	51.05	1 13/16-12 UN-2B	10	10
R	2.14	54.36	1 15/16-12 UN-2B	10	10

SUBSEA/DEEPWATER: SEAKING™